


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE	DIMENSIONS in. [mm]				
		L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
PN10-6RX	#6	1.13 [28,7]	.37 [9,4]	.33 [8,4]	.94 [23,9]	.15 [3,8]
PN10-8RX	#8	1.13 [28,7]	.37 [9,4]	.33 [8,4]	.94 [23,9]	.17 [4,3]
PN10-10RX	#10	1.13 [28,7]	.37 [9,4]	.33 [8,4]	.94 [23,9]	.20 [5,1]
PN10-14RX	1/4"	1.27 [32,3]	.52 [13,2]	.42 [10,7]	1.01 [25,7]	.27 [6,9]
PN10-56RX	5/16"	1.27 [32,3]	.52 [13,2]	.42 [10,7]	1.01 [25,7]	.34 [8,6]
PN10-38RX	3/8"	1.35 [34,3]	.58 [14,7]	.46 [11,7]	1.06 [26,9]	.40 [10,2]

NOTES:


- USED FOR:
 - #12-10 AWG [4,0-6,0 mm²] SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600 V. MAX. VOLTAGE RATING
(1000 V. IN SIGNS, FIXTURES & LUMINARIES)
- INSTALLATION TOOLS:
 - UL APPROVED: CT-600A (CT-550CH), CT-1550, CT-1551, CT-2550 (CT-2550CH)
 - PANDUIT APPROVED: CT-100A
- WIRE STRIP LENGTH: 9/32" ^{+1/32}/₀ [7,1^{+0,8}/₀]
- MATERIAL:
 - STAMPING: .04" [1,0] THK COPPER, TIN PLATED
 - HOUSING: NYLON, YELLOW
 - SLEEVE: BRASS, TIN PLATED
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED
587H
E52164



CERTIFIED
LR31212

										TITLE RING TERMINALS, 3 PC. NYLON INSULATION, #12-10			
										CUSTOMER DRAWING			
										ITEM REVISION NAME N41273BA/08		<div>PANDUIT</div>	
										DATASET FILE NAME N41273BA_DC/08A			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.13] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION			
08	10.16.12	JBN	LCA	VMB	REVISED INSTALLATION TOOLS NOTES. UPDATED DRAWING TO CURRENT STANDARDS.	A41273				MATERIAL: SEE NOTES			
										DRAWING NUMBER: A41273			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY DAW	DATE -	CHK CJH	SCALE N.T.S.	SHT 1 OF 1	SIZE A	