
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	TAB SIZE	WIRE RANGE AWG (mm²)	HOUSING COLOR	MAX INSUL DIA	DIMENSIONS in		
PREF I X	170 2175				A ±.03	B ±.01	C (0.3)
DNF18-188	.187 × .020 (4.8 × 0.5)	22-18 (.5-1.0)	RED	.137 (3.48)	.76 (19.3)	.23 (5.8)	.10 (2.5)
DNF 14 - 188	.187 × .020 (4.8 × 0.5)	16-14 (1.5-2.5)	BLUE	.162 (4.11)	.76 (19.3)	.23 (5.8)	.10 (2.5)




## NOTES:

- I.UL LISTED AND CSA CERTIFIED FOR:
  - A. 300V. MAX. VOLTAGE RATING
  - B. STRANDED COPPER WIRE ONLY
  - C. 194° F (90° C) MAX. TEMP. RATING
- 2. SEE www.panduit.com

FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE

- 3. MATERIAL:
  - A. STAMPING: .016 (0.4) THK BRASS, TIN PLATED
  - B. SLEEVE: BRASS, TIN PLATED
  - C. HOUSING: NYLON
- 4. WIRE STRIP LENGTH 9/32 +1/32 (7.1 +0.8)
- 5. INITIAL INSERTION FORCE 12 LB. (53 N) MAX INITIAL WITHDRAWAL FORCE 12 LB. (53 N) MAX 6 LB. (27 N) MIN
- 6. INSTALLATION TOOLS:
  A. UL LISTED AND CSA CERTIFIED: CT-500, CT-600-A
  B. PANDUIT APPROVED: CT-100, CT-160, CT-260,
  CT-400, CT-460(FOR DNF14-188 ONLY)
  CT-1550, CT-1551, CT-2500
- 7. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS OR mm2



1 1	8/11	SHOR	ADDED INSTALLATION TOOLS	
10	7/11	SB	Added Note # 2	
REV	DATE	BY	DESCRIPTION	DR/

	CORP
•	CURF

TINLEY PARK, ILLINOIS

NYLON INSULATED FEMALE DISCONNECT, FUNNELED WIRE ENTRY (.188 SERIES)

DAW | SOALE NONE |

DRAWING NO. A41313