



VAPOR BARRIER NON-METALLIC CABLE BOXES

Vapor Barrier Cable Boxes
2-3/4 in. Deep, 18.0 Cu. in., 1/2 in. Setback

A83



Catalog #: 2011FBAR

APPLICATIONS

Vapor barrier boxes prevent unwanted penetration of exterior air and help maintain the existing interior environment from elements outside the structure. RACO® nonmetallic vapor barrier cable boxes provide the installer with a cost alternative that is lightweight and easy to install and provide excellent protection for wiring system or devices. RACO® Nonmetallic cable boxes are used in branch circuit wiring to splice wires and accommodate wiring devices such as switches and receptacle.

PRODUCT FEATURES

- Self-clamping wire entry clamps
- Vapor/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- N/A

CSA

CSA C22.2 #18

GENERAL PRODUCT INFORMATION

Wiring System:	Nonmetallic Sheathed Cable
Color:	Yellow

RECOMMENDED MAX LOAD

Ceiling Fan (Dynamic) Lbs.:	No
Fixture (Static) Lbs.:	50

CONFIGURATION

Cable Clamps:	4
Bracket Type:	Flush
Bracket Setback:	1/2 in.

DRAWING DIMENSIONS

Dimension A:	2-3/4 in.
--------------	-----------

PRODUCT MEASUREMENTS

Depth:	2-3/4 in.
Cubic Inches (cm ³):	18.0 (295.0)
Wt. Ea. (Lbs.):	0.256
Product Length (in.):	3.13
Product Width (in.):	3.63
Product Height (in.):	4.63

PACKAGING

Minimum Pack Qty.:	50
Std. Pkg.:	50
Product UPC-A Labeled:	Yes
Weight (Lbs. Per/C):	25.60
Ship Carton Length (in.):	21.50
Ship Carton Width (in.):	18.38
Ship Carton Height (in.):	6.63
Ctn Weight (Lbs.):	12.80
Pallet Qty:	1600
UPC Number:	805035000212
I2of5:	30805035000213