

Order code	Description	Shape	Base	ANSI code	Color temp. (K)	Average life (hrs)	Lumen output (lm)	Mean lumens (lm)	CRI	Operating position	Finish	Luminaire	Case qty (master)
<b>150 watts</b>													
58025	MH150W/U/PS/740 STD	ED17	E26	M102/E	4 000	15 000	14 000	10 500	65	U	Clear	E	12
58018	MH150W/C/U/PS/737 STD	ED17	E26	M102/E	3 700	15 000	13 300	10 000	70	U	Coated	E	12
58053	MP150W/U/UVS/PS/740 STD	EDX17	E26	M102/O	4 000	15 000	13 300	10 000	65	U	Clear	O	12
58054	MP150W/C/U/UVS/PS/737 STD	EDX17	E26	M102/O	3 700	15 000	12 600	9 500	70	U	Coated	O	12
58038	MH150W/U/ED28/PS/740 STD	ED28	E39	M102/E	4 000	15 000	14 000	10 500	68	U	Clear	E	12
58057	MP150W/C/U/ED28/UVS/PS/737 STD	ED28	EX39	M102/O	3 700	15 000	12 600	9 500	70	U	Coated	O	12
<b>175 watts</b>													
58044	MS175W/BU/MED/PS/740 STD	ED17	E26	M152/E	4 000	15 000	17 500	14 000	65	BU±15°	Clear	E	12
59144	MS175W/C/BU/MED/PS/737 STD	ED17	E26	M152/E	3 700	15 000	16 600	13 300	70	BU±15°	Coated	E	12
57986	MS175W/BU/PS/740 STD	ED28	E39	M152/E	4 000	15 000	17 500	14 000	65	BU±15°	Clear	E	12
57984	MS175W/C/BU/PS/737 STD	ED28	E39	M152/E	3 700	15 000	16 600	13 300	70	BU±15°	Coated	E	12
<b>200 watts</b>													
57976	MS200W/BU/MED/PS/740 STD	ED17	E26	M136/E	4 000	12 000	21 000	16 800	68	BU±15°	Clear	E	12
57967	MS200W/V/PS/740 STD	ED28	E39	M136/E	4 000	15 000	21 000	16 800	68	BU±15°	Clear	E	12
57987	MS200W/C/V/PS/737 STD	ED28	E39	M136/E	3 700	20 000	20 000	16 000	70	BU±15°	Coated	E	12
<b>250 watts</b>													
58072	MS250W/V/PS/740 STD	ED28	E39	M153/E	4 000	20 000	25 000	19 000	65	BU±15°	Clear	E	12
57999	MS250W/C/V/PS/737 STD	ED28	E39	M153/E	3 700	20 000	23 800	18 088	70	BU±15°	Coated	E	12
57998	MS250W/H75/PS/740 STD	ED28	E39	M153/E	4 000	10 000	22 000	17 600	68	HOR±75°	Clear	E	12
57980	MP250W/BU/UVS/PS/740 STD	ED28	EX39	M153/O	4 000	15 000	23 800	19 000	65	BU±15°	Clear	O	12
<b>320 watts</b>													
57964	MS320W/V/ED37/PS/740 STD	ED37	E39	M154/E	4 000	20 000	33 000	26 400	65	BU±15°	Clear	E	6
59147	MS320W/H75/ED28/PS/740 STD	ED28	E39	M154/E	4 000	10 000	30 000	24 000	68	HOR±75°	Clear	E	12
58026	MP320W/BU/ED28/UVS/PS/740 STD	ED28	EX39	M154/O	4 000	20 000	31 000	24 800	65	BU±15°	Clear	O	12
58027	MP320W/C/BU/ED28/UVS/PS/737 STD	ED28	EX39	M154/O	3 700	20 000	29 000	23 200	70	BU±15°	Coated	O	12
58051	MP320W/BU/ED37/UVS/PS/740 STD	ED37	EX39	M154/O	4 000	20 000	31 000	24 800	65	BU±15°	Clear	O	6
<b>350 watts</b>													
58024	MS350W/V/PS/740 STD	ED37	E39	M131/E	4 000	20 000	37 000	29 000	65	BU±15°	Clear	E	6
57988	MS350W/C/V/PS/737 STD	ED37	E39	M131/E	3 700	20 000	35 000	28 000	70	BU±15°	Coated	E	6
58052	MP350W/V/UVS/PS/740 STD	ED37	EX39	M131/O	4 000	20 000	35 000	28 000	65	BU±15°	Clear	O	6
59146	MP350W/C/V/UVS/PS/737 STD	ED37	EX39	M131/O	3 700	20 000	33 000	26 000	70	BU±15°	Coated	O	6
<b>400 watts</b>													
58001	MS400W/V/ED28/PS/740 STD	ED28	E39	M155/E	4 000	20 000	44 000	35 200	65	BU±15°	Clear	E	12
57994	MS400W/V/PS/740 STD	ED37	E39	M155/E	4 000	20 000	44 000	35 000	68	BU±15°	Clear	E	6
58070	MP400W/C/V/UVS/PS/737 STD	ED37	EX39	M155/O	3 700	20 000	39 000	31 000	70	BU±15°	Coated	O	6
<b>450 watts</b>													
59140	MS450W/V/PS/740 STD	ED37	E39	M155/E	4 000	20 000	50 000	40 000	65	BU±15°	Clear	E	6
57981	MP450W/BU/UVS/PS/740 STD	ED37	EX39	M155/O	4 000	20 000	47 000	37 600	65	BU±15°	Clear	O	6
<b>1 000 watts</b>													
61055	MS1000W/BU/ED37/PS/740 STD	ED37	E39	M141/E	4 000	12 000	115 000	86 000	68	BU±15°	Clear	E	6

O = Open rated for indoor fixtures E = Enclosed rated for indoor or outdoor fixtures  
 Note: Lamp description containing UVS have the UV Stop feature.



# Traditional



MOL.: 5 7/16 in. (138 mm)  
 Ø 2 1/8 in. (54 mm)  
 LCL.: 3 3/8 in. (86 mm)

ED17



MOL.: 9 3/4 in. (248 mm)  
 Ø 1 7/8 in. (48 mm)  
 LCL.: 5 in. (127 mm)

T15



MOL.: 8 5/16 in. (211 mm)  
 Ø 3 1/2 in. (89 mm)  
 LCL.: 5 in. (127 mm)

ED28



MOL.: 11 1/2 in. (292 mm)  
 Ø 4 5/8 in. (117.5 mm)  
 LCL.: 7 in. (178 mm)

ED37



MOL.: 15 13/32 in. (391 mm)  
 Ø 7 in. (178 mm)  
 LCL.: 9 1/2 in. (241 mm)

BT56

Order code	Description	Shape	Base	ANSI code	Color temp. (K)	Lumen output (lm)	Mean lumens (lm)	Average life (hrs)	CRI	Operating position	Finish	Luminaire	Case qty (master)
<b>175 watts</b>													
58041	MH175W/U/MED STD	ED17	E26	M57/E	4 000	14 000	9 100	10 000	65	U	Clear	E	12
57979	MH175W/C/U/MED STD	ED17	E26	M57/E	3 700	13 300	8 600	10 000	70	U	Coated	E	12
58010	MH175W/U STD	ED28	E39	M57/E	4 000	14 000	9 100	10 000	65	U	Clear	E	12
58022	MH175W/C/U STD	ED28	E39	M57/E	3 700	13 300	8 600	10 000	70	U	Coated	E	12
<b>250 watts</b>													
57978	MH250W/U STD	ED28	E39	M58/E	4 000	21 000	13 700	10 000	65	U	Clear	E	12
57977	MH250W/C/U STD	ED28	E39	M58/E	3 700	20 000	13 000	10 000	70	U	Coated	E	12
<b>400 watts</b>													
57966	MH400W/U/ED28 STD	ED28	E39	M59/E	4 000	36 000	23 000	20 000	65	U	Clear	E	12
58049	MH400W/C/U/ED28 STD	ED28	E39	M59/E	3 700	34 000	22 000	20 000	70	U	Coated	E	12
58048	MH400W/U STD	ED37	E39	M59/E	4 000	36 000	23 000	20 000	65	U	Clear	E	6
58000	MH400W/C/U STD	ED37	E39	M59/E	3 700	34 000	22 000	20 000	70	U	Coated	E	6
59145	MS400W/HOR STD	ED37	EP39	M59/E	4 000	40 000	26 000	20 000	65	HOR±45°	Clear	E	6
58019	MPI400W/BU STD	ED37	EX39	M59/O	4 000	38 000	30 400	20 000	65	BU±15°	Clear	O	6
58076	MH400W/U/T15 STD	T15	E39	M59/E	4 000	36 000	23 000	15 000	65	U	Clear	E	12
<b>1 000 watts</b>													
61056	MH1000W/U/ED37 STD	ED37	E39	M47/E	4 000	110 000	71 000	12 000	65	U	Clear	E	6
57993	MH1000W/U STD	BT56	E39	M47/E	4 000	110 000	71 000	12 000	65	U	Clear	E	6

O = Open rated for indoor fixtures E = Enclosed rated for indoor or outdoor fixtures