

Eaton SVX200A1-4A1N1

Catalog number: SVX200A1-4A1N1

Eaton SVX adjustable frequency drive, 200HP, NEMA Type 1/IP21, 480V, FR9, Three-phase, EMC H, Standard Software, A/N keypad, No brake chopper, Standard boards



General specifications

Product Name	Catalog Number
Eaton SVX adjustable frequency drive	SVX200A1-4A1N1
UPC	Product Length/Depth
782116094196	13.4 in
Product Height	Product Width
45.3 in	18.9 in
Product Weight	Warranty
321.9 lb	2 year
Compliances	Certifications
Contact Manufacturer	IEC 61800-2 EN 61800-3 Level H UL 508C

defaultTaxonomyAttributeLabel

Frame size

9

Modification

Standard boards

Input

EMC H

Three-phase

Brake chopper

No brake chopper

Horsepower

200 hp

Keypad

Alphanumeric

Rating

NEMA 1, IP21

Software

Standard

Voltage rating

480 V

Resources

Application notes

SPI - Variable frequency drives with a common DC bus

Electromagnetic compatibility (EMC)

Connecting drives to generator supplies

Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

Catalogs

Product Datasheet - SVX200A1-4A1N1

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Drawings

SVX and SPX Series FR4-FR11 PDF Open Drawings

SVX_(FR9) 2D Drawing Xchange

SVX_(FR9) AutoCAD 2D Footprint

SVX_(FR9) AutoCAD 2D Footprint (mm)

SVX_(FR9) 2D PDF

SVX_(FR9) 3D Inventor

SVX_(FR9) 3D Model Xchange

Installation instructions

9000X AFD User Manual

Specifications and datasheets

Eaton Specification Sheet - SVX200A1-4A1N1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



Eaton.com/socialmedia