

# Eaton SVX040A1-5A4B1

Catalog number: SVX040A1-5A4B1

Eaton SVX adjustable frequency drive, 40HP, NEMA Type 1/IP21, 575V, FR7, Three-phase, EMC L, Standard Software, A/N keypad, Internal brake chopper, Standard boards



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton SVX adjustable frequency drive	SVX040A1-5A4B1
<b>UPC</b>	<b>Product Length/Depth</b>
782116929245	10.1 in
<b>Product Height</b>	<b>Product Width</b>
24.8 in	9.3 in
<b>Product Weight</b>	<b>Warranty</b>
77.2 lb	2 year
<b>Compliances</b>	<b>Certifications</b>
Contact Manufacturer	UL 508C IEC 61800-2 EN 61800-3 Level H

## defaultTaxonomyAttributeLabel

### Frame size

7

### Modification

Standard boards

### Input

EMC L

Three-phase

### Brake chopper

Brake chopper

### Horsepower

40 hp

### Keypad

Alphanumeric

### Rating

NEMA 1, IP21

### Software

Standard

### Voltage rating

575 V

## Resources

### Application notes

SPI - Variable frequency drives with a common DC bus

Connecting drives to generator supplies

Electromagnetic compatibility (EMC)

### Brochures

SVX9000 Adjustable Frequency Drives Brochure

SVX9000 Adjustable Frequency Drives Product Aid

### Catalogs

Product Range Catalog Drives Engineering

Eaton's Volume 6—Solid-State Motor Control

Product Datasheet - SVX040A1-5A4B1

### Drawings

SVX and SPX Series FR4-FR11 PDF Open Drawings

### Installation instructions

9000X AFD User Manual

### Specifications and datasheets

Eaton Specification Sheet - SVX040A1-5A4B1



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2022 Eaton  
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are  
property of their respective  
owners.



Eaton.com/socialmedia