

Eaton XTCE150G00A

Catalog number: XTCE150G00A

Eaton XT IEC contactor, 150A, 110 Vac 50 Hz, 120 Vac 60 Hz, ONO-ONC, 150A, Frame G, 90 mm, 50-60 Hz, 10, 25, 30/ 40, 60, 125, 125 hp (1/3PH @115, 200, 230/200, 230, 460, 575 V), Three-pole, Screw terminals, FVNR



General specifications

Product Name	Catalog Number
Eaton XT IEC contactor	XTCE150G00A
EAN	Product Length/Depth
4015082395872	6.2992126 in
Product Height	Product Width
6.69291339 in	4.37007874 in
Product Weight	Compliances
.5070632 lb	CE Marked RoHS Compliant
Certifications	Catalog Notes
UL Listed CSA Certified IEC 60947 EN 60947	Screw terminals (6-65A); 5 mm (80-150A); no lugs (185-2000A)

defaultTaxonomyAttributeLabel

Frame size

90 mm

Contact configuration

0 NO, 0 NC

Coil voltage

110-120 Vac, 50/60 Hz

Series

XT IEC

Type

Full voltage non-reversing contactor

HP rating - max

10, 25, 30/ 40, 60, 125, 125 hp (1/3PH
@115,200,230/200,230,460,575 V)

Continuous ampere rating

150 A

Frequency rating

50-60 Hz

Terminals

Screw terminals

Operation

Non-reversing

Amperage Rating

150A

Number Of Poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[XTCE_G 3D Inventor](#)

[XTCE_G AutoCAD 2D Footprint](#)

[XTCE_G 2D Drawing Xchange](#)

[XTCE_G 2D PDF](#)

[XTCE_G 3D Model Xchange](#)

Specifications and datasheets

[Global Data Sheet - XTCE150G00A](#)

[Eaton Specification Sheet - XTCE150G00A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2022 Eaton
All Rights Reserved

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)