

# Technical Information Bulletin

## CHOICE LED Lamps



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION


Order code: 66284  
Description: P20/8W/40K/40/CHOICE/STD  
UPC: 669549662841  
Case quantity: 12

### PERFORMANCE DATA

Shape: PAR20  
Base: E26  
Watts(W): 8  
Volts (VAC): 120  
Colour temperature (K)\*\*: 4 000  
Life L70 (hrs): 15 000  
Initial lumens (lm)\*: 652  
Initial lumens per watt (lm/W): 82  
CRI: 94  
Beam angle (°): 40  
CBCP: 914  
Power factor: 0.90  
Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)  
Traditional equivalent (W): 50

\*Initial lumens range: +/- 10 %

\*\*Typical colour temperature range: +/- 10 %



### COMPATIBLE DIMMERS

Lutron PD5NE, RRD6NA, DVRP253, SELV-300P



### CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit [www.standardpro.com](http://www.standardpro.com).

| Qty | Description | Price |
|-----|-------------|-------|
|     |             |       |

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
Company: \_\_\_\_\_  
Signature: \_\_\_\_\_

Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
Data is based upon tests performed in a controlled environment and representative of relative performance.  
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

September 30, 2019