



BE1 Series  
125 A 600 V; king size

- Product specifications**
- Conductor range: 6–1/0 AWG
  - Aluminum tunnel type connectors for both load and line sides
  - For overhead, underground and combination overhead/underground
  - Supplied with screw type ring

- Weatherproof Type 3R enclosure
- Primarily used in all provinces

Note: Supply from an underground network often requires use of stud type connector. Consult your local utility.



	Cat. no.	Description	Dimensions (in.)			Weight each	
			H	W	D	lb	kg
	<b>4 Jaw</b>						
	BE1-V	Overhead, hub opening	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-INV	Overhead, hub opening, comes with insulated neutral	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-1 1/4V	Overhead, hub opening, comes with 1 <sup>1</sup> / <sub>4</sub> in. hub	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-1 1/4INV	Overhead, hub opening comes with 1 <sup>1</sup> / <sub>4</sub> " hub and insulated neutral	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-1 1/2V	Overhead, hub opening, comes with 1 <sup>1</sup> / <sub>2</sub> in. hub	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-TV	Underground	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-INTV	Underground comes with insulated neutral	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-TCV	Combination overhead-underground	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-TCV-CR	Combination overhead-underground, corrosion resistant	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE1-INTCV	Combination overhead-underground comes with insulated neutral	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE11-V-CM	Overhead, twin hub opening	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE11-1 1/4V	Overhead, twin hub opening comes with 1 <sup>1</sup> / <sub>4</sub> in. hubs	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	BE11 1/4INV	Overhead, twin hub opening comes with 1 <sup>1</sup> / <sub>4</sub> in. hubs and insulated neutral	14 <sup>9</sup> / <sub>16</sub>	8 <sup>3</sup> / <sub>4</sub>	4 <sup>3</sup> / <sub>16</sub>	8	3.6
	<b>Factory-installed accessories</b>						
	Include: -5	5 <sup>th</sup> jaw, standard capacity, 9 o'clock position					
	-9	5 <sup>th</sup> jaw, full capacity, 9 o'clock position					
	-IN	Insulated neutral					

Diagrams

