

# Technical Information Bulletin

## CHOICE LED Lamps



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 66287  
Description: P30L/12W/30K/25/CHOICE/STD  
UPC: 69549662872  
Case quantity: 6



### PERFORMANCE DATA

Shape: PAR30LN  
Base: E26  
Watts(W): 12  
Volts (VAC): 120  
Colour temperature (K)\*\*: 3 000  
Life L70 (hrs): 15 000  
Initial lumens (lm)\*: 974  
Initial lumens per watt (lm/W): 81  
CRI: 92  
Beam angle (°): 25  
CBCP: 4 178  
Power factor: 0.92  
Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)  
Traditional equivalent (W): 75

\*Initial lumens range: +/- 10 %

\*\*Typical colour temperature range: +/- 10 %

### COMPATIBLE DIMMERS

|         |   |
|---------|---|
| Legrand | HCL453P, RH703PTUTC   |
| Cooper  | AAL06, DAL06P, SLC03P   |
| Leviton | 6615, 6674, DSL06-1LZ, DSM10-1LZ, IPE04-1LZ, IPL06                                    |
| Lutron  | AYCL-253P, CTCL-153P, DVCL-153P, DVCL-253P, DVELV-300P, MACL-153P, PD-6WCL, SELV-300P |



### CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in wet locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit [www.standardpro.com](http://www.standardpro.com).

| Qty | Description | Price |
|-----|-------------|-------|
|     |             |       |

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
Company: \_\_\_\_\_  
Signature: \_\_\_\_\_

Date: \_\_\_\_\_

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.  
Data is based upon tests performed in a controlled environment and representative of relative performance.  
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

August 19, 2019