

Technical Information Bulletin


CHOICE LED Lamps



Date: _____ Name of distributor: _____
 In hands date of project: _____ Client #: _____
 Project name/Number: _____ Name of end user: _____

ORDERING INFORMATION

Order code: 66297
 Description: P38/16.5W/27K/25/CHOICE/STD
 UPC: 69549662971
 Case quantity: 6



PERFORMANCE DATA

Shape: PAR38
 Base: E26
 Watts(W): 16.5
 Volts (VAC): 120
 Colour temperature (K)**: 2 700
 Life L70 (hrs): 15 000
 Initial lumens (lm)*: 1 360
 Initial lumens per watt (lm/W): 82
 CRI: 93
 Beam angle (°): 25
 CBCP: 6 067
 Power factor: 0.9
 Operating temperature range: -20 °C to 40 °C (-4 °F to 104 °F)
 Traditional equivalent (W): 100

COMPATIBLE DIMMERS

Legrand	HCL453P, RH703PTUTC
Cooper	AAL06, DAL06P, SLC03P
Leviton	6615, 6674, DSL06-1LZ, IPE04-1LZ, IPL06
Lutron	AYCL-253P, CTCL-153P, DVCL-153P, DVCL-253P, DVELV-300P, MACL-153P, PD-6WCL, SELV-300P

*Initial lumens range: +/- 10 % **Typical colour temperature range: +/- 10 %



CAUTIONS

- Turn power off before inspection, installation, or removal.
- Not for use in totally enclosed luminaires.
- Suitable for use in wet locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____ Date: _____

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.
 Data is based upon tests performed in a controlled environment and representative of relative performance.
 Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.