

Project:		Type:	
,			
Drawn by:	Catalogue #:	Date:	

Individual Spec Sheet

FLUO LED

LED UNDERCABINET LUMINAIRE

Slim Bar

ORDERING INFORMATION

Order code: 67254

Model number: UCFL/24IN/120V/10W/40K/FR/WH/STD

UPC: 069549672543

Case quantity:

PHYSICAL DATA

Dimensions: 24" (610 mm) Lens Type: Frosted

Frame Material: Aluminum housing

Frame finish: White Mounting: Surface

Daisy chain installation: 30 units (300 W) can be installed in row

PERFORMANCE DATA

Watts (W): 10 Volts (VAC): 120 4 000 Colour temperature (K)1: 730 Lumen output (lm)2: Lumen per Watts (Im/W): 73 CRI: 90 Life L70 (h)3: 35 000 Beam angle (°): 120 THD (%): 15 **Power factor:** 0.95

Dimming: Forward and Reverse

Operating temp. range: -20 °C to 40 °C (-4 °F to 104 °F)

ACCESSORIES (order separately)

Order code	Model number	Type
67787	UC/HARDWIREBOX/120V/STD	Hardwire Box
67202	UCS/PLUG/120V/STD	120 V Power Cord Plug
67203	UCS/JUMPER/6IN/STD	6" Jumper
67204	UCS/JUMPER/24IN/STD	24" Jumper
67205	UCS/JUMPER/36IN/STD	36" Jumper

COMPATIBLE DIMMERS

Brand	Model number		
LEGRAND	PD-5NE, RH703PTUTC		
LUTRON	PD-6WCL, DVCL-153P, CTCL-153P, DVCL-253P, AYCL-253P, DVRP-253P-WH, SELV-300P, MACL-153P		
COOPER	RRD-6NA-WH, AAL06, SCL03P		
LEVITON	6615, IPL06, 6674, DSL06-1LZ, DSM10-1LZ, IPE04-1LZ, DDMX1		

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Stanpro recommends to use dimmers designed to work with LED products. Older dimmers designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.

Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

This lighting equipment complies with Canadian standard ICES-005 for use in residential applications







quick
















¹ Typical colour temperature range: +/- 5 %.
² Lumen values are derived from Energy Star reported data. Initial lumens range: +/- 10 %.
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations.




DIMENSIONS



PHOTOMETRIC DATA¹

67254 • UCFL/24IN/120V/10W/30K/FR/WH/STD • 857.9 lm


Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	176.3	20.6%
0-40	291.7	34%
0-60	535.5	62.4%
60-90	247.5	28.8%
70-100	178.4	20.8%
90-120	66.4	7.7%
0-90	783.0	91.3%
90-180	74.9	8.7%
0-180	857.9	100%

Illuminance at a distance



Oty Description Price

I accept the specifications of the luminaire configuration mentioned above.

Name:
Company:
Signature:
Date:

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.



¹ Complete IES files available on our website.