



# LED Reflector

Allowing you to focus light where it matters, these LED reflectors will not let your colors fade. Choose from many sizes, color temperatures and beam distributions to create the perfect lighting with consistent lamp to lamp color.

Reduce energy consumption and protect all goods and materials that are sensitive to heat and UV emissions.

STANDARD's LED reflectors are ideal for tracks, recessed luminaires and accent lighting in residential, retail, hospitality and commercial applications.



MR11



MR16  
S2



GU10



GU10  
S2

Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (master)
<b>MR11</b>												
64244 <sup>1</sup>	LED/MR11/4W/30K/38/GU4/ND/STD	4	GU4	12	3 000	80	25 000	260	38	550	30	48
<b>MR16</b>												
68263	MR16/S2/7.5W/27K/25/STD	7.5	MR16	12	2 700	90	54 000	570	25	3 196	75	60
68259	MR16/S2/7.5W/27K/35/STD	7.5	GU5.3	12	2 700	90	50 000	570	35	1 908	75	60
68264	MR16/S2/7.5W/30K/25/STD	7.5	GU5.3	12	3 000	90	54 000	570	25	3 268	50	60
68260	MR16/S2/7.5W/30K/35/STD	7.5	GU5.3	12	3 000	90	50 000	570	35	1 905	75	60
68265	MR16/S2/7.5W/40K/25/STD	7.5	GU5.3	12	4 000	90	50 000	570	25	3 613	75	60
68261	MR16/S2/7.5W/40K/35/STD	7.5	GU5.3	12	4 000	90	50 000	570	35	2 066	75	60
68262	MR16/S2/7.5W/50K/35/STD	7.5	GU5.3	12	5 000	90	54 000	570	35	2 020	50	60
<b>GU10</b>												
68252	GU10/S2/6.5W/27K/25/STD	6.5	GU10	120	2 700	90	54 000	570	25	1 975	75	60
68255	GU10/S2/6.5W/27K/35/STD	6.5	GU10	120	2 700	90	54 000	570	35	1 231	75	60
64416 <sup>1</sup>	LED/GU10/6.5W/30K/25/STD	6.5	GU10	120	3 000	83	40 000	574	25	2 504	50	24
68256	GU10/S2/6.5W/30K/35/STD	6.5	GU10	120	3 000	90	54 000	570	35	1 996	50	60
68254	GU10/S2/6.5W/40K/25/STD	6.5	GU10	120	4 000	90	54 000	570	25	1 975	50	60
68257	GU10/S2/6.5W/40K/35/STD	6.5	GU10	120	4 000	90	54 000	570	35	1 231	50	60
68258	GU10/S2/6.5W/50K/35/STD	6.5	GU10	120	5 000	90	54 000	570	35	1 231	50	60

Lumen values are derived from photometric testing  
For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit [www.standardpro.com](http://www.standardpro.com)





Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (master)
<b>PAR16</b>												
63990	LED/P16/6.5W/30K/38/STD	6.5	E26	120	3 000	82	40 000	582	38	1 242	50	24
63991	LED/P16/6.5W/40K/38/STD	6.5	E26	120	4 000	83	40 000	635	38	1 298	50	24
<b>PAR20</b>												
68218	P20/S2/7W/27K/25/STD	7	E26	120	2 700	90	54 000	550	25	3 422	50	12
68219	P20/S2/7W/27K/40/STD	7	E26	120	2 700	92	54 000	550	40	1 253	50	12
68220	P20/S2/7W/30K/25/STD	7	E26	120	3 000	90	54 000	550	25	3 572	50	12
68221	P20/S2/7W/30K/40/STD	7	E26	120	3 000	90	54 000	550	40	1 303	50	12
65380 <sup>2</sup>	LED/P20HO/7W/30K/35/STD	7	E26	120	3 000	82	25 000	660	35	1 374	-	50
68222	P20/S2/7W/40K/25/STD	7	E26	120	4 000	90	54 000	550	25	3 829	50	12
68224	P20/S2/7W/40K/40/STD	7	E26	120	4 000	90	54 000	550	40	1 358	50	12
68225	P20/S2/7W/50K/25/STD	7	E26	120	5 000	90	54 000	550	25	2 350	50	12
68226	P20/S2/7W/50K/40/STD	7	E26	120	5 000	90	54 000	550	40	1 257	50	12
<b>PAR30SN</b>												
68227	P30S/S2/12W/27K/25/STD	10	E26	120	2 700	90	54 000	1 050	25	4 981	75	6
68228	P30S/S2/12W/27K/40/STD	12	E26	120	2 700	90	50 000	1 050	40	2 337	75	6
63970 <sup>1</sup>	LED/P30S/10W/30K/25/STD	10	E26	120	3 000	94	40 000	830	25	2 174	75	6
68230	P30S/S2/12W/30K/40/STD	10	E26	120	3 000	90	54 000	1 050	40	2 470	75	6
63973 <sup>1</sup>	LED/P30S/10W/40K/25/STD	10	E26	120	4 000	94	40 000	904	25	2 587	75	6
68232	P30S/S2/12W/40K/40/STD	12	E26	120	4 000	90	50 000	1 050	40	2 711	75	6
63975 <sup>1</sup>	LED/P30S/10W/50K/25/STD	10	E26	120	5 000	96	40 000	865	25	2 477	75	6
63976 <sup>1</sup>	LED/P30S/10W/50K/40/STD	10	E26	120	5 000	96	40 000	865	40	1 607	75	6

Lumen values are derived from photometric testing  
 For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit [www.standardpro.com](http://www.standardpro.com)  
<sup>1</sup> Not Energy Star  
<sup>2</sup> Consult factory for availability





Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (inner/master)
<b>PAR30LN</b>												
68235	P30L/S2/12W/27K/25/STD	12	E26	120	2 700	90	50 000	1 050	25	5 240	75	6
68236	P30L/S2/12W/27K/40/STD	12	E26	120	2 700	90	54 000	1 050	40	2 117	75	6
68237	P30L/S2/12W/30K/25/STD	12	E26	120	3 000	90	54 000	1 050	25	5 137	75	6
68238	P30L/S2/12W/30K/40/STD	12	E26	120	3 000	90	50 000	1 050	40	2 639	75	6
68239	P30L/S2/12W/40K/25/STD	10	E26	120	4 000	90	54 000	1 050	25	5 359	75	6
68240	P30L/S2/12W/40K/40/STD	12	E26	120	4 000	90	54 000	1 050	40	2 767	75	6
68241	P30L/S2/12W/50K/25/STD	10	E26	120	5 000	90	54 000	1 050	25	5 473	75	6
68242	P30L/S2/12W/50K/40/STD	10	E26	120	5 000	90	54 000	1 050	40	2 471	75	6
<b>PAR38</b>												
68243	P38/S2/16.5W/27K/25/STD	15	E26	120	2 700	90	54 000	1 370	25	7 056	100	1/6
68244	P38/S2/16.5W/27K/40/STD	16.5	E26	120	2 700	90	50 000	1 370	40	2 783	120	1/6
68245	P38/S2/16.5W/30K/25/STD	16.5	E26	120	3 000	90	50 000	1 370	25	7 354	120	1/6
68246	P38/S2/16.5W/30K/40/STD	16.5	E26	120	3 000	90	50 000	1 370	40	3 127	120	1/6
68247	P38/S2/16.5W/40K/25/STD	16.5	E26	120	4 000	90	50 000	1 370	25	6 800	120	1/6
68249	P38/S2/16.5W/40K/40/STD	16.5	E26	120	4 000	90	54 000	1 370	40	3 237	120	1/6
68250	P38/S2/16.5W/50K/25/STD	16.5	E26	120	5 000	90	54 000	1 370	25	6 800	120	1/6
68251	P38/S2/16.5W/50K/40/STD	16.5	E26	120	5 000	90	50 000	1 370	40	2 842	120	1/6

Lumen values are derived from photometric testing  
 For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit [www.standardpro.com](http://www.standardpro.com)  
<sup>2</sup> Not Energy Star  
<sup>3</sup> Consult factory for availability





Order code	Description	Watts (W)	Base	Volts (VAC)	Color temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Case qty (inner/master)
<b>PAR38HO</b>												
67909	P38HO/27W/30K/40/120-277/STD	27	E26	120-277	3 000	80	50 000	3 000	40	3 272	250	1/6
67910	P38HO/27W/35K/40/120-277/STD	27	E26	120-277	3 500	80	50 000	3 000	40	3 272	250	1/6
<b>R20</b>												
64964 <sup>2</sup>	LED/R20/S2/6.5W/27K/STD	6.5	E26	120	2 700	83	25 000	525	107	180	50	6/24
<b>BR30</b>												
64965 <sup>2</sup>	LED/BR30/S2/8W/27K/STD	8	E26	120	2 700	84	25 000	650	105	220	65	6/24
64966 <sup>2</sup>	LED/BR30/S2/8W/40K/STD	8	E26	120	4 000	82	25 000	700	105	240	65	6/24
<b>BR40</b>												
66032 <sup>2</sup>	LED/BR40/S2/16.5W/27K/STD	16.5	E26	120	2 700	82	25 000	1 252	103	445	85	6/24

Lumen values are derived from photometric testing  
 For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit [www.standardpro.com](http://www.standardpro.com)

