

Wire connector TA1.1 8 AWG...3/0 with control wire voltage tap-off 3 units accessories for: 3VA4/5 125



Model	
product brand name	SETRON
product designation	accessories
Product version	circular conductor terminal voltage tap 3 units
Accessories	Wire connector
General technical data	
designation / of the terminal	TA1.1
type of electrical connection / with control wire tap	Yes
Connections according IEC	
connectable conductor cross-section	
• for copper cable / stranded / minimum	10 mm ²
• for copper cable / stranded / maximum	95 mm ²
• for aluminum cable / solid / minimum	10 mm ²
• for aluminum cable / solid / maximum	16 mm ²
• for aluminum cable / stranded / minimum	10 mm ²
• for aluminum cable / stranded / maximum	95 mm ²
stripped length	12,2 mm
tightening torque / when using copper cables	
• solid	10 mm ² : 6.2 Nm 16 - 95 mm ² : 11.3 Nm
• stranded	10 mm ² : 6.2 Nm 16 - 95 mm ² : 11.3 Nm
• finely stranded	10 mm ² : 6.2 Nm 16 - 95 mm ² : 11.3 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	0.48 in
connectable conductor cross-section	
• for copper cable / stranded / minimum	8 AWG
• for copper cable / stranded / maximum	3/0 AWG
• for copper cable / finely stranded / minimum	8 AWG
• for copper cable / finely stranded / maximum	3/0 AWG
• for aluminum cable / stranded / minimum	12 AWG
• for aluminum cable / stranded / maximum	3/0 AWG
tightening torque / when using copper cables	
• solid	8 AWG: 55 lb-in 6 - 3/0 AWG: 100 lb-in
• stranded	8 AWG: 55 lb-in 6 - 3/0 AWG: 100 lb-in
• finely stranded	8 AWG: 55 lb-in 6 - 3/0 AWG: 100 lb-in
Further information	
Information- and Downloadcenter (Catalogs, Brochures,...)	
http://www.siemens.com/lowvoltage/catalogs	
Industry Mall (Online ordering system)	

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=3VA9133-0JG11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JG11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3VA9133-0JG11

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/19/2022 

