THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT		UD ZE	DIMENSIONS in. [mm]				
PART #	ENGLISH	METRIC	L± .03 [0,8]	W± .01 [0,3]	C± .02 [0,5]	M± .03 [8,0]	H± .01 [0,3]
PMNF1-3F*	-	M3	.83 [21,1]	.23 [5,8]	.20 [5,1]	.69 [17,5]	.13 [3,3]
PNF18-6F	#6	M3,5	.80 [20,3]	.30 [7,6]	.22 [5,6]	.66 [16,8]	.15 [3,8]
PNF18-8F	#8	M4	.86 [21,8]	.31 [7,9]	.25 [6,4]	.69 [17,5]	.17 [4,3]
PNF18-10F	#10		.87 [22,1]	.34 [8,6]	.26 [6,6]	.71 [18,0]	.20 [5,1]
PMNF1-5F*		M5	.90 [22,9]	.35 [8,9]	.25 [6,4]	.74 [18,8]	.21 [5,3]
PNF18-14F	1/4"	M6	1.05 [26,7]	.44 [11,2]	.35 [8,9]	.80 [20,3]	.27 [6,9]

* NOT UL LISTED OR CSA CERTIFIED

NOTES:

B

1. USED FOR:

A. #22-18 AWG [0,5-1,0 mm²] STRANDED COPPER WIRE B. 221 °F [105 °C] MAX. OPERATING TEMPERATURE

C. 600V. MAX. BLDG WIRE

(1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
2. INSTALLATION TOOLS:

A. UL APPROVED: CT-100A, CT-1550, CT-1551
B. PANDUIT APPROVED: CT-160, CT-260, CT-400, CT-460, CT-600A (CT-550CH), CT-2500 (CT-2550CH)

3. WIRE STRIP LENGTH: 7/32" 1/32 [5,6 10,8]

4. MATERIAL:

A. STAMPING: .03" [0,8] THK COPPER, TIN PLATED


B. HOUSING: NYLON, RED

C. SLEEVE: BRASS, TIN PLATED

5. SEE www.panduit.com FOR PACKAGE QUANTITIES

INDICATED BY PART NUMBER SUFFIX

6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



HDIA



LISTED 587H E52164



CERTIFIED LR31212

							FORK, NYLON (FUNNEL) INSULATED #22-18		
							CUSTOMER DRAWING		
							ITEM REVISION NAME N41260BA/09	DANBUIT	
							DATASET FILE NAME N41260BA_DC/09A	PANDUIT	
09	12.12.13	JHNU	JHNU		REVISED NOTE 2B: CT-550CH WAS CT-520CH, CT-2550CH WAS CT-2525	A41260	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]	MATERIAL:	
08	11.26.13	JHNU	TMR		INDICATED PART NUMBERS WHICH ARE NOT UL LISTED/CSA CERTIFIED	A41260	.x : .1 [2.54] .xx : .005 [.13] .xx : .01 [.25] ANGLES : 5 *	SEE NOTES	
07	09.19.12	JBN	LCA		ADDED METRIC EQUIVALENT. REVISED NOTES. UPDATED TO CURRENT STANDARDS	A41260	THIRD ANGLE PROJECTION	DRAWING NUMBER: A41260	
REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DRAWN BY DATE CHK SCALE DAW - LA N.T.S.	SHT 1 0F 1	