

# **FEATURES & SPECIFICATIONS**

**INTENDED USE** — RT8S is designed for applications that require the extremely energy efficient delivery of comfortable volumetric light from a lay-in fixture that is appealing and shallow in depth and where room-side ballast access is required. Ideal for offices, schools, hospitals and numerous other commercial applications. **Certain airborne contaminants can diminish integrity of acrylic.** <u>Click here for Acrylic Environmental Compatibility table for suitable uses.</u>

**CONSTRUCTION** — Rugged, steel reflector with embossed facets. Painted after fabrication.

Fixtures may be mounted end-to-end.

**OPTICS** — Delivers volumetric lighting by filling the entire volume of space with light, providing the ideal amount to walls, cubicles, work surfaces and people.

Luminous characteristics are carefully managed at high angles, distributing just enough intensity to deliver the volumetric effect.

98% reflective Alanod MIRO° silver optical assembly efficiently redirects lamp output to the refractor.

Regressed refractive system obscures and softens the lamp and smoothly washes the reflector with light.

Linear faceted reflector softens and distributes light into the space and minimizes the luminance ratio between the fixture and the ceiling.

 $Mechanical \ cut-off across the \ reflector \ and \ fresnel \ refraction \ along \ the \ refractor \ provide \ high \ angle \ shielding \ and \ a \ quiet \ ceiling.$ 

Sloped endplates provide a balanced fixture to ceiling ratio while enhancing the perception of fixture depth.

**ELECTRICAL** — High-efficiency, CEE qualified, instant-start,  $\leq$  10% THD, universal voltage and sound rated A are available as quick-ship items.

Optional program-start and step-dimming ballasts available.

Designed and optimized for use with CEE (Consortium for Energy Efficiency) qualified, high-lumen, long life T8 lamps and energy-efficient electronic ballasts.

**INSTALLATION** — Lamps accessed by unlatching trim and allowing it to hinge open for easy maintenance. Ballast is accessed from below by removing channel cover.

**LISTINGS** — UL Listed to US and Canadian standards.

**WARRANTY** — 1-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Protected by one or more of US Patents Nos. 7,229,192; D541,467; D541,468; D544,633; D544,634; D544,992; D544,933 and additional patent pending.

**NOTE**: Actual performance may differ as a result of end-user environment and application. Specifications subject to change without notice.

Catalog Number

Notes


Type



# **2RT8S**



2 X 4 2 Lamps T8



Example: 2RT8S 2 32 MVOLT BINP L835HT8

All dimensions are inches (centimeters) unless otherwise specified.

### ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

2RT8S		2	32							
Series	Trim type	Number of lamps	Wattage	Voltage	Ballast		Lamp		Options	
2RT8S	<b>(blank)</b> Lay-in grid F Overlapping flanged	2	<b>32</b> 32W T8 (48")	MVOLT <sup>1</sup> 347	BILP BINP GEB10IS BIHP BSNP	IS, high efficiency, .78 bf (low) <sup>2</sup> IS, high efficiency, .88 bf (normal) <sup>2</sup> IS, .88 ballast factor IS, high efficiency, 120 bf (high) <sup>2</sup> PS, step-dimming, high efficiency, .88 bf (normal) <sup>2,3</sup>	LP835	3500K	GLR EL <b>EL14</b> PWS1836 PWS1846 QFC_	Fast-blow fuse <sup>4</sup> 500 nominal lumen battery pack (Noncompliant with CA T20) 1400 nominal lumen battery pack (Noncompliant with CAT20) 6' prewire, 3/8" diameter, 18 gauge, 3-wires <sup>2</sup> 6' prewire, 3/8" diameter, 18 gauge, 4-wires <sup>6</sup> Quick-flex fixture cable, factory installed prewired cable (RELOC®) <sup>4</sup>


### Notes


- 1 MVOLT standard for 120V-277V applications.
- 2 CEE qualified HPT8.
- 3 Not available with 347 volt.
- 4 Must specify voltage, 120 or 277.
- 5 For use with standard ballast.
- 6 For use with step-dimming ballast.

COMMERCIAL INDOOR 2RT8S\_2X4

## **MOUNTING DATA**

Continuous row mounting of flanged units requires CRE and CRM trim options (see Options).






T8 Energy Comparison									
System	Lamp Type	Ballast Factor	Input Watts	Watts Saved Compared to 3 lamp T8					
3-lamp T8 Parabolic	F32T8	0.88	85	-					
2RT8B 2-lamp BINP T8	F32T8	0.88	55	30					
2RT8B 2-lamp BILP T8	F32T8	0.78	48	37					

Recommended rough-in dimensions for F-trim fixtures 24"x48" (Tolerance is +1/4"-0"). Swing-gate range 1-3/16" to 3-15/16". Swing-gate span 23-3/8" to 26-11/16". Fixture swing-gate points require additional 1-1/16" over nominal fixture height.

# **PHOTOMETRICS**

2RT8S 2 32, FO32 lamps, 2800 lumens per lamp, s/m 1.28 (along) 1.4 (across), test no. LTL18481



<sup>\*</sup>The LER (Luminaire Efficacy Rating) is the lumens per watt rating for this fixture. It is used to compare the energy efficiency of various products. This photometric report is based upon IES testing procedures, as stated in LM-41-1998.