
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	PANDUIT PART #	TAB SIZE	WIRE RANGE			DIMENSIONS in. [mm]			
			ENGLISH AWG	METRIC mm²	COLOR	MAX. WIRE INSUL. DIA.	L ± (0,8)	W ± .01 [0,3]	H± (0,3)
DNF18	8–187	.187 X .032 [4,8 X 0,8]	22–18	0,5-1,0	RED	.14 [3,5]	.76 [19,3]	.23 [5,8]	.10 [2,5]
DNF1	4–187		16-14	1,5-2,5	BLUE	.16 [4,1]			

NOTES:

В

- 1. USED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 194°F [90°C] MAX. OPERATING TEMPERATURE C. 300 V. MAX. VOLTAGE RATING
- 2. MATERIAL:
 - A. STAMPING: .016 [0,41] TIN PLATED BRASS
 - B. SLEEVE: BRASS, TIN PLATED
 - C. HOUSING: NYLON
- 3. INSTALLATION TOOLS:
 - A. UL LISTED AND CSA CERTIFIED: CT-600-A (CT-570CH), CT-1550, CT-1551, CT-2500 (CT-2550CH)
 - B. PANDUIT APPROVED: CT-100A, CT-160, CT-260
- 4. WIRE STRIP LENGTH: 9/32 +1/32 [7,1 +0,8]
- 5. SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- 6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- 7. FIRST INSERTION FORCE: 12 Lb [53 N] MAXIMUM FIRST WITHDRAWAL FORCE: 12 Lb [53 N] MAXIMUM 6 Lb [27 N] MINIMUM





CERTIFIED

LR31212

20H3 E78522

							2,0022	- 1	
							FEMALE DISCONNECTS, NYLON FUNNEL INSULATED		
							CUSTOMER DRAWING		
							N41312BA/07 DATASET FILE NAME PANDLIT		
							N41312BA_DC/U/A		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] SEE NOTES		
							.xx ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		
07	10.19.12	JBN	LCA	VMB	ADDED METRIC EQUIVALENTS UPDATED DRAWING TO CURRENT STANDARDS	A41312	THIRD ANGLE PROJECTION A41312		
REV	DATE	BY	СНК	APR	DESCRIPTION	ECN	DAW - CHK SCALE N.T.S. SHT 1 0F 1		

D10100DA/15

2