

HID Lamps



Order code	Description	Watts (W)	Base	Shape	Colour temp. (K)	ANSI code	CRI	Life L70 (hrs)	Lumen output (lm)	Mean lumens (lm)	Burn pos.	Finish	Luminaire	Case qty (master)
Pulse Start														
58514	MH70W/C/U/PS/ELUME	70	E26	BD17	3 700	M98	70	15 000	5 300	3 400	U	Coated	E	24
58517	MH100W/C/U/PS/ELUME	100	E26	BD17	3 700	M90	70	15 000	8 500	5 500	U	Coated	E	24
58521	MP150/U/UVS/PS/740/ELUME	150	E26	EDX17	4 000	M102	65	15 000	13 300	10 000	U	Clear	O	24

E = Enclosed O = Open

Fluorescent Lamps



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS 3-12 hrs ²	Lumen output (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty (master)
T8 Preheat Start											
56514 ¹	F15T8/CW/PH/G13/ELUME	15	Med Bipin	4 100	62	6 000-7 500	610	573	18 457	41	48
56515 ¹	F15T8/DL/PH/G13/ELUME	15	Med Bipin	6 500	72	6 000-7 500	560	526	18 457	37	48

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS 3-12 hrs ²	Rated life PS/PRS 3-12 hrs ²	Lumen output (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty (master)
T8 800 Series - Rapid Start												
62513 ¹	F32T8/35K/8/RS/G13/ELUME/BULK	32	Med Bipin	3 500	85	24 000-30 000	40 000-42 000	3 050	2 900	48 1 220	95	25
62514 ¹	F32T8/41K/8/RS/G13/ELUME/BULK	32	Med Bipin	4 100	85	24 000-30 000	40 000-42 000	3 000	2 850	48 1 220	94	25
62515 ¹	F32T8/50K/8/RS/G13/ELUME/BULK	32	Med Bipin	5 000	85	24 000-30 000	40 000-42 000	2 950	2 800	48 1 220	92	25
62516 ¹	F32T8/65K/8/RS/G13/ELUME/BULK	32	Med Bipin	6 500	85	24 000-30 000	40 000-42 000	2 900	2 750	48 1 220	91	25

¹TCLP compliant
²Based on a 3 hour and 12 hour start
 IS=Instant Start ballast PS=Program Start ballast PRS=Program Rapid Start ballast



Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS 3-12 hrs ²	Lumen output (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty (master)	
T5 Preheat Start												
56509	F4T5/CW/PH/G5/ELUME	4	Min Bipin	4 100	62	5 000-6 000	120	113	6 152	40	48	
56510	F6T5/CW/PH/G5/ELUME	6	Min Bipin	4 100	62	6 000-7 500	240	225	9 229	40	48	
56511	F6T5/DL/PH/G5/ELUME	6	Min Bipin	6 500	62	6 000-7 500	210	197	9 229	35	48	
56512	F8T5/CW/PH/G5/ELUME	8	Min Bipin	4 100	62	6 000-7 500	350	329	12 305	44	48	
56513	F8T5/DL/PH/G5/ELUME	8	Min Bipin	6 500	62	6 000-7 500	310	291	12 305	39	48	
56518	F13T5/WW/PH/G5/ELUME	13	Min Bipin	3 000	62	6 000-7 500	800	752	21 530	62	48	
57392	F13T5/CW/PH/G5/ELUME	13	Min Bipin	4 100	62	6 000-7 500	740	695	21 530	57	48	

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life PS/PRS 3-12 hrs ²	Lumen output (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty (master)	
T5 Program Start												
59187 ¹	F14T5/35K/8/PS/G5/ELUME	14	Min Bipin	3 500	85	24 000-30 000	1 350	1 280	22 559	96	25	
59188 ¹	F14T5/41K/8/PS/G5/ELUME	14	Min Bipin	4 100	85	24 000-30 000	1 350	1 280	22 559	96	25	
59189 ¹	F14T5/50K/8/PS/G5/ELUME	14	Min Bipin	5 000	85	24 000-30 000	1 300	1 230	22 559	93	25	
59190 ¹	F21T5/35K/8/PS/G5/ELUME	21	Min Bipin	3 500	85	24 000-30 000	2 100	2 000	34 864	100	25	
59191 ¹	F21T5/41K/8/PS/G5/ELUME	21	Min Bipin	4 100	85	24 000-30 000	2 100	2 000	34 864	100	25	
59192 ¹	F21T5/50K/8/PS/G5/ELUME	21	Min Bipin	5 000	85	24 000-30 000	2 100	2 000	34 864	100	25	
59196 ¹	F28T5/35K/8/PS/G5/ELUME	28	Min Bipin	3 500	85	24 000-30 000	2 900	2 750	46 1 168	104	25	
59197 ¹	F28T5/41K/8/PS/G5/ELUME	28	Min Bipin	4 100	85	24 000-30 000	2 900	2 750	46 1 168	104	25	
59198 ¹	F28T5/50K/8/PS/G5/ELUME	28	Min Bipin	5 000	85	24 000-30 000	2 750	2 610	46 1 168	98	25	

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life PS/PRS 3-12 hrs ²	Lumen output (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty (master)	
T5 HO Program Start												
59193 ¹	F24T5/35K/8/HO/PS/G5/ELUME	24	Min Bipin	3 500	85	24 000-30 000	2 000	1 900	22 559	83	25	
59194 ¹	F24T5/41K/8/HO/PS/G5/ELUME	24	Min Bipin	4 100	85	24 000-30 000	2 000	1 900	22 559	83	25	
59195 ¹	F24T5/50K/8/HO/PS/G5/ELUME	24	Min Bipin	5 000	85	24 000-30 000	1 900	1 805	22 559	79	25	
59199 ¹	F39T5/35K/8/HO/PS/G5/ELUME	39	Min Bipin	3 500	85	24 000-30 000	3 500	3 325	34 864	90	25	
59200 ¹	F39T5/41K/8/HO/PS/G5/ELUME	39	Min Bipin	4 100	85	24 000-30 000	3 500	3 325	34 864	90	25	
59201 ¹	F39T5/50K/8/HO/PS/G5/ELUME	39	Min Bipin	5 000	85	24 000-30 000	3 500	3 325	34 864	90	25	
65494	F54T5/35K/8/HO/PS/G5/ELUME	54	Min Bipin	3 500	85	35 000-40 000	5 000	4 651	46 1 168	83	25	
65495	F54T5/41K/8/HO/PS/G5/ELUME	54	Min Bipin	4 100	85	35 000-40 000	5 000	4 450	46 1 168	93	25	
65497	F54T5/50K/8/HO/PS/G5/ELUME	54	Min Bipin	5 000	85	35 000-40 000	4 900	4 465	46 1 168	77	25	



Ø 1 5/32" (29.5 mm)

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Life L70 (hrs)	Lumen output (lm)	Mean lumens (lm)	Nominal length (in.) (mm)	Efficacy (lm/W)	Case qty (master)	
CIRCLINE Rapid Start												
56516	FC8T9/CW/RS/4P/ELUME	22	Circline 4-Pin	4 100	60	12 000	1 150	1 095	9 229	52	24	
56517	FC12T9/CW/RS/4P/ELUME	32	Circline 4-Pin	4 100	85	12 000	1 570	1 495	12 305	49	24	

¹TCLP compliant

²Based on a 3 hour and 12 hour start

IS=Instant Start ballast

PS=Program Start ballast

PRS=Program Rapid Start ballast