

Project:		Type:
Drawn by:	Catalogue #:	Date:

# Individual Spec Sheet

# **GIMBAL LED MODULE**

# **ORDERING INFORMATION**

65421 Order code:

Model number: LED/DL/GIMBAL/MOD/7W/40K/WH/STD

UPC: 069549654211

Case quantity:

#### PHYSICAL DATA

**Dimensions:** 1 31/32" X 2 17/32" (50 mm X 64 mm)

Mounting: Recessed Module color: White Shape: Round

Clear Polycarbonate Lens type:

Cable rating:

# PERFORMANCE DATA

Watts (W): 7 Beam angle (°): 40 Colour temperature (K)1: 4 000 Lumen output (lm)2: 620 Lumen per Watts (Im/W): 89 Life L70 (h)3: 36 000 CRI: >80 **Traditional equivalent:** 50 W PAR20 IP rating: IP44

Dimmer type: Forward-Reverse phase Operating temperatures range: -20°C / -4°F to 45°C / 113°F

THD (%): <40 Power factor: >0.9 Frequency (Hz): 60

# **COMPATIBLE DIMMERS**

Brand	Model
COOPER	AAL06
LEVITON	6615, 6674, DSL06-1LZ, IPE04-1LZ, IPL06
LUTRON	AYCL -253P CTCL -153P DVCL -153P DVCL -253P DVELV-300P SELV-300P

NOTE: The above table shows dimmers that have been tested and have demonstrated proper operation under normal conditions. Each installation being unique, various factors such as load, common neutrals or other electrical products on the circuit can, in certain instances, cause variance in system performance. Read and comply to the dimmer installation instructions. Consult dimming system manufacturer for additional support in operation. Starpor recommends to use dimmers designed to rive or additional support in operation. Starpor recommends to use dimmers designed to rive roaddesses designed for incandescent products may cause erratic operation. Some dimmers may require more than one product for stable operation. The maximum number of products is determined by the dimmer wattage rating with LEDs. Be careful, these dimmers have different ratings depending on the product type. Again, refer to the dimmer installation instructions.























This lighting equipment complies with Canadian standard ICES-005 for use in residential applications Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.





<sup>&</sup>lt;sup>1</sup> Typical colour temperature range: +/- 5 % <sup>2</sup> Lumens values from Energy Star reported data

<sup>&</sup>lt;sup>3</sup> Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations



#### **DIMENSIONS**






#### **WARNINGS**

- This device is not intended for use with emergency fixtures or emergency exit lights.
- To avoid risk of electric shock, make sure to turn off main power switch prior to installation or maintenance.
- Do not open no user serviceable parts inside.
- Must be installed in compliance with Canadian Electrical Code in Canada or National Electrical Code (NEC) in the US.
- Make sure input voltage and frequency are compatible with the fixture. Check installation guide for power requirements prior to installation.

#### PHOTOMETRIC DATA<sup>1</sup>

# 65421 • LED/DL/GIMBAL/MOD/7W/40K/WH/STD • 701.2 Im


#### Polar candela distribution



# Zonal lumen summary

Zone	Lumens	% Fixture
0-30	539.0	76.9%
0-40	625.0	89.1%
0-60	681.7	97.2%
60-90	18.4	2.6%
70-100	6.3	0.9%
90-120	0.0	0%
0-90	700.1	99.8%
90-180	1.1	0.2%
0-180	701.2	100%

#### Illuminance at a distance



Qty	Description	Pri	ce
I accept the specifica Name:	ations of the luminaire configuration mentioned above.		
Company:			
Company: Signature:		Di	ate:

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.



<sup>&</sup>lt;sup>1</sup> Complete IES files available on our website.