

# Technical Information Bulletin

## LED Linear



Date: \_\_\_\_\_ Name of distributor: \_\_\_\_\_  
In hands date of project: \_\_\_\_\_ Client #: \_\_\_\_\_  
Project name/Number: \_\_\_\_\_ Name of end user: \_\_\_\_\_

### ORDERING INFORMATION

Order code: 66996  
Description: T5/13W/840/46/BYP/120-277/ND/STD  
UPC: 69549669963  
Case quantity: 25  
DLC Unique ID: PLK4HMWSOE0Y



Nominal length : 46 in. (1 168 mm) Dia. : 19/16 in. (21 mm)

### PHYSICAL DATA

Shape: T5  
Base: G5  
Material: Glass

### PERFORMANCE DATA

Install method: Ballast bypass  
Lamp Watts (W): 13  
Volts (VAC): 120 -277  
Colour temperature (K)<sup>1</sup>: 4 000  
Initial Lumens (lm)<sup>2</sup>: 1 650  
Initial lumens per watt (lm/W): 127  
Life L70 (hrs): 50 000  
CRI: 82  
Operating temperature range: -25°C to 45°F (-13°C to 113°F)

<sup>1</sup> Typical colour temperature range: +/- 5 %  
<sup>2</sup> Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %



\*This product complies with UL1598C Standard for LED luminaire Retrofit kits. Not suitable for hazardous location.

### ADDITIONAL INFORMATION

ONLY FOR BALLAST BYPASS INSTALLATION IN 120-277V APPLICATIONS. NOT FOR USE IN 347V DIRECT LINE VOLTAGE APPLICATIONS.  
Direct replacement for 28 watts lamps only.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: \_\_\_\_\_  
Company: \_\_\_\_\_  
Signature: \_\_\_\_\_ Date: \_\_\_\_\_

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

