



KSA2/0

by Burndy
Catalog ID: KSA2/0

Prop65

Aluminum Split Bolt, (Run, Tap):: Al-Al: 2/0 AWG (Str), 2/0 AWG (Str) , Al-Cu: 2 AWG (Str), 8 AWG (Str) , Cu-Cu: 2/0 AWG (Str), 8 AWG (Str), Tin Plated.

Features: No Scratch Brushing Required, No Oxide Inhibitor Required, Orients The Conductor, Provides Maximum Pressure And Assures A Secure Connection Of Run And Tap Conductors, Facilitates Piercing The Aluminum Conductor Surface Oxides, UL 486B Listed, 90 DEG C Rated, Provides A Low Contact Resistance, Provides Equal Coefficient Of Expansion Inhibits The Reformation Of Oxides By Producing A Gas-Tight Seal, Provides Improved Retention Of Minimum To Maximum Conductor Combinations, Installation Torque: 385 IN-LB, Conductor Type: Run: Commercial Stranded Aluminum, Commercial Stranded And Solid Copper, Tap: Commercial Stranded Aluminum, Commercial Stranded and Solid Copper, Cross Flats: 1.12 IN, Length: 1.92 IN, Width: 0.88 IN

Product Details

General

Application	For All Combinations of Aluminum to Aluminum, Aluminum to Copper and Copper to Copper, Aluminum Alloy Tin Plated
Hardware Type	7/8-14 UNF
Installation Torque Recommended in-lb	385 LBS/in
Material	Aluminum Alloy
Plated	Y
Plating Type	Tin
Sub Brand	TRITAP, SERVIT
Temperature Rating	194
Trade Name	TRITAP™ SERVIT®
Type	KSA
UPC	781810153505
UPC 12 Digit	7818101535055

Dimensions

Dimension - B Length fraction	1-4/9 in
Dimension - B Length inch	1.92 in
Dimension - Bolt Size inch	0.88 in
Dimension - Cross Flats inch	1.12 in
Dimension - Height fraction	8/9 in
Dimension - Height inch	0.90 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.92 in
Dimension - Width inch	0.88 in
Dimension - Width mm	22 mm

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Run	2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	2 AWG-2/0 AWG
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Tap Range	8 AWG-2/0 AWG
Conductor - Copper Solid Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Tap Range	8 AWG-2/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 AWG-2/0 AWG
Conductor - Copper Str Tap	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	8 AWG-2/0 AWG
Conductor Type	<ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• CU C Solid-Run• AL C Str-Tap• CU C Str-Tap• CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL468A-468B
Standards - Industry Standards Met	UL468A-468B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)