

Project: _____ Type: _____

Drawn by: _____ Catalogue #: _____ Date: _____

Individual Spec Sheet

VTL4-L

3 CCT SELECT, NEMA4X, NSF VAPOR TIGHT

ORDERING INFORMATION

Order code: 68323
Model number: VTL4-LS4-Q/3C
UPC: 69549008144
DLC unique ID: PLHKWBBWLJ17
Case quantity: 1

PHYSICAL DATA

Dimensions: 45.66" x 4.74" (1160 mm x 120 mm)
Lens material: Frosted PC
Latch material: Stainless steel
Housing material: Polycarbonate
Mounting: Surface, suspended

PERFORMANCE DATA

Watts (W): 65
Volts (VAC): 347
Colour temperature (K)¹: 3 CCT (3 500/4 000/5 000)
Lumen output (lm)²: 8 560
Lumen per Watts (lm/W): 128
CRI: 80+
Life L70 (h)³: >50 000
THD (%): 9.37
Power factor: 0.9956
Dimming range: 0-10 V
Frequency (Hz): 50/60
Operating temp. range: -32°C to 40°C (-25°F to 104°F)

¹ Typical colour temperature range: +/- 5 %


² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %

³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations



Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.


DIMENSIONS



PHOTOMETRIC DATA¹

68323 • VTL4-LS4-Q/3C • at 4 000 K • 9 260.3 lm

Polar candela distribution



Zonal lumen summary

Zone	Lumens	% Fixture
0-30	2 188.8	23.6%
0-40	3 577.5	38.6%
0-60	6 342.4	68.5%
60-90	2 378.9	25.7%
70-100	1 603.4	17.3%
90-120	477.1	5.2%
0-90	8 721.3	94.2%
90-180	539.0	5.8%
0-180	9 260.3	100%

Illuminance at a distance

Center beam fc	Beam width	
4.3'	153 fc	11.0' 16.6'
8.7'	37.4 fc	22.2' 33.6'
13.0'	16.8 fc	33.2' 50.2'
17.3'	9.46 fc	44.2' 66.8'
21.7'	6.01 fc	55.4' 83.7'
26.0'	4.19 fc	66.4' 100.3'

Vert. spread: 103.8°
 Horiz. spread: 125.2°

¹ Complete IES files available on our website.

Qty	Description	Price

I accept the specifications of the luminaire configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.