

| oject: | | Type: | |
|-----------|--------------|-------|--|
| , | | 31 | |
| Drawn by: | Catalogue #: | Date: | |

Individual Spec Sheet

FLB

LED FLOOD LIGHT GEN 4

Quick and Easy Mounting accessories (Sold separately)

ORDERING INFORMATION

Order code: 68553

Model number: FLBL-L4AM-W-4K-BR UPC: 069549017283

Case quantity:

DLC unique ID: PUMW99US

PHYSICAL DATA

Dimensions: 17 7/8" x 12 5/8" x 2 3/4" (454 mm x 320 mm x 70 mm)

Lens material: Polycarbonate Aluminum die-cast **Housing material:**

Finish: Bronze

PERFORMANCE DATA

Watts (W): 300 Volts (V): 120-277 Color temperature (K)1: 4 000 Lumen output (Im)2: 41 709 Efficiency (Im/W): 139 CRI: 70 **NEMA Type (HxV)** 7x6 Life L70 (h)3: >60 000 Dimming (Yes/No): Yes Power factor: 0.99 THD (%): 5.87 Surge protection (kV): LED current (mA): 2.703-1.168 Operating temp. range: -40 °C to 40 °C

COMPATIBLE ACCESSORIES

| Order code | Description |
|------------|---|
| 68570 | Bronze Yoke for FLBL-FLBX |
| 68571 | Bronze Slipfitter |
| 68572 | Bronze square/round Pole arm |
| 68573 | Bronze Trunnion |
| 68574 | Bronze Wall/Pole mount adapter ¹ |
| 68717 | Bronze Slipftter and Wall mount adapter |

¹ Wall mount adapter used conjunctively with Slipfitter.

This lighting equipment complies with Canadian standard ICES-005 for use in commercial applications Data is based upon tests performed in a controlled environment.

Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.









quick

LED fixture





ship







IK08

fixture



ICES 005






Not all products are qualified on the DLC QPL. To view our DLC qualified products, please consult the DLC Qualified Products List at www.designlights.org/search.

¹ Typical colour temperature range: +/- 5 %

² Lumen values are derived from photometric testing. Initial lumens range: +/- 10 %
³ Life hours are derived from IESNA LM80-08 testing report and projected per IESNA TM-21-11 extrapolations




DIMENSIONS



PHOTOMETRIC DATA¹

68553 • FLBL-L4AM-W-40K-BR • 41 646.9 lm

Polar candela distribution



¹ Complete IES files available on our website.

Zonal lumen summary

| Zone | Lumens | % Fixture |
|--------|----------|-----------|
| 0-30 | 13 429.8 | 32.2% |
| 0-40 | 21 982.5 | 52.8% |
| 0-60 | 36 445.3 | 87.5% |
| 60-90 | 5 201.6 | 12.5% |
| 70-100 | 1 453.8 | 3.5% |
| 90-120 | 0 | 0% |
| 0-90 | 41 646.9 | 100% |
| 90-180 | 0 | 0% |
| 0-180 | 41 646.9 | 100% |

Illuminance at a distance

| Center beam fc | | | Beam | Beam width | |
|----------------|---------------------------------|-----------------|--------|------------|--|
| 17' | 58.6 fc | | 33.4' | 57.5' | |
| 34' | 14.7 fc | | 66.8' | 114.9' | |
| 51' | 6.51 fc | | 100.2' | 172.4' | |
| 68' | 3.66 fc | | 133.6' | 229.9' | |
| 85' | 2.34 fc | | 167.0' | 287.4' | |
| 102' | 1.63 fc | | 200.4' | 344.8' | |
| | Vert. spread: Horiz. spread: | 89.0° 118.8° | | | |

Data is based upon tests performed in a controlled environment. Actual performance can vary depending on operating conditions. All products are subject to change or may be discontinued any time without notice.

Signature:

Date:

Qty Description Price

I accept the specifications of the luminaire configuration mentioned above.

Name:
Company: