





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
SEE SHEET 2	SEE SHEET 2



SPECIFICATION:

1. STANDARD:
- UNIT TYPE: SEE SHEET 2
 - ORIENTATION: VERTICAL, MID
 - OUTLET QTY&TYPE: (20)C13, (4)C19
 - INPUT VOLTAGE: 200-240VAC
 - INPUT CURRENT: 30A (24A DERATED)
 - BREAKER QTY&TYPE: (2) 20AMP, DOUBLE-POLE
 - INPUT PHASE: SINGLE-PHASE
 - RATED POWER: 5.0kVA
 - INPUT PLUG: NEMA L6-30P
 - INPUT POWER CORD: SEE SHEET 2 FOR PART NUMBER TABLE
 - REGULATORY STANDARD: RoHS COMPLIANT

2. ADDITIONAL:

NONE

3. ACCESSORIES:


- (1) QUICK-START GUIDE

NOTES:

- PRIMARY DIMENSIONS ARE IN MILLIMETERS. SECONDARY DIMENSION ARE IN [INCHES]
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES
- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- FOR FULL PRODUCT FUNCTIONALITY REFER TO USER MANUAL CONFIGURATION
- DRAWING VIEWS SHOW THE INPUT CORD IN THE "TOP END FED"
- PARTS USING UPGRADEABLE IPDU BLANKING PANEL CAN BE UPGRADED TO INTELLIGENT MODELS USING PANDUIT CONTROLLER PART NUMBER MA002

IDENTIFICATION

FOR FINISHED GOOD PART NUMBER & DESCRIPTION TABLE SEE SHEET 2 CONFIGURABLE PART NUMBERS: P24D07M-XX Y Z



BOTTOM VIEW



WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.	SIGN
	DATE
	PRINT

PLUG/RECEPTACLE BLOCK

PLUG
NEMA L6-30P, 2P 3W
30A, 250V MAX RATED INPUT
24A DERATED

RECEPTACLES
IEC 60320/C19
16A, 250V MAX RATED OUTPUT

RECEPTACLES
IEC 60320/C13
10A, 250V MAX RATED OUTPUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	05/18/2022	FYZ	MIM	MJD	1. ADDED UPGRADEABLE PDU OPTION 2. REMOVED OBSOLETE SKU'S	P24D07M
03A	07/16/2020	CWW	MIM	JAWI	UPDATED THE OUTLET DESIGN	P24D07M
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER' UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24D07M
01A	07/27/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D07M

TITLE INTELLIGENT SERIES PDU P24D07M-XXYZ CUSTOMER DRAWING	
ITEM REVISION NAME:	
DATASHEET FILE NAME:	
UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]	
Tolerance(mm)	
04<50	±0.5
50<1250	±1.0
250<500	±1.5
500<1000	±2.5
1000<2000	±4.0
THIRD ANGLE PROJECTION	
DRAWN BY	DATE
GEORGE	07/27/2017
CHK	SCALE
SEAN	NONE
MATERIAL/COLOR: N/A	
DRAWING NUMBER: P24D07M_DC	
SHT 1 OF 2	
SCALE B	

2 ↑ 1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

MAIN PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24D07M	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-BL1A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-RD1A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-RD1C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-YL1A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-YL1C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-BU1A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-BU1C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-BL2A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLACK	BLACK (RAL 9005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-BL2C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-RD2A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, RED	RED (RAL 3020)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-RD2C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, RED	RED (RAL 3020)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-YL2A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-YL2C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, YELLOW	YELLOW (RAL 1023)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
P24D07M-BU2A	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 1 METER INPUT CORD, BLUE	BLUE (RAL 5005)	1M(+178MM/-89MM) 3.3'[+3.5"/-1.75"]	6.4kg
P24D07M-BU2C	VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , BOTTOM-END FED, 3 METER INPUT CORD, BLUE	BLUE (RAL 5005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.8kg
UPGRADEABLE PDU CONFIGURATIONS				
FINISHED GOOD PART NUMBER	FINISHED GOOD DESCRIPTION	COLOR	INPUT CORD LENGTH	WEIGHT
P24D07U	UPGRADEABLE,VERTICAL,(20) C13,(4) C19,MONITORED INPUT, 200-240V/30A/1 PHASE , TOP-END FED, 3 METER INPUT CORD, BLACK	BLACK (RAL 9005)	3M(+254MM/-127MM) 10'[+10"/-5"]	6.5kg

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	05/18/2022	FYZ	MIM	MJD	1.ADDED UPGRADEABLE PDU OPTION 2.REMOVED OBSOLETE SKU'S	P24D07M
03A	07/16/2020	CWW	MIM	JAWI	UPDATED THE OUTLET DESIGN	P24D07M
02A	06/07/2018	H.XU	MIM	JAWI	ADDED SHEET 2 WITH CONFIGURABLE PART NUMBER TABLE AND DESCRIPTION UPDATED IDENTIFICATION TO INCLUDE CONFIGURABLE OPTION 'DE-CODER' UPDATED CIRCUIT BREAKER LABELS WITH ROTATED TEXT	P24D07M
01A	07/27/2017	GEORGE	MIM	EDM	INITIAL RELEASE	P24D07M

<p style="font-size: 8px;">WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX. THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY</p>	<p style="font-size: 8px;">SIGN _____</p> <p style="font-size: 8px;">DATE _____</p> <p style="font-size: 8px;">PRINT _____</p>												
<p style="text-align: center;">TITLE INTELLIGENT SERIES PDU P24D07M-XXYZ CUSTOMER DRAWING</p>													
<p style="font-size: 8px;">ITEM REVISION NAME:</p>													
<p style="font-size: 8px;">DATASHEET FILE NAME:</p>	<p style="font-size: 8px;">MATERIAL/COLOR: N/A</p>												
<p style="font-size: 8px; text-align: center;">UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE ARE: mm [IN]</p> <table style="width: 100%; font-size: 8px;"> <tr> <td style="width: 50%;">Tolerance(mm)</td> <td style="width: 50%;"></td> </tr> <tr> <td>0-1<50</td> <td>±0.5</td> </tr> <tr> <td>50-1<250</td> <td>±1.0</td> </tr> <tr> <td>250-1<500</td> <td>±1.5</td> </tr> <tr> <td>500-1<1000</td> <td>±2.5</td> </tr> <tr> <td>1000-1<2000</td> <td>±4.0</td> </tr> </table>		Tolerance(mm)		0-1<50	±0.5	50-1<250	±1.0	250-1<500	±1.5	500-1<1000	±2.5	1000-1<2000	±4.0
Tolerance(mm)													
0-1<50	±0.5												
50-1<250	±1.0												
250-1<500	±1.5												
500-1<1000	±2.5												
1000-1<2000	±4.0												
<p style="font-size: 8px;">DRAWN BY DATE GEORGE 07/27/2017</p>	<p style="font-size: 8px;">CHK SCALE SEAN NONE</p>												
<p style="font-size: 8px;">DRAWING NUMBER: P24D07M_DC</p>													
<p style="font-size: 8px;">SHT 2 OF 2</p>													
<p style="font-size: 8px;">SCALE B</p>													

2 ↓ 1