



Pass & Seymour


# Isolated Ground PlugTail™ Receptacles 15 & 20A, 125V

PTIG5262, PTIG5362

## PlugTail™ — The fastest, most consistent and reliable wiring devices – ever.

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device — no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

The toughest and safest isolated ground receptacle available.



### FEATURES & BENEFITS

**Auto-ground clip** assures positive ground.

**Plastic barrier** isolates grounding terminal from mounting strap and metal boxes.

**.036 inch thick, brass, triple-wipe power contacts** for lasting retention.

**Three drive screws anchor strap** to back body and face.

**Plated steel wrap strap design** for maximum durability and corrosion resistance.

**Built-in connector** features large brass terminal blades to ensure consistent, reliable electrical connections.

**Large brass contacts** snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

**Ultrasonically welded polycarbonate connector housing** secures terminations and conductors in a UL Listed, finger safe housing.

**Pre-stripped connector leads** fasten to conductors, easier than standard pigtails.

**No exposed terminals** create a finger safe application before, during, and after installation.



PTIG5362-LA

### FIELD USES/VERTICAL MARKETS

- Industrial
- Health Care
- Education
- Institutional
- Retail
- Office
- Hospitality/Lodging

# Isolated Ground PlugTail™ Receptacles

## 15 & 20A, 125V

### ORDERING INFORMATION

Catalog Number	Rating		Color	NEMA Config. No.
	A.	V.		
<b>Duplex Receptacles</b>				
PTIG5262-I	15	125	Ivory	5-15R
PTIG5262-W	15	125	White	5-15R
PTIG5262	15	125	Orange	5-15R
PTIG5262-GRY	15	125	Gray	5-15R
PTIG5262-RED	15	125	Red	5-15R
PTIG5262-LA	15	125	Light Almond	5-15R
PT5362-I	20	125	Ivory	5-20R
PT5362-W	20	125	White	5-20R
PT5362	20	125	Orange	5-20R
PT5362-GRY	20	125	Gray	5-20R
PT5362-RED	20	125	Red	5-20R
PT5362-LA	20	125	Light Almond	5-20R

Catalog Number	Wire Type	Wire Length
<b>PlugTail Connectors — Right Angle</b>		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"



NEMA  
5-15R



NEMA  
5-20R

For more information on these and other P&S products refer to our Catalog or visit our web site.

# PlugTail™ Isolated Ground Receptacles

## 15 & 20A, 125V



### TECHNICAL SPECIFICATIONS

#### 3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498.  
Federal Specification WC596.

#### Performance

##### Electrical


Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rate current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

##### Mechanical

PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are a permanent part of the device

##### Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Dimensions for 15 & 20 Amp



#### PlugTail™ GFCI Receptacle Materials


Face	Nylon	Internal Ground System	.036 260 Brass
Body	PVC	Assembly Drive Screw	Zinc-Plated Steel
Contacts	.036 688 Brass	Aut-Ground Clip	Steel
Mounting Strap	.042" Zinc-Plated Steel	Mounting Screws	Tri-Drive Steel

#### Plug Tail Connector Materials

Housing	Polycarbonate	Contacts	.030 Brass
---------	---------------	----------	------------


#### Warranty

1 Year




PTR6STR

## COMPLEMENTARY DEVICES & ACCESSORIES




### PLUGTAIL™ DEVICES

- Spec Grade
- Decorator
- Hospital Grade
- Tamper-Resistant
- Isolated Ground
- Split Circuit




### STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




### DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



### SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



### GFCIs

- Specification Grade
- Hospital Grade



### WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

## ALSO AVAILABLE...

- |                                      |                                     |                               |                            |
|--------------------------------------|-------------------------------------|-------------------------------|----------------------------|
| ■ Hospital Grade Devices             | ■ Straight Blade Plugs & Connectors | ■ Weatherproof Boxes & Covers | ■ Flexcor® Wire Mesh Grips |
| ■ TVSS & Isolated Ground Devices     | ■ Turnlok® Locking Devices          | ■ IEC 309 Industrial Products | ■ Bulk Solutions           |
| ■ Ground Continuity Monitoring (GCM) |                                     |                               |                            |



**Legrand/Pass & Seymour**  
 P.O. Box 4822  
 Syracuse, NY 13221-4822  
 800-223-4185

**North America Headquarters**  
 60 Woodlawn Street  
 West Hartford, CT 06110  
 Phone: 1.877.BY.LEGRAND (295.3472)  
 Fax: 1.860.232.2062  
 www.legrand.us

**Legrand Canada**  
 570 Applewood Crescent  
 Vaughan, ON, L4K 4B4  
 Phone: 905.738.9195  
 Fax: 905.738.9721  
 www.legrand.ca

