



Selection & Application Guide

Residential Load Centers


usa.siemens.com/loadcenters

Load Centers

Table of Contents

Description	Page
Catalog Numbering System	1
Plug-On Neutral Load Centers	2
Electronic Breakers and Surge Protection	3
1-Phase PN Series Plug-On Neutral Load Centers	4
1-Phase SN Series Plug-On Neutral Load Centers	7
3-Phase PL and ES Series Load Centers	11
EQ® Load Centers, 300-400 Amp	15
Generator Ready Load Centers	16
Riser Panel Load Centers	17
EQ® Load Centers, Small Circuit and Circuit Breaker Enclosures	18
Renovation Interiors	20
Load Center Accessories	21
Circuit Breakers	25
Surge Protection	28
Load Center Cross Reference	30

Catalog Numbering System



Products Shown In Sections 1 of this Speedfax Meet or Exceed the Following Standards.

- UL50 Electric Cabinets and Boxes
- UL67 Electric Panelboards
- UL486 Wire Connectors
- UL489 Molded-Case Circuit Breakers
- UL869 Service Equipment
- UL943 Ground Fault interrupters (Class A — Personnel Protection)
- Federal Specification W-P-115b Panel Power Distribution
- Federal Specification W-C-375B Circuit Breakers
- NEC
- NEMA 250

Underwriters' Laboratories, Inc. Reference File Numbers:

- Series Connected Circuit Breaker Information is recognized by UL under file #E10848(N)
- Load Centers Listed by UL under file #E10703
- Load Centers UL recognized components found under file #E10703, Volume 6 and 7. (Also referenced under the recognized components directory — section QEUY2)
- EQ Circuit Breakers are Listed by UL under file #E82615

Plug-On Neutral Load Centers

Overview

Plug-On Neutral Load Centers

You have come to know Siemens solutions for their durability, innovation, and safety attributes. This continues with the plug-on neutral load center with electronic breakers to provide a more secure connection resulting in a more confident installation.


With an overall smaller electronic breaker footprint, the plug-on neutral load center still gives you over 4" of wire bending space, which allows for a simpler, cleaner, and faster path to a finished project.



Simple Spacious Secure

- Quicker breaker installation
- Wiring made easier with the neutral lug removed on CAFCI breakers
- Same great features as PL and ES load centers
- Small electronic breaker footprint
- · Design allows for neutral terminal accessibility
- Over 4 inches of wire bending space
- Same reliable installation method
- Neutral clip is the same as line side
- Durable hook-rail

A Siemens Advantage



Electronic Breakers and Surge Protection

Complete Offering

Electronic Breakers and Surge Protection

The new plug-on neutral load center is compatible with existing surge solutions including the QSA breaker and FirstSurge™ stand-alone units. Additionally, there are four panels offered with a factory-installed FirstSurge

For more information on the Surge Protection product line, see Section 10 and Section 7 Page 7-28 of the Speedfax at usa.siemens.com/speedfax.







QSA Circuit Breaker and Surge Protection Device



Plug-on neutral breaker offering:

- 1 and 2-pole CAFCI
- 1-pole Dual Function (CAFCI/GFCI)
- 1-pole GFCI

Features:

- Load Lug(s) only on the CAFCI breakers
- LED indicators for troubleshooting
- Insta-Wire connectors

Technical Data:

- 10,000 AIC
- 120V
- UL Listed
- HACR and SWD rated

	Breaker Type	Ampere Rating	10,000 A IR Catalog No.
	QAF2N	15	QA115AFCN
AFCI	Plug-on Neutral 1-Pole 120V AC	20	QA120AFCN
AFCI	QAF2N Plug-on Neutral	15	Q215AFCN
	2-Pole 120/240V AC	20	Q220AFCN
Dual	QFGA2N	15	Q115DFN
Function	Plug-on Neutral 1-Pole 120V AC	20	Q120DFN
	ODEAN	15	QF115AN
GFCI (5mA)	QPF2N Plug-on Neutral 1-Pole 120V AC	20	QF120AN
		30	QF130AN

Note: Both plug-on neutral and existing pigtail breakers are listed for use in plug-on neutral load centers. For information on the complete product line, go to page 25.

1-Phase PN Series Plug-On Neutral Load Centers

Features

- Convertible
- Invertible
- Bonding Screw
- Visible Neutrals
- Insta-Wire
- Durable Hook-Rails
- Integrated Neutral Bus
- Extended Lifetime Warranty

All devices convertible from main lug to main breaker and vice versa.

Invertible for bottom feed application.®

All devices are provided with 2 factory installed ground bars.





Mounting tabs on the trim hold it in place on the load center, freeing up both hands to drive the trim screws.

Combination head screw on the neutrals, ground, trim, upper pan, and bond screw provide installation flexibility.








The prepositioned bond screw eliminates bond strap/ screw assemblies, and reduces the risk of

losing components in the field.

A rigid, sturdy base pan provides the ruggedness required for the most harsh applications.







The patented INSTA-WIRE™ neutral/ground system allows for faster installation because screws are backed out,

ready for wire insertion. The visible neutral and grounds system aids in the insertion of conductors.

Copper Bus[®]



The outdoor enclosure has a slide hinge door for the easiest installation and can be removed by backing out only one screw.



All devices come with an integrated neutral bus.

> 1-Phase PN Series Plug-On Neutral Load Centers ship with trims packaged separately.



① Applies only to NEMA 1 PN and SN plug-on neutral load centers. @ PN SKUs that have a C suffix have copper bus.

1-Phase PN Series Plug-On Neutral Load Centers

1-phase, 3-wire, 120/240 Volts AC Main Breaker/Convertible

Main Breaker / Convertible Load Centers ① 100-225 Amperes

Copper Bus 60/75°C Rated

			Indoor Enclosure - NEMA T	ype 1	Outdoor Enclosure - NEM	A Type 3R
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number [©]	Enclosure Height (inches) ②	Catalog Number	Enclosure Height (inches) ③
100	12	24	PN1224B1100C	18	PNW1224B1100C	21
100	16	32	PN1632B1100C	21	PNW1632B1100C	23
100	20	20	PN2020B1100C	21	PNW2020B1100C	27
100	20	40	PN2040B1100C	21	-	-
100	24	24	PN2424B1100C	24	-	-
100	30	30	PN3030B1100C	26	-	-
100	30	48	-	-	PNW3048B1100C	29
125	30	30	PN3030B1125C	26	-	-
125	30	48	-	-	PNW3048B1125C	29
150	8	16	-	-	PNW0816B1150TC 5	23
150	20	40	PN2040B1150C	24	PNW2040B1150C	27
150	30	30	PN3030B1150C	30	-	-
150	30	48	-	-	PNW3048B1150C	35
200	8	16	-	-	PNW0816B1200TC ⑤	23
200	20	40	PN2040B1200C	26	PNW2040B1200C	27
200	30	48	PN3048B1200 ④	30	-	-
200	30	48	PN3048B1200C	30	PNW3048B1200C	35
200	40	40	PN4040B1200 ④	36	-	-
200	40	40	PN4040B1200C	36	PNW4040B1200C	38
200	40	60	PN4060B1200 4	36	-	-
200	40	60	PN4060B1200C	36	-	-
200	54	82	PN5482B1200C	42	-	-
225	42	64	PN4264B1225C	39	PNW4264B1225C	38
225	54	82	PN5482B1225C	43	-	-

 $[\]textcircled{1} \quad \text{Factory installed 22KAIC main breaker. Suitable for use as service equipment.}$

② Indoor enclosures are 14 1/4" wide by 3 7/8" deep.

③ Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

⁴ Includes all PN series features with aluminum bus.

⑤ Feed-thru lugs.

⁶ Available (made to order) in white by adding "W" to the end of the catalog number.

1-Phase PN Series Plug-On Neutral Load Centers

1-phase, 3-wire, 120/240 Volts AC Main Lug/Convertible

Main Lug / Convertible Load Centers ^③ 125-225 Amperes

Copper Bus 60/75°C Rated

			Indoor Enclosure - NEMA	Type 1	Outdoor Enclosure - NEM	:MA Type 3R	
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number [©]	Enclosure Height (inches) ①	Catalog Number	Enclosure Height (inches) ②	
125	12	12	PN1212L1125C	18	PNW1212L1125C	21	
125	12	24	PN1224L1125C	18	PNW1224L1125C	21	
125	16	32	PN1632L1125C	21	PNW1632L1125C	23	
125	20	20	PN2020L1125C	21	-	-	
125	20	40	PN2040L1125C	21	-	-	
125	24	48	PN2448L1125C	24	-	-	
125	30	48	PN3048L1125C	26	PNW3048L1125C	29	
125	40	40	PN4040L1125C	36	-	-	
150	20	40	PN2040L1150C	24	PNW2040L1150C	27	
200	8	16	-	-	PNW0816L1200TC 5	23	
200	12	24	PN1224L1200C	21	PNW1224L1200C	23	
200	20	40	PN2040L1200C	26	PNW2040L1200C	27	
200	24	48	PN2448L1200C	30	-	-	
200	30	30	PN3030L1200C	30	-	-	
200	30	48	PN3048L1200 4	30	-	-	
200	30	48	PN3048L1200C	30	PNW3048L1200C	35	
200	40	40	PN4040L1200 4	36	-	-	
200	40	40	PN4040L1200C	36	PNW4040L1200C	38	
200	40	60	PN4060L1200C	36	-	-	
225	12	24	-	-	PNW1224L1225C	27	
225	42	64	PN4264L1225C	39	PNW4264L1225C	38	
225	54	82	PN5482L1225C	43	-	-	

① Indoor enclosures are 14 1/4" wide by 3 7/8" deep.

② Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

^{3 125}A load centers will accept MBK100A and MBK125A. 150A load centers will accept MBK150A. 200A load centers will accept MBK200A and MBK150A. 225A load centers will accept MBK225A, MBK200A, MBK150A.

⁴ Includes all PN series features with aluminum bus.


⑤ Feed-thru lugs.

⑥ Available (made to order) in white by adding "W" to the end of the catalog number.

1-Phase SN Series Plug-On Neutral Load Centers

Features

- Invertible
- Bonding Screw
- Visible Neutrals
- Insta-Wire
- Durable Hook-Rails
- Integrated Neutral Bus
- Extended 10-Year Warranty



① Applies only to NEMA 1 PN and SN plug-on neutral load centers

installation and can be removed by backing out only one screw.

1-Phase SN Series Plug-On Neutral Load Centers

1-phase, 3-wire, 120/240 Volts AC Main Breaker

Main Breaker Load Centers ① 100-225 Amperes

Aluminum Bus 60/75°C Rated

			Indoor Enclosure - NEMA	A Type 1	Outdoor Enclosure - NE	MA Type 3R
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number ^⑤	Enclosure Height (inches) ②	Catalog Number	Enclosure Height (inches) ^③
100	12	24	SN1224B1100	18	SNW1224B1100	21
100	16	32	SN1632B1100	21	SNW1632B1100	23
100	20	20	SN2020B1100	21	SNW2020B1100	27
100	20	40	SN2040B1100	21	-	-
100	24	48	SN2448B1100	24	-	-
100	30	30	SN3030B1100	26	-	-
100	30	48	SN3048B1100	26	-	-
125	12	24	-	-	SNW1224B1125	21
125	16	32	SN1632B1125	21	-	-
125	20	40	-	-	SNW2040B1125	27
125	24	24	SN2424B1125	24	SNW2424B1125	27
125	30	30	SN3030B1125	26	-	-
125	30	48	SN3048B1125	26	SNW3048B1125	29
150	16	32	SN1632B1150	24	-	-
150	20	40	SN2040B1150	24	SNW2040B1150	27
150	24	48	SN2448B1150	26	-	-
150	30	30	SN3030B1150	30	-	-
150	30	48	SN3048B1150	30	SNW3048B1150	35
200	40	40	-	-	SNW4040B1150	38
200	8	16	-	-	SNW0816B1200T @	23
200	12	24	-	_	SNW1224B1200	23
200	16	32	SN1632B1200	24	-	-
200	20	40	SN2040B1200	26	SNW2040B1200	27
200	24	48	SN2448B1200	30	-	-
200	30	48	SN3048B1200	30	SNW3048B1200	35
200	40	40	SN4040B1200	36	SNW4040B1200	38
200	40	60	SN4060B1200	36	-	-
200	42	64	SN4264B1200	39	-	-
200	54	82	SN5482B1200	42	-	-
225	42	64	SN4264B1225	39	SNW4264B1225	38
225	54	82	SN5482B1225	43	-	-

① Factory installed 22KAIC main breaker. Suitable for use as service equipment.

② Indoor enclosures are 14 1/4" wide by 3 7/8" deep.

③ Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

⁴ Feed-thru lugs.

S Available (made to order) in white by adding "W" to the end of the catalog number.

1-Phase SN Series Plug-On Neutral Load Centers

1-phase, 3-wire, 120/240 Volts AC Main Lug

Main Lug Load Centers 100-225 Amperes

Aluminum Bus 60/75°C Rated

			Indoor Enclosure - NEMA Type 1		Outdoor Enclosure - NEMA	Type 3R
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number ^④	Enclosure Height (inches) ^①	Catalog Number	Enclosure Height (inches) $^{\textcircled{2}}$
125	12	12	SN1212L1125	18	SNW1212L1125	21
125	12	24	SN1224L1125	18	SNW1224L1125	21
125	16	32	SN1632L1125	21	SNW1632L1125	21
125	20	20	SN2020L1125	21	-	-
125	20	40	SN2040L1125	21	SNW2040L1125	23
125	24	24	SN2424L1125	24	SNW2424L1125	27
125	24	48	SN2448L1125	24	-	-
125	30	48	SN3048L1125	26	SNW3048L1125	29
125	40	40	SN4040L1125	30	-	-
150	16	32	SN1632L1150	21	-	-
150	20	40	SN2040L1150	24	SNW2040L1150	27
150	24	48	SN2448L1150	26	-	-
200	8	16	-	-	SNW0816L1200T ③	23
200	12	24	SN1224L1200	21	SNW1224L1200	21
200	20	40	SN2040L1200	26	SNW2040L1200	27
200	24	48	SN2448L1200	26	-	-
200	30	30	SN3030L1200	30	-	-
200	30	48	SN3048L1200	30	SNW3048L1200	29
200	40	40	SN4040L1200	36	SNW4040L1200	35
225	12	24	-	-	SNW1224L1225	21
225	40	60	SN4060L1225	36	-	-
225	42	64	SN4264L1225	36	SNW4264L1225	38
225	54	82	SN5482L1225	42	-	-

① Indoor enclosures are 14 1/4" wide by 3 7/8" deep.

② Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

③ Feed-thru lugs.

④ Available (made to order) in white by adding "W" to the end of the catalog number.

Specialty Main Lug and Main Breaker Plug-On Neutral Load Centers

1-phase, 3-wire, 120/240 Volts AC

Factory Installed FirstSurge™ Load Centers

			Indoor Enclosure - NEMA Type 1 Enclosure Height (inches)		
Amp Rating	No. of Spaces	No. of Circuits			Surge Protection
200	30	48	PN3048B1200S14	36	140kA
200	40	60	PN4060B1200S14	42	140kA
200	30	48	SN3048B1200S06	36	60kA
200	40	60	SN4060B1200S06	42	60kA

500 Kcmil Lug Load Center

			Indoor Enclosure - NEMA Ty	pe 1					
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height (inches)					
200	30	48	SN3048L1200L50	36					

Selectable Main Load Centers

			Indoor Enclosure - NEMA Type 1		Outdoor Enclosure - NEMA Type 3R		
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height (inches)	Catalog Number	Enclosure Height (inches)	
125	24	24	SN2424C1125	24	SNW2424C1125	27	
200	20	40	SN2040C1200	26	SNW2040C1200	27	
200	30	48	SN3048C1200	30	SNW3048C1200	35	
200	40	40	SN4040C1200	36	SNW4040C1200	38	

3-Phase PL and ES Series Load Centers

Features

PL Series:


- Convertible
- Invertible
- Flush or Surface Mount Combination Cover
- Insta-wire neutrals & grounds
- Ground bars included
- Copper busbars
- · Dual neutrals on all configurations
- Carton-in-carton packaging
- · Lifetime warranty



PL Series 3-phase

ES Series:

- Invertible
- Flush or Surface Mount Combination Cover
- Insta-wire neutrals & grounds
- Aluminum busbars
- Single sided neutral on 24 circuits and below
- · Single piece carton packaging
- 10 year warranty



ES Series 3-phase

PL Series 3-Phase Main Lug & Main Breaker Load Centers

3-phase, 3-wire, 240 Volt AC or 3-phase, 4-wire, 120/240 or 120/208 Volts AC

Main Breaker/Convertible Load Centers

30-70 Circuits / 100-225 Amperes

Copper Bus^① 60/75°C Rated 22,000A IR^①

Branch Circuits			Indoor Enclosure – NEM	1A Type 1	Outdoor Enclosure – NEMA Type 3R		
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height Catalog Number (inches)® (Enclosure Height (inches) ⁽⁴⁾	
100	12	24	P1224B3100CU ²	24	_	<u> </u>	
100	30	42	P3042B3100CU ²	30	_	<u> </u>	
125	30	30	P3030B3125CU	39	_	_	
150	24	42	P2442B3150CU	36	_	_	
150	42	42	P4242B3150CU	42	_	_	
200	30	54	P3054B3200CU	39	PW3054B3200CU	38	
200	42	60	P4260B3200CU [®]	42	PW4260B3200CU	42	
225	42	60	P4260B3225CU	42	_	_	
225	42	60	P4260B3225TCU [®]	49	_	<u> </u>	
225	54	70	P5470B3225CU	49	_		

Main Lug/Convertible Load Centers 12-70 Circuits / 125-225 Amperes

Copper Bus^⑦ 60/75° Rated 100,000A IR®

			<u> </u>				
Branch Circuits			Indoor Enclosure – NEI	MA Type 1	pe 1 Outdoor Enclosure – NEMA Type 3R		
Amp No. of No. of Spaces Circuits		Catalog Number	log Number Enclosure Height (inches) [®] Catalog N		Enclosure Height (inches) ⁴		
125	12	24	P1224L3125CU [®]	21	PW1224L3125CU®	21	
200	24	42	P2442L3200CU	36	PW2442L3200CU	35	
200	30	54	P3054L3200CU	39	PW3054L3200CU	38	
225	42	60	P4260L3225CU	42	PW4260L3225CU	42	
225	54	70	P5470L3225CLI	49		_	

¹⁾ May be installed on higher rated systems when protected by a circuit breaker with a higher AIR rating.

Back fed main breaker.
 Indoor enclosures are 14 1/4" wide by 3 7/8" deep.
 Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

 $[\]ensuremath{\texttt{\$}}$ Includes factory installed feed through lugs and is also nonconvertible.

[®] Non-convertible to main breaker.② All load centers are provided with tin plated copper bus bars.

[®] Rated 100,000A IR in series with breakers listed on wiring diagram.

Available (made to order) in white by adding "W" to the end of the part number

PL Series 3-Phase Unassembled Load Centers

3-phase, 3-wire, 240 Volt AC or 3-phase, 4-wire, 120/240 or 120/208 Volts AC







Main Breaker Convertible Unassembled Load Centers

Copper Bus^⑤ 60/75°C Rated 22,000A IR^①

24-70 Circuits / 100-225 Amperes

Interiors				Enclosure		Trim Kit	
Amp Rating	No. of Spaces	No. of Circuits	Interior Catalog Number	Enclosure Height (inches) [®]	Enclosure Catalog Number	No. Breaker Spaces	Trim Catalog Number [®]
100	30	42	PI3042B3100CU ²	30	3PE30	30	PT3042B3100
150	24	42	PI2442B3150CU	36	3PE36	24	PT2442X3150
200	30	54	PI3054B3200CU	39	3PE39	30	PT3054X3200
200	42	60	PI4260B3200CU	42	3PE42	42	PT4260X3200
225	54	70	PI5470B3225CU	49	3PE49	54	PT5470X3225

Main Lug Convertible Unassembled Load Centers

Copper Bus^⑤ 60/75° Rated 100,000A IR®

12-70 Circuits / 125-225 Amperes

Interiors				Enclosure		Trim Kit	
Amp Rating	No. of Spaces	No. of Circuits	Interior Catalog Number	Enclosure Height (inches) ^③	Enclosure Catalog Number	No. Breaker Spaces	Trim Catalog Number [®]
125	12	24	PI1224L3125CU	21	3PE21	12	PT1224L3125
200	24	42	PI2442L3200CU	36	3PE36	24	PT2442X3200
200	30	54	PI3054L3200CU	39	3PE39	30	PT3054X3200
225	42	60	PI4260L3225CU	42	3PE42	42	PT4260X3225
225	54	70	PI5470L3225CU	49	3PE49	54	PT5470X3225

① May be installed on higher rated systems when protected by a circuit breaker with a higher AIR rating.

② Back fed main breaker. ③ Indoor enclosures are 14 1/4" wide by 3 7/8" deep.

[®] Trim catalog numbers with a "B" indicate for use with main breaker and is not convertible. "L" indicates for use with main lug and is not convertible. "X" indicates can be used with convertible interior.

[®] All load center interiors are provided with tin plated copper bus

[®] Rated 100,000A IR in series with breakers listed on wiring diagram.

ES Series 3-Phase Main Lug & Main Breaker Load Centers

3-Phase, 3-Wire, 240 Volt AC or 3-Phase, 4-Wire, 120/240 or 120/208 Volts AC

Main Breaker

Aluminum Bus

30-60 Circuits / 100-225 Amperes

60/75°C Rated 10,000A IR¹

Branch Circu	its		Indoor Enclosure – NEI	ИА Туре 1	Outdoor Enclosure -	NEMA Type 3R
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height (inches) [®]	Catalog Number	Enclosure Height (inches) [®]
100	12	24	S1224B3100 ²	24	SW1224B3100	23
100	30	30	S3030B3100 ²	30	_	_
100	30	42	S3042B3100 ²	30	_	_
125	30	42	S3042B3125	35	_	_
150	24	42	S2442B3150	36	SW2442B3150	35
150	42	42	S4242B3150	42	_	_
150	30	54	S3054B3150	35	_	_
200	30	54	S3054B3200	39	SW3054B3200	38
200	42	60	S4260B3200	42	SW4260B3200	42
225	42	42	S4242B3225	42	SW4242B3225	42

Main Lug

Aluminum Bus

12-70 Circuits / 125-225 Amperes

60/75° Rated 100,000A IR^⑤

Branch Circu	iits		Indoor Enclosure - N	EMA Type 1	Outdoor Enclosure -	Enclosure Height (inches)® 21 23 27 21		
Amp Rating	No. of Spaces	No. of Circuits	Catalog Number	Enclosure Height (inches) ^③	Catalog Number	Enclosure Height (inches)®		
125	12	24	S1224L3125	21	SW1224L3125	21		
150	18	36	S1836L3150	24	SW1836L3150	23		
150	24	42	S2442L3150	30	SW2442L3150	27		
200	12	24	S1224L3200	21	SW1224L3200	21		
200	24	42	S2442L3200	30	SW2442L3200	27		
200	30	54	S3054L3200 [®]	30	SW3054L3200	35		
225	42	60	S4260L3225®	36	SW4260L3225	38		
225	54	70	S5470L3225®	42	_	_		

May be installed on higher rated systems when protected by a circuit breaker with a higher AIR rating.
 Rated 100,000A IR in series with breakers listed on wiring diagram.

② Back fed main breaker.

<sup>Bdck led main breaker.
Indoor enclosures are 14 1/4" wide by 3 7/8" deep.
Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.</sup>

[®] Available (made to order) in white by adding "W" to the end of the part number.

EQ® Load Centers—300-400 Amp

1-Phase, 3-Wire/3-Phase, 3-Wire, 4-Wire

Features

- UL listed for 60/75°C conductors. See equipment markings for applications.
- Copper bus standard.
- · Factory installed lock on indoor enclosures.
- Main breaker units have a factory installed JXD2 type breaker.



Main Breaker 300-400 Ampere^② 1Ø, 3-Wire

120/240 Volts AC 65,000A IR

Branch Circuits			Indoor Enclosure – NEMA Typ	e 1		Outdoor Enclosure – NEMA Type 3R		
Amp Rating	No. of Spaces	No. of Circuits	Siemens Catalog Number	Enclosure Height [®]	Trim Style	Siemens Catalog Number	Enclosure Height [®]	
300	42	42	E4242MB1300FCU	58	Flush	_	_	
300	42 42		E4242MB1300SCU	58	Surface	_	_	
	30	30	_	47	Surface			
400	30	30	E3030MB1400SCU	52	Surface	W3030MB1400CU	52	
400	42 42	E4242MB1400FCU	58	Flush	_	_		
	42	42	E4242MB1400SCU	58	Surface	W4242MB1400CU	58	

3Ø, 3-Wire, 4-Wire

240 Volts AC 65,000A IR

Branch Circuits			Indoor Enclosure - NEMA Typ	e 1		Outdoor Enclosure - NEMA	Type 3R
Amp Rating	No. of Spaces	No. of Circuits	Siemens Catalog Number	Enclosure Height [®]	Trim Style	Siemens Catalog Number	Enclosure Height [®]
300	42	42	E4242MB3300SCU	58	Surface	_	_
	30	30	E3030MB3400SCU	52	Surface	_	_
400	42	42	E4242MB3400FCU	58	Flush	_	_
	42	42	E4242MB3400SCU	58	Surface	W4242MB3400CU	58

Main Lug 400 Ampere

1Ø, 3-Wire

120/240 Volts AC 65,000A IR

Branch Circuits			Indoor Enclosure – NEMA Typ	e 1		Outdoor Enclosure – NEMA Type 3R		
Amp Rating	No. of Spaces	No. of Circuits	Siemens Catalog Number	Enclosure Height [®]	Trim Style	Siemens Catalog Number	Enclosure Height [®]	
	12	6	_	_	_	W0606ML1400CU®®	43	
400	30	30	E3030ML1400SCU	41	Surface	W3030ML1400CU	43	
400	42	42	E4242ML1400FCU	47	Flush	_	_	
	42	42	E4242ML1400SCU	47	Surface	W4242ML1400CU	47	

3Ø, 3-Wire, 4-Wire

240 Volts AC 22,000A IR

Branch Circuits			Indoor Enclosure - NEMA Typ	e 1		Outdoor Enclosure - NEMA T	ype 3R
Amp Rating	No. of Spaces	No. of Circuits	Siemens Catalog Number	Enclosure Height [®]	Trim Style	Siemens Catalog Number	Enclosure Height [®]
	30	30	E3030ML3400SCU	41	Surface	_	_
400	42	42	E4242ML3400FCU	47	Flush	_	_
	42 42		E4242ML3400SCU	47	Surface	W4242ML3400CU	47

 $[\]ensuremath{\textcircled{0}}$ Indoor and outdoor enclosures are 20" wide by 6" deep.

② UL listed as suitable for use as service equipment.

 $[\]ensuremath{\mathfrak{D}}$ Accepts up to six QN style breakers

Generator Ready Load Centers

1-Phase, 3-Wire SN, 120/240 Volts AC

Generator Ready Load Centers

The Siemens generator ready load center can save thousands of dollars in future generator installation expenses while keeping initial expenses to a minimum. Works with an automatic standby generator or a portable generator.

Load center features:

- UL Listed
- Indoor Type 1 and outdoor Type 3R
- · 225A max rated
- · Flush or surface mounting
- · Fits between standard stud centers
- · Tin plated copper bus bars
- 22 kAIC rated
- 120/240V ~
- · Main lug convertible to main breaker with addition of MBK150A, MBK200A, or MBK225A
- · Installation of transfer mechanism can be performed at time of generator installation



- UL Listed
- Operates automatically when connected to generator
- Transfers load from utility to generator and back to utility
- Transfer switch (sold separately) catalog number: GENTFRSWTCH^{①③}


Indoor Enclosure - NEMA Type 1

Amp Rating	No. of Spaces ²	No. of Circuits [®]	Siemens Catalog Number	Main	Enclosure Height®
200	30	42	G3042B1200GEN	Main Breaker	42
225	30	42	G3042L1225GEN	Main Lug	42
200	42	54	G4254B1200GEN	Main Breaker	44
225	42	54	G4254L1225GEN	Main Lug	44

Outdoor Enclosure - NEMA Type 3R

Amp Rating	No. of Spaces ²	No. of Circuits ²	Siemens Catalog Number	Main	Enclosure Height®
200	30	42	W3042B1200GEN	Main Breaker	42
225	30	42	W3042L1225GEN	Main Lug	42





GENTERSWITCH



① Q2125S provided with GENTFRSWTCH for use with automatic transfer mechanism.

^{2 2} spaces and 2 circuits are reserved for standby generator installation.

③ Field install breaker for voltage sensing required.

① Indoor enclosures are 14 1/4" wide by 3 7/8" deep. ⑤ Outdoor enclosures are 14 1/2" wide by 4 1/4" deep.

Siemens Industry, Inc. Residential Load Centers Selection & Application Guide

Riser Panel Load Centers

1-Phase, 3-Wire SN, 120/240 Volts AC

Riser Panel Load Centers®

Riser panel load centers are ideal for high rise applications. The shifted interior provides room for conductors to pass through the load center. The tap kits allow the installer to tap off from those conductors to power the panel.

Features

- UL Listed for use in 1Ø and 3Ø riser gutter applications.
- · Copper bus standard.
- Main lug factory standard convertible to main breaker.
- Neutrals aligned on left side- keeps way clear for riser cables.
- Available in 125 and 200 amp models.
- Invertible for left and right hand applications.



The riser gutter tap kit (ECRLK250) allows the installer to tap off the main conductors, eliminating the need to cut completely through the conductor. The tap kit accepts 250 -1/0 on the main conductor side and 250-#6 on the tap side.



The riser gutter (RAG24) is used to convert any load center 24" or larger into a riser panel.

Features

- Single and 3-phase applications
- · Compatible with any single or 3-phase Siemens load center 24" or higher
- · Flush trim included
- · Load center mounting hardware and pass through brush included (Catalog no. RAG24)









Any Load Center 24" or larger



RAG24

1-phase, 3-wire SN, 120/240 Volts AC

			Catalog Number				Dimens	ions (inc	hes)	
Amp Rating	No. of Spaces	No. of Circuits	Aluminum Bus	Aluminum Bus White Coating	Copper Bus	Copper Bus White Coating	Height	Width	Depth	Acceptable Main Breaker Kits
125	16	32	R1632L1125	R1632L1125W	R1632L1125CU	_	24	14.25	3.88	MBK100A,MBK125A
125	24	24	R2424L1125	R2424L1125W	R2424L1125CU	_	30	14.25	3.88	MBK100A, MBK125A
125	24	42	R2442L1125	R2442L1125W	R2442L1125CU	R2442L1125CUW	30	14.25	3.88	MBK100A, MBK125A
200	30	42	R3042L1200	R3042L1200W	R3042L1200CU	R3042L1200CUW	36	14.25	3.88	MBK150A, MBK200A

① The riser panels are single phase only, but can be fed from 1-phase or 3-phase systems running through the gutter trough area. © ECRLK250 is sold separately.

EQ® Load Centers, Small Circuit and Circuit Breaker Enclosures

1-Phase, 3-Wire SN, 120/240 Volts AC

Features/Applications

- Indoor and Outdoor Applications
- UL Listed
- 2 to 12 Space Options
- SPA panels offer a 50A or 60A factory installed GFCI breaker
- · Service Entrance or Subfeed **Applications**



Small Circuit Load Centers

Ideal for subfeed applications



Renovation Panel

Ideal for older home renovation projects where the distance between the studs is narrower than current construction practices. The narrower panel eliminates the need to 'notch' out the existing studs.



Spa Panels

Spa Panels are ideal for outdoor applications requiring the use of ground fault protection, such as hot tubs. A factory installed 2-Pole GFCI breaker is provided, along with 2 extra circuits.

			Indoor Enclosure - NEMA	Type 1							
Amp			Siemens	Max Short Circuit Rating	Bus Material	Mauntina	Phase Lug Wire Size	Ground Bar		W I 12.3 3 12.3 3 12.3 3 12.3 3 12.3 12.3 3 12.3	ches)
Kating	Spaces 10	20	Catalog Number E1020MB1100FCGP ⁰³³			Mounting Flush	wire Size	Ground Bar		1	3.7
100	10	20	E1020MB1100FCGP	22,000	Copper Aluminum	Flush	CU or AL	ECGB10 Installed		_	3.7
100	12	24		100,000		Flush	#4 - 2/0 AWG	Use ECGB kits	-	W 12.3 12.3 12.3 6.5 6.5 12.3 12.3 12.3 12.3 12.3 12.3 12.3 12.3	3.7
			E1224ML1100FCU®®	100,000	Copper			USE ECGB KITS	-	W 12.3 12.	
	4	8	E0408ML1125F®7®9®	100,000	Aluminum	Flush	AL #12 - 2/0 AWG or CU #14 - 2/0 AWG			8 6.5 8 6.5 6 12.3 6 12.3 6 12.3 6 12.3 6 12.3 6 12.3 6 12.3	3.3
			E0408ML1125S®0®0®	100,000	Aluminum	Surface ⁱ	CU #14 - 2/0 AWG	Use ECGB or	14.6 12.3 14.6 12.3 14.6 12.3 14.6 12.3 12.8 6.5 12.8 6.5 14.6 12.3 14.7 12.1 6.2 12.1 6.2 14.7 12.1 20.0 11.1	3.3	
			E0816ML1125F®	100,000	Aluminum	Flush		ECLX kits		3.7	
425			E0816ML1125S ²⁰	100,000	Aluminum	Surface				12.3	3.7
125	8	16	E0816ML1125FGB®	100,000	Aluminum	Flush	CU or AL #4 - 2/0 AWG	ECGB10 or ECLX071M Installed	14.6	12.3	3.7
			_	100,000	Aluminum	Surface	#4 - 2/0 AVVG	ECLX071M Installed	14.6	12.3	3.7
			E0816ML1125FCU®	100,000	Copper	Flush		Use ECGB kits	14.6	12.3	3.7
			E0816ML1125SCU®	100,000	Copper	Surface		USE ECGB KILS	14.6	12.3	3.7
			Outdoor Enclosure - NEM	/IA Type 3R							
Amp	No. of	No. of	Siemens	Max Short			Phase Lug		Dimen	sions (in	ches)
Rating	Spaces	Circuits	Catalog Number	Circuit Rating	Bus Material	Hub Provision	Wire Size	Ground Bar	Н	W	D
100	2	4	W0204MB1100 ³⁰	100,000	Aluminum	1.25" HS Hub		Use ECGB or	12.1	6.2	4.4
			W0408ML1125®®®®	100,000	Aluminum		AL #12 - 2/0 AWG or	ECLX kits	12.1	6.2	4.4
	4	8	W0408L1125SPA50®®	100,000	Aluminum	1	CU #14 - 2/0 AWG	ECGB5 Installed	12.1	6.2	4.4
125			W0408L1125SPA60®®	100,000	Aluminum	1		ECGBS Installed	12.1	6.2	4.4
	8	16	W0816ML1125CU ^{©®}	100,000	Copper	HS Cover Plate		Use ECGB or ECLX kits	14.7 12.1		4.1
150	4	4	W0404MB1150CTS®	22,000	Copper	1			20.0	11.1	4.7
		0		100,000	Aluminum]	CU or AL #4 - 2/0 AWG		20.0	11.1	4.7
200	4	8	_	100,000	Aluminum	- 2" HS Hub	1 #4 - 2/U AWG	ECLX384M Installed	20.0	11.1	4.7
200	4	4	W0404MB1200CT®®	22,000	Copper	12 H3 HUD			20.0	nsions (inch W	4.7
		4	W0404MB1200CTS®®	22,000	Copper	HS Cover Plate]			4.7	

① Suitable for use as service equipment when a main breaker (100A maximum) is used with retainer clip (Cat. No. ECMBR1).

② Two Q115 and one Q130 included ③ 22KAIC Main Breaker factory installed

^{@ 70} amp maximum breaker.

[©] Suitable for use as service entrace equipment when a main breaker (70A maximum) is used with reatiner clip (Cat. No. ECMBR1).

[®] Will not accommodate a 2-pole circuit breaker with shunt trip.

② Suitable for use as service equipment when not more than six main disconnecting means are provided. Check local codes and restrictions.

[®] Packaged in quantities of 5.

^{10 10} KAIC Main Breaker factory installed

[@] I2-pole 60A GFCI, a restriction of #6 wire applies due to wire bend space of the enclosure.

[®] Suffix SPA50 indicates a factory installed 50A 2-pole GFCI and suffix SPA60 indicates a factory installed 60A 2-pole GFCI.

[@] Suitable only for use as service equipment.

EQ® Load Centers, Small Circuit and Circuit Breaker Enclosures

1-Phase and 3-Phase, 240V AC Max.

Features

- Circuit breaker enclosures range from 60A to 250A, indoor and outdoor models
- UI listed
- Suitable for use as service entrance equipment
- UL listed for 60/75°C Conductors (See equipment markings for applications)
- Outdoor type 3R devices use HS type hubs (pg. 1-22) except for the W0204ML1060 which uses HA type hubs





		Indoor Enclosure - NEMA Type 1							Outdoor Enclosure - NEMA Type 3R						
				Max Short		Dimensions (inches)		S			Max Short		Dime (inch		ns
	No. of Poles	Catalog Number	Breaker Used ^①	Circuit Rating	Std. Pkg.	Н	w	D	Catalog Number	Breaker Used ^①	Circuit Rating	Std. Pkg.	Н	w	D

1-Phase, 3-Wire SN - 120/240 Volts AC - Breaker Factory Installed

100	2	E0202MB1100	Q2100	22,000	1	17.3	7.3	4.3	W0202MB1100CU	Q2100	22,000	1	17.2	7.3	4.3
150	2	_	_		_	_	_	_	W0202MB1150CU	QN2150H	65.000	1	10.0	8.7	_
200	2	E0202MB1200	QN2200	22,000	1	20	8.7	4	W0202MB1200CU	QN2200H	65,000	1	19.8		5
150	2	_	_		_	_	_	_	WB2150BQR	QR22B150L					
200	2	_	_	_	_		_	_	WB2200BQR	QR22B200L	10,000	1	26.9	7.1	4.4
225	2	_	_	_	_	I—	_	_	WB2225BQR	QR22B225L					

1-Phase, 3-Wire SN - 120/240 Volts AC - Enclosure Only

60	12	E0204ML1060S24	QP, QPH, or HQP 1	100,000®	5	9.9	5.2	2.7	W0204ML1060 ²	QP, QPH, or HQP	100.000®	_	8.1	5.5	3.5
60		E0204ML1060F@4				9.9	5.2	2.7	_	_	100,000	٥	0.1	5.5	3.5
125	2	E0204ML1125SCU ³	OP or OPH	22,000	1	17.3	7.3	.3 4.3	W0204ML1125CU ³	QP or QPH	22,000	1	17.2	7 2	4.3
123		E0204ML1125FCU ³	QF OF QFH		'	17.3	7.3		_	_	22,000	'	17.2	/.5	4.3
200	2	_	_		_	_	_	_	W0202ML1200CU	QN, QNH, or HQN	65,000	1	19.8	8.7	5
225	1-4	_	_	1	_	_	_	_	W0406ML1225CU	QPP or QP	10,000	1	23.2	10.4	4.5
223	2	_	_	1	_	_	_	_	QR2N3R2	QR2, QRH2, or HQR2	65,000	1	26.9	7.1	4.4
250	12 H	QR2N1S	QR2, QRH2,	100.000	1	31.4	9.6	5.6	_	_	_	_	_	_	—
250		QR2N1F	HQR2, or HQR2H	100,000	<u> </u>	31.4		5.6	_	_	_		_	—	-

		, -								,	,					
	100	2-3	E0303ML3100S [®]	QP or QPH	22,000	000 1	17.3	7.3	143 F	W0303ML3100 [©]	QP or QPH	22.000	1	17.2	7.3	4.3
	100		EB3100S ^⑤	BQ or BQH	22,000					WB3100 [®]	BQ or BQH	22,000	<u> </u>	17.2		4.5
	250	2-3	QR2N1S	QR2, QRH2, HQR2, or HQR2H	100,000	1	31.4	9.6	5.6	QR2N3R3	QR2, QRH2, HQR2, or HQR2H	100,000	1	31.4	9.6	5.6
			QR2N1F	nqkz, or nqkzn						_	_	_	_	_	_	_

① Additional breaker types may be listed on the wiring diagram.

② Will not accommodate 2-pole GFCI or Circuit breaker with shunt trip.

shunt trip.

3 Can accommodate 2-pole GFCI breaker up to 60A.

[@] CSA Listed

 $[\]ensuremath{\texttt{\textcircled{0}}}$ Will not accommodate circuit breaker with shunt trip.

[®] Series rating

Renovation Interiors

1 Phase, 3 WIRE, 120/240V


Features

- For use in home renovations with existing load centers[®]
- Suitable for use in indoor Type 1 Enclosure
- Interior, Flush Cover, and Hardware included
- · Adjustable depth
- Incoming lugs: 2/0 #4 AWG
- UL listed





Amp	No. of	No. of		Min. Enclosure Size (inches)			Max. Enclosure Size (inches)			Cover Dimensions (inches)	
Rating	Spaces	Circuits	Catalog Numbers	L	W	D ^②	L	W	D ^②	L	W
100	8	16	RE0816ML1100J	13.00	10.50	3.75	19.00	14.25	6.00	22.00	18.00
100	8	16	RE0816ML1100K	20.00	10.50	3.75	26.00	14.25	6.00	29.00	18.00
125	12	24	RE1224ML1125J	17.00	12.25	3.75	21.00	14.25	6.00	23.00	18.00
125	12	24	RE1224ML1125K	22.00	12.25	3.75	26.00	14.25	6.00	29.00	18.00



① Existing enclosure must mearsure within listed

dimensions for the use of the kit.

② Depth of enclosure is measured from finished wall

Load Center Accessories¹

Ground bar kits, hubs, lugs, and conversion kits

Catalog Number	Description	Pack Qty							
Ground Bar	Ground Bar Kits								
EC1GB8	GROUND BAR KIT-8 POS	1							
EC1GB82	GROUND BAR KIT-8 POS, 2/0 LUG	1							
EC2GB12	GROUND BAR KIT-12 POS	1							
EC2GB122	GROUND BAR KIT-12 POS, 2/0 LUG	1							
EC2GB15	GROUND BAR KIT-15 POS	1							
EC2GB152	GROUND BAR KIT-15 POS, 2/0 LUG	1							
EC3GB21	GROUND BAR KIT-21 POS	1							
EC3GB212	GROUND BAR KIT-21 POS, 2/0 LUG	1							
EC3GB27	GROUND BAR KIT-27 POS	1							
EC3GB272	GROUND BAR KIT-27 POS, 2/0 LUG	1							
EC3GB30	GROUND BAR KIT-30 POS	1							
EC3GB302	GROUND BAR KIT-30 POS, 2/0 LUG	1							
EC3GB352	GROUND BAR KIT-35 POS, 2/0 LUG	1							
EC3GB352G	GROUND BAR KIT-35 POS, 2/0 LUG ²	1							

Ground Bar Kits (For Legacy Load Centers)

ECGB5	GROUND BAR KIT-5 POS	1
ECGB10	GROUND BAR KIT-10 POS	1
ECGB101	GROUND BAR KIT-10 POS, 1/0 LUG	1
ECGB14	GROUND BAR KIT-14 POS	1
ECGB141	GROUND BAR KIT-14 POS, 1/0 LUG	1
ECGB142	GROUND BAR KIT-14 POS, 2/0 LUG	1
ECGB20	GROUND BAR KIT-20 POS	1
ECGB201	GROUND BAR KIT-20 POS, 1/0 LUG	1
ECGB202	GROUND BAR KIT-20 POS, 2/0 LUG	1
ECINSGB5	INSULATED GROUND BAR KIT-5 POS	1
ECINSGB14	INSULATED GROUND BAR KIT-14 POS	1
ECINSGB20	INSULATED GROUND BAR KIT-20 POS	1

Hubs

11483			
ECHA000		CLOSURE PLATE	1
ECHA075	1	HUB - 3/4"	1
ECHA100	HA Type W0204ML1060	HUB - 1"	1
ECHA125	W0204WIL1000	HUB - 1 1/4"	1
ECHA150]	HUB - 1 1/2"	1
ECHS000		CLOSURE PLATE	1
ECHS075		HUB - 3/4"	1
ECHS100	HS Type	HUB - 1"	1
ECHS125	PL & ES and Small Circuit	HUB - 1 1/4"	1
ECHS150	Loadcenters	HUB - 1 1/2"	1
ECHS200		HUB - 2"	1
ECHS250		HUB - 2 1/2"	1
ECHV000		CLOSURE PLATE	1
ECHV200		HUB - 2"	1
ECHV250	HV Type 300-400A	HUB - 2.5"	1
ECHV300	Loadcenters	HUB 3"	1
ECHV350		HUB - 3.5"	1
ECHV400		HUB - 4"	1

Lock Kits

ECQFL2	FLUSH LOCK KIT FOR ULT., PL, ES, 3PH 100A-225A	1
ECQFL1	FLUSH LOCK KIT-REPLACEMENT FOR EQ LC	1
ECQFL3	ADD-A-LOCK (FLUSH LOCK) FOR 300-400A LC	1

The pack quantity is the number that is sold in a pack. Items listed on this page must be ordered in multiples of pack quantities but items are priced per each. For example, ECRLK250 come 3 to a pack so must be ordered in multiples of 3 but pricing would be individual unit price times 3.
 Bar has green-colored screws.

Catalog Number	Description	Pack Qty
Load Center	Conversion Kits ³⁴	
MBK100A	MAIN BREAKER KIT 100A 1PH 22K	1
MBK125A	MAIN BREAKER KIT 125A 1PH 22K	1
MBK150A	MAIN BREAKER KIT 150A 1PH 22K	1
MBK200A	MAIN BREAKER KIT 200A 1PH 22K	1
MBK225A	MAIN BREAKER KIT 225A 1PH 22K	1
MBK3100	MAIN BREAKER KIT 100A 3PH QP 240V 10K	1
MBK3125R	MAIN BREAKER KIT 125A 3PH 240V 10K, QR	1
MBK3150R	MAIN BREAKER KIT 150A 3PH 240V 10K, QR	1
MBK3175R	MAIN BREAKER KIT 175A 3PH 240V 10K, QR	1
MBK3200R	MAIN BREAKER KIT 200A 3PH 240V 10K, QR	1
MBK3225R	MAIN BREAKER KIT 225A 3PH 240V 10K, QR	1
MBK3125HR	MAIN BREAKER KIT 125A 3PH 240V 22K, QR	1
MBK3150HR	MAIN BREAKER KIT 150A 3PH 240V 22K, QR	1
MBK3175HR	MAIN BREAKER KIT 175A 3PH 240V 22K, QR	1
MBK3200HR	MAIN BREAKER KIT 200A 3PH 240V 22K, QR	1
MBK3225HR	MAIN BREAKER KIT 225A 3PH 240V 22K, QR	1
MBK3125HHR	MAIN BREAKER KIT 125A 3PH 240V 65K, QR	1
MBK3150HHR	MAIN BREAKER KIT 150A 3PH 240V 65K, QR	1
MBK3175HHR	MAIN BREAKER KIT 175A 3PH 240V 65K, QR	1
MBK3200HHR	MAIN BREAKER KIT 200A 3PH 240V 65K, QR	1
MBK3225HHR	MAIN BREAKER KIT 225A 3PH 240V 65K, QR	1
HMBK3125HR	MAIN BREAKER KIT 125A 3PH 240V 100K, QR	1
HMBK3150HR	MAIN BREAKER KIT 150A 3PH 240V 100K, QR	1
HMBK3175HR	MAIN BREAKER KIT 175A 3PH 240V 100K, QR	1
HMBK3200HR	MAIN BREAKER KIT 200A 3PH 240V 100K, QR	1
HMBK3225HR	MAIN BREAKER KIT 225A 3PH 240V 100K, QR	1
ECMLK125	1 PH MAIN LUG CONVERSION KIT 100-125A	1
ECMLK225	1 PH MAIN LUG CONVERSION KIT 150-225A	1
ECMLK3125	3 PH MAIN LUG CONVERSION KIT 100-125A	1
ECMLK3225	3 PH MAIN LUG CONVERSION KIT 150-225A	1

Lug Kits

ECCS1	COLLAR STRAP FOR GRD BARS #14-1/0	1
ECCS2	COLLAR STRAP FOR GRD BARS #6-250	1
ECLKB1	NEUTRAL LUG KIT WITH BOND TAB	1
ECLK3	NEUTRAL LUG KIT #1-300	1
ECLK1-2	NEUTRAL LUG KIT #2 TO 1/0	1
ECLK2N	NEUTRAL LUG KIT #4-2/0	1
ECLK3N	NEUTRAL LUG KIT #1-300	1
ECLK2	NEUTRAL LUG KIT #4-2/0	1
ECLK2SC	2/0 LUG FOR 125AMP NEUTRAL FEEDER	1
ECLK2125	125A SUB FEED LUGS-USES 2 SPACES	1
ECLK2225	150A-225A SUB FEED LUGS-USES 4 SPACES	1
ECLK3225	3P SUB FEED LUGS-USES 6 SPACES	1
ECRLK250	RISER LUG KIT 250 KCMIL	3

Miscellaneous Load Center Accessories

100 5 1
5 1
1
1
ı
1
4
6
6
100
100
25
10
4
1
10

③ QR Main Breaker Kits include a QR filler plate.

Main Breaker Kits include line terminal barriers.

Load Center Accessories

Miscellaneous Load Center Accessories



Lug Kit, 3-Pole, Subfeed or Feed thru Applications ECLK3225



2 PH Main Lug Conversion Kit 150A-225A ECMLK225



Main Breaker Kit 200A - 225A, 1PH 22K **MBK200A**



3-Pole Main Breaker Kit MBK3200



Main Breaker Retainer Kit for EQ Load Centers ECMBR1



Main Breaker Retainer kit for PN, SN, PL, ES, & Ultimate Load Centers ECMBR2



Ground Bar Kit 20 POS. 2/0 Lug ECGB202



Ground Bar Kit, ECGB14



Neutral Lug Kit, ECLK1-2 wire range — #2-1 AWG Cu or Al



Neutral Lug Kit, ECLK3 wire range — #1-300 MCM Neutral Lug Kit, ECLK2 wire range — #4-#2/0 AWG Cu or Al



For use on Ground Bar only Collar Strap, Wire Range; ECCS1; ECCS2



Add-A-Lock (Flush Lock) **ECQFL1** For EQ load centers



Filler Plate, ECQF3



Add-A-Lock (Flush Lock), **ECQFL2** PN, SN, PL, ES, Ultimate Load Centers and EQ III up to 225A



Add-A-Lock (Flush Lock), **ECQFL3** 300-400A Load Centers

Load Center Accessories

Load Center and Meter Combos Accessories

Load centers and meter combos

Touchsafe barriers are required for any single main service entrance application for a panel covered under UL 67. Line Terminal Barriers will be included in Main Breaker Load Centers and Single Main Meter Combos manufactured after January 1, 2017.

Single phase and 3-phase main breaker kits will include a barrier. Field installable kits are being created for replacements if needed and line terminal barriers are being added to hold down kits that can be used in back-fed applications. The barriers are designed to have minimal interference during load center installation, and can be removed and reattached as necessary.



Catalog number	Description
ECLTB1	For EQ Main Breakers/MBK kits 100A-125A
ECLTB2	For EQ Main Breakers/MBK kits 150A-225A
ECLTB3	For QN / QNR type breakers
ECLTB4	For QR 3 phase breakers
ECMBR1 ^①	For 2 Pole QP / MP-T type breakers for EQIII (extruded basepan) and Line 5
ECMBR2®	For 2 Pole QP / MP-T type breakers to be used with PN, SN, ES, PL, Ultimate, and legacy Murray or Rock Solid load centers
ECMBR3	For 3 Pole QP / MP-T type breakers to be used with PL, ES 3 phase load centers
ECLX387HD	For 2 Pole MP-T type breakers in legacy Murray load centers

⁽¹⁾ Barrier fits with 2-pole QP 70A and above and all amperages of QPH and HQP.

Load Center Accessories

Manual Transfer Interlock Kits for Load Centers and Meter Combinations

Prevents dangerous feedback between two sources of power

Manual Transfer Interlock Kits^①

Catalog number		Usage Information	Utility main breaker types	Standby main breaker types	Interlock Number
	ECSBPK01	For use on load centers or meter combinations that will accept 2-pole circuit breakers opposite one another as shown.	QР, QРН, НQРН	QР, QРН, НQРН	1
	ECSBPK02	For use on load centers or meter combinations that will accept 2- or 4-pole next to a 2-pole circuit breaker side by side as shown.	QР, QРН, НQРН	QP, QPH, HQPH	2
	ECSBPK03 [©]	For use on Ultimate™ and Rock Solid load centers, 150 amp and higher, to connect the main breaker to a 2-pole circuit breaker.	MBK150A, MBK200A, OR MBK225A	QР, QРН, НQРН	3
	ECSBPK10	For use on PN and SN plug-on neutral load centers, 150 amp and higher, to connect the main breaker to a 2-pole circuit breaker.			
	ECSBPK04 [©]	For use on Ultimate™ and Rock Solid load centers, 125 amp and lower, to connect the main breaker to a 2-pole circuit breaker.	MBK100A or MBK125A	QР, QРН, НQРН	4
	ECSBPK11	For use on PN and SN plug-on neutral load centers, 125 amp and lower, to connect the main breaker to a 2-pole circuit breaker.			F. 1
	ECSBPK05	For use on load centers or meter meter combinations that will accept a QNR (MD-TR) frame circuit breaker next to a 2-pole circuit breaker as shown.	QNR, QNRH, HQNR	QP, QPH, HQPH	5
	EECSBPK06®	For use on load centers or meter combinations that will accept a QN (MD-T) frame circuit breaker next to a 2-pole circuit breaker as shown.	QN, QNH, HQN	QР, QРН, НQРН	6
	ECSBPK07	For use on load centers or meter combinations that will accept two QNR (MDTR) circuit breakers side by side as shown OR will accept two QN (MDT) circuit breakers side by side as shown.	QNR, QNRH, HQNR, QN, QNH, HQN	QNR, QNRH, HQNR QN, QNH, HQN	

① Manual breaker interlock kits are attached to the breakers not the trim of the load center.

③ These kits take up 2 spaces adjacent to the 2 pole breaker being interlocked. Those spaces cannot accommodate filler plates.

Arc-Fault and Ground-Fault Breakers

Arc-Fault Circuit Interrupters (AFCI)

AFCI's detect arcing faults (an unintentional arcing condition in a circuit) that standard circuit breakers are not designed to detect. The device is intended to mitigate the effects of arcing faults by functioning to de-energize the circuit when an arc-fault is detected.

Combination Type AFCI

Detects all three possible types of arc faults: line-to-ground, line-to-neutral, and series.

Breaker	Amp	10,000 A IR	22,000 A IR	65,000 A IR
Type	Rating	Catalog No.	Catalog No.	Catalog No.
QAF2/QAFH2/HQAF2	15	QA115AFC [®]	QA115AFCH [®]	QA115AFCHH∎ ^①
1-Pole 120V AC	20	QA120AFC [®]	QA120AFCH [®]	QA120AFCHH ■ ^①
QAF/QAFH	15	Q215AFC [®]	Q215AFCH∎ ^①	
2-Pole 120/240V AC	20	Q220AFC [®]	Q220AFCH∎ ^①	
QAF2N Plug-on Neutral/1-Pole 120V AC	15 20	QA115AFCN QA120AFCN		_
QAF/QAFH Plug-on Neutral/2-Pole 120/240V AC	15 20	Q215AFCN Q220AFCN	_	_



The Dual Function Circuit Breaker combines Combination Type AFCI and 5mA GFCI protection in one device. The device includes the Self Test feature, making it the first in class in electrical safety for homeowners.

QFGA2/QFGAH2/HQFGA2 1-Pole 120V AC	1	Q115DF ^① Q120DF ^①	` '	Q115DFHH∎ ^① Q120DFHH∎ ^①
OFGA2N	15	Q115DFN	_	_
Plug-on Neutral/1-Pole 120V AC	20	Q120DFN	_	_

Ground-Fault Circuit Interrupters (GFCI)

Provides Class A (5mA) ground fault protection. Intended for personnel protection. Includes Self Test as an added safety feature.

	Amp	10,000 A IR	22,000 A IR	65,000 A IR
Breaker Type	Rating	Catalog No.	Catalog No.	Catalog No.
QPF2/QPHF2/HQPF2	15	QF115A ^①	QF115AH∎ ^①	QF115AHH∎ ^①
	20	QF120A ^①	QF120AH∎ ^①	QF120AHH∎ ^①
1-Pole 120V AC	30	QF130A ^①	QF130AH∎ ^①	QF130AHH∎ ^①
	15	QF215A	QF215AH∎	_
	20	QF220A	QF220AH∎	_
QPF/QPHF	30	QF230A	QF230AH∎	-
2-Pole 120/240V AC	40	QF240A	QF240AH■	-
	50	QF250A	QF250AH∎	_
	60	QF260A	QF260AH■	_
0.05.011	15	QF115AN	_	_
QPF2N Plug-on Neutral/1-Pole 120V AC	20	QF120AN	_	
Flug-off Neutral/1-Pole 120V AC	30	QF130AN	_	_

Ground Fault Equipment Protection (30mA)

Provides protection of equipment from damaging line-to-ground faults currents.

QE/QEH 1-Pole 120V AC	15 20	QE115 QE120	QE115H■ QE120H■	_
TTOIC 120V AC	30	QE130	QE130H ■	<u> </u>
	15	QE215	QE215H■	_
	20	QE220	QE220H■	_
QE/QEH	30	QE230	QE230H■	_
2-Pole 120/240V AC	40	QE240	QE240H■	_
2 1 010 120/2 10 1 110	50	QE250	QE250H■	 —
	60	QE260	QE260H ■	_

QAF2/QPF/QE/QPF2 Accessories

Description	Catalog Number ^①
Padlocking Device 1-Pole	ECPLD1
Padlocking Device 2-Pole	ECPLD2
Handle Block	ECBX231M

■ Built to order. Allow 8 -10 weeks for delivery.

① UL Listed as SWD (Switching Duty) Rated, suitable for 120V AC Fluorescent Lighting.



1-Pole Combination Type AFCI



Pole Combination:
Type AFCI





1-Pole AFCI Plug-on Neutral



1-Pole Dual Function Plug-on Neutral







1-Pole Equipment Protection



2-Pole Equipment Protection

Circuit Breakers

Type QP with INSTA-WIRE

	Type QP ^①	Type QPH	Type HQP
Continuous Current	10,000A IR	22,000A IR	65,000A IR
Rating @ 40° C	Catalog Number	Catalog Number	Catalog Number

1-Pole Plug-In (120/240V AC)⁽⁵⁾

i i oic i iug iii	(120/2101/10)			
10	Q110 [®]	_	_	
15	Q115 ³	Q115H ³	Q115HH ■ ③	
20	Q120 ³	Q120H ³	Q120HH ■ ③	
25	Q125	Q125H ■	Q125HH ■	
30	Q130	Q130H	Q130HH ■	
35	Q135 ■	Q135H ■	Q135HH ■	
40	Q140	Q140H	Q140HH ■	
45	Q145 ■	Q145H ■	Q145HH ■	
50	Q150	Q150H	Q150HH ■	
60	Q160	Q160H ■	Q160HH ■	
70	Q170	Q170H ■	Q170HH■	

2-Pole Plug-In (Common-Trip 120/240V AC)[®]

2-1 ole i lug-ili (Collilli	711 111p 120/240 V AC	·/ -	
10	Q210 [®]	_	_
15	Q215	Q215H	Q215HH
20	Q220	Q220H	Q220HH
25	Q225	Q225H ■	Q225HH ■
30	Q230	Q230H	Q230HH
35	Q235	Q235H ■	Q235HH ■
40	Q240	Q240H	Q240HH ■
45	Q245	Q245H ■	Q245HH ■
50	Q250	Q250H	Q250HH
60	Q260	Q260H	Q260HH
70	Q270	Q270H	Q270HH
80	Q280	Q280H ■	Q280HH ■
90	Q290	Q290H	Q290HH ■
100	Q2100	Q2100H	Q2100HH
110	Q2110	Q2110H	Q2110HH ■
125	Q2125	Q2125H	Q2125HH



	Q215R		
	Q220R	_	-
	Q230R	_	-
	Q240R	_	-
50	Q250R	_	_

3-Pole Plug-In (Common-Trip 240V AC)

	common mp 240 v	<u>-, </u>		
15	Q315	Q315H	Q315HH ■	
20	Q320	Q320H	Q320HH	
25	Q325	Q325H ■	Q325HH ■	
30	Q330	Q330H	Q330HH	
35	Q335	Q335H ■	Q335HH ■	
40	Q340	Q340H	Q340HH	
45	Q345	Q345H ■	Q345HH ■	
50	Q350	Q350H	Q350HH	
60	Q360	Q360H	Q360HH	
70	Q370	Q370H	Q370HH ■	
80	Q380	Q380H	Q380HH ■	
90	Q390	Q390H	Q390HH ■	
100	Q3100	Q3100H	Q3100HH	







QP / QPH / HQP Internal Accessories

Control Voltage AC	Catalog Number	Field/Factory Installed
120V Shunt Trip	add suffix00S01■	Factory
24V Shunt Trip	add suffix00S07■	Factory
120V Auxiliary Switch	add suffix01∎ ^②	Factory

■ Built to order. Allow 2-3 weeks for delivery.

① UL Listed for use with 60/75° wire through 40 amps, UL listed for use with 75° wire only for 50 amps

and above, HACR rated. ② 1A and 1B contacts.

Modifications

Description	Catalog Number	
400 Hz Calibration	add suffixY®	
Marine 50°C Ambient Calibration	add suffixM	
Fungus Proofing	add suffixF	

 $[\]ensuremath{\mathfrak{D}}$ UL Listed for frequent switching applications (SWD).

¹² UL Listed for use on 3-phase grounded "B" systems —

^{10,000} for this application. ⑤ Shipped 12 per sleeve.

Shipped 6 per sleeve.
 Shipped 4 per sleeve.
 UL Listed 5 KA IR.
 Type QP1, UL listed for 16 AWG conductors and multiple wires.

Circuit Breakers

Duplex, Triplex and Quadplex Plug-In Breakers

Duplex Circuit Breakers


Breaker Type	Ampere Rating	Catalog Number	Catalog Number			
QT	15–15	Q1515	Q1515NC ^①			
1-Pole	15-20	Q1520	Q1520NC ^①			
10K AIC	20-20	Q2020	Q2020NC ^①			
120V AC	20-30	Q2030	_			
	30-15■	Q3015	_			
	30-20	Q3020	_			
	30-30	Q3030	Q3030NC ^①			
	SHIPPING: 12 per carto	SHIPPING: 12 per carton, (Wt. 4.8 lbs.)				

Triplex Circuit Breakers

	Ampere Rating	Ampere Rating		
Breaker Type	Single Pole	Common-Trip 2-Pole	Catalog Number	
QT	15	15	Q21515CT	
2-Pole	15	20	Q21520CT	
10K AIC	15	25	Q21525CT■	
120/240V AC	15	30	Q21530CT	
Inner Poles	15	35	Q21535CT■	
Common Trip	15	40	Q21540CT	
	15	45	Q21545CT■	
	15	50	Q21550CT	
	20	20	Q22020CT	
	20	25	Q22025CT■	
	20	30	Q22030CT	
	20	35	Q22035CT■	
	20	40	Q22040CT	
	20	45	Q22045CT■	
	20	50	Q22050CT	
	30	30	Q23030CT	
	SHIPPING: 6 per carton	, (Wt. 4.9 lbs.)		

Quadplex Circuit Breakers


	Ampere Rating		
Breaker Type	Common-Trip 2-Pole Outside	Common-Trip 2-Pole Inside	Catalog Number
QT	15	15	Q21515CT2
2-Pole	15	30	Q21530CT2
10K AIC	20	20	Q22020CT2
120/240V AC	20	50	Q22050CT2
Inner and	30	20	Q23020CT2
Outter 2 Poles	30	25	Q23025CT2
Common Trip	30	30	Q23030CT2
	30	50	Q23050CT2
	40	20	Q24020CT2
	40	30	Q24030CT2
	40	40	Q24040CT2
	SHIPPING: 6 per carton, (Wt. 4.8 lbs.)		




QT Duplex

These space saver duplex breakers combine two independent 1/2" breaker poles in a common unit.

This unit plugs into one load center stab and requires one panel space. HACR rated.



These space saver triplex breakers provide a 2-pole common trip breaker for 120/240V AC circuits and two single poles for 120V AC circuits. Triplex require two panel spaces. HACR rated.



QT Quadplex

These space saver quadplex breakers provide two sets of common trip, two-pole breakers for 120/240V AC circuits, and require two panel spaces. HACR rated.

 $[\]blacksquare$ Built to order. Allow 2–3 weeks for delivery.

Surge Protection

Circuit Breaker and Surge Protective Device (SPD)

Features

- 2 inch wide plug-on design
 - Includes (2) 1 Pole circuits breakers
 - No loss of load center spaces
- · Easy to install and perfect for retrofit
- · LEDs provide protection status

Benefits

By installing a Siemens Circuit Breaker and Surge Protective Device (SPD) in the load center of the residence, surge protection is provided for all branch circuits.

Two green LED indicator lights are provided to show that surge protection is provided for all circuits connected to the load center. These breakers should be used for circuit protection of frequently used household or facility circuits because the lights and devices connected to these circuits provide an effective indication that surge protection is being provided.

The circuit breaker and SPD utilize Siemens-built 150V AC, 40mm, metal oxide varistors (MOVs). The maximum impulse rating for the SPD module is 40kA. The standard interrupting rating for the circuit breakers is 10k AIC. All Type QP circuit breakers and SPD are plug-on style, with load terminals provided. The devices are rated for 120/240V AC and are calibrated for 40 degrees C maximum ambient applications.

Breaker Type	Ampere Rating	Catalog Number	Surge Type
QP 1- Pole	(2) 15	QSA1515SPD	SPD
120/240V AC 10K AIC	(2) 20	QSA2020SPD	SPD

Catalog Number	QSA1515SPD QSA2020SPD
Amperage	15 or 20 Amp
Number of Poles	(2) 1-Pole Circuit Breakers
Initial Clamping Level	240 Volts
Transient Energy Rating	360 Joules line-to-neutral 720 Joules line-to-line
Transient Suppression	500 volts peak, line-to-neutral
Voltage Rating	1000 volts peak, line-to-line
Peak Current Rating (impulse)	40,000 amperes
Discharge Voltage Characteristic	@ 1,500A, 600 volts @ 5,000A, 800 volts (both line-to-neutral)
Discharge Current Withstand Rating	10,000 amperes line-to-neutral
Circuit Breaker Interrupting Rating	10,000A, 120/240V AC
Listings/Certifications	UL, CSA Meets UL 1449 4th Edition



Surge Protection


Power Service Entrance Surge Protection


FirstSurge[™] - Power, Plus, or Pro

- · 4th Listed, Type 2, Surge Protective Device (SPD
- · Surge Current Capacities:
 - 60,000 A, First Surge Power (FS060)
 - 100,000 A, First Surge Plus (FS100)
 - 140,000 A, FirstSurge Pro (FS140)
- 3 Stage Commercial Grade Notification:
 - Protection Status LEDs
 - Audible Alarm
 - Flashing Red Service LED
- Ground Reference Monitoring (GRM)
- 10 year product & connected equipment warranty*
- * See www.usa.siemens.com/surge for warranty terms and conditions.

Surge Type	Catalog Number
FirstSurge Power	FS060
FirstSurge Plus	FS100
FirstSurge Pro	FS140

AC Surge Protection	
UL and CSA Listings	1449 4th Edition & CSA 22.2 No. 269.2
Surge Spike Capacity	60kA, 100kA, or 140kA
Line Voltage	120/240 1 Phase 50/60 Hz
UL 1449 4th Edition VPR	L-N, L-G, N-G: 600 V; L-L: 900V
Rated Voltage (MCOV)	L-N, L-G, and N-G: 150V; L-L: 300V
Short Circuit Current Rating (SCCR)	100kA
Inominal (I _n) Rating	20kA
Response Time	<1 nanosecond
Enclosure	NEMA 4X Indoor and Outdoor Rated
Product Warranty	10 years





Type 1 SPD / Surge Arrestor Replacement

TPS3 03

TPS3 03 is a UL 1449 4th Edition 50 kA Type 1 compact surge protective device that can be used as a replacement secondary surge or lighting arrestors. Having a Type 1 designation allows for flexible electrical system connection location (line or load side) as well as UL 96A compliance (@ 20 kA I_).

TPS3 03 Key Features

- UL 1449 4th Edition Listed Type 1
- Type 1 Rated SPD
- 50 kA Per Phase Surge Current
- 20 kA I (Most models)
- 200 kA SCCR (Most models
- UL 96A Lightning Protection Master Labeling compliant (@ 20 kA))
- · Every MOV is monitored
- Mounts external to electrical distribution equipment
- Recommend for Line Side or Load Side Applications
- Standard compact NEMA 4X polycarbonate enclosure
- · Modes of Protection: L-N or L-G and L-L
- · Standard Monitoring: LED Indicator
- Dimensions: 3.25" x 3.25" x 3.3"

(82.6 mm x 82.6 mm x 83.8 mm)


- Weight: 2 lb. (0.9 kg)
- 2 Year Product Warranty

Available Options:

• Dry contacts & Audible Alarm (option "D")



Ordering Information



Example: TPS3C0305D0 = Type 1 SPD for a 208/120V application with a surge current capacity of 50 kA per phase, in a standard NEMA 4X enclosure with dry contacts and audible alarm option.

When an option is not selected, include a zero (0) in the field.

Available Accessories: Ordered Separately

RMSIE = Remote monitor

L = 600/347 V, 3Ø, 4W

Cross Reference

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	LC1224B1100	SN1224B1100	Main Breaker	100	Aluminum
1	Indoor	LC1224L1125	SN1224L1125	Main Lug	125	Aluminum
1	Indoor	LC1224L1125P	SN2020B1100P1	Main Lug	125	Aluminum
1	Indoor	LC1224L1125W	SN1224L1125W	Main Lug	125	Aluminum
1	Indoor	LC1632B1150	SN1632B1150	Main Breaker	150	Aluminum
1	Indoor	LC1632B1200	SN1632B1200	Main Breaker	200	Aluminum
1	Indoor	LC1632L1125	SN1632L1125	Main Lug	125	Aluminum
1	Indoor	LC1632L1125W	SN1632L1125W	Main Lug	125	Aluminum
1	Indoor	LC1632L1150	SN1632L1150	Main Lug	150	Aluminum
1	Indoor	LC2040B1100	SN2040B1100	Main Breaker	100	Aluminum
1	Indoor	LC2040B1100CU	PN2040B1100C	Main Breaker	100	Copper
1	Indoor	LC2040B1100P	SN2020B1100P1	Main Breaker	100	Aluminum
1	Indoor	LC2040B1150	SN2040B1150	Main Breaker	150	Aluminum
1	Indoor	LC2040B1200	SN2040B1200	Main Breaker	200	Aluminum
1	Indoor	LC2040B1200CU	PN2040B1200C	Main Breaker	200	Copper
1	Indoor	LC2040B1200P	SN3048B1200P1	Main Breaker	200	Aluminum
1	Indoor	LC2040L1125	SN2040L1125	Main Lug	125	Aluminum
1	Indoor	LC2040L1125CU	PN2040L1125C	Main Lug	125	Copper
1	Indoor	LC2040L1200	SN2040L1200	Main Lug	200	Aluminum
1	Indoor	LC2040L1200CU	PN2040L1200C	Main Lug	200	Copper
1	Indoor	LC2440B1100	SN2448B1100	Main Breaker	100	Aluminum
1	Indoor	LC2440B1150	SN2448B1150	Main Breaker	150	Aluminum
1	Indoor	LC2440B1200	SN2448B1200	Main Breaker	200	Aluminum
1	Indoor	LC2440L1150	SN2448L1150	Main Lug	150	Aluminum
1	Indoor	LC2440L1200	SN2448L1200	Main Lug	200	Aluminum
1	Indoor	LC2448B1100	SN2448B1100	Main Breaker	100	Aluminum
1	Indoor	LC2448B1100P	SN2020B1100P1	Main Breaker	100	Aluminum
1	Indoor	LC3040B1100	SN3048B1100	Main Breaker	100	Aluminum
1	Indoor	LC3040B1100W	SN3048B1100W	Main Breaker	100	Aluminum
1	Indoor	LC3040B1150	SN3048B1150	Main Breaker	150	Aluminum
1	Indoor	LC3040B1200	SN3048B1200	Main Breaker	200	Aluminum
1	Indoor	LC3040B1200CU	PN3048B1200C	Main Breaker	200	Copper
1	Indoor	LC3040B1200P	SN3048B1200P1	Main Breaker	200	Aluminum
1	Indoor	LC3040L1125	SN3048L1125	Main Lug	125	Aluminum
1	Indoor	LC3040L1200	SN3048L1200	Main Lug	200	Aluminum
1	Indoor	LC3040L1200CU	PN3048L1200C	Main Lug	200	Copper
1	Indoor	LC3054B1200	SN3048B1200	Main Breaker	200	Aluminum
1	Indoor	LC3060B1200P	SN3048B1200P1	Main Breaker	200	Aluminum
1	Indoor	LC4040B1200	SN4040B1200	Main Breaker	200	Aluminum
1	Indoor	LC4040B1200CU	PN4040B1200C	Main Breaker	200	Copper
1	Indoor	LC4040B1200P	SN4040B1200P1	Main Breaker	200	Aluminum
1	Indoor	LC4040L1200	SN4040L1200	Main Lug	200	Aluminum

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	LC4040L1200CU	PN4040L1200C	Main Lug	200	Copper
1	Indoor	LC4040L1200W	SN4040L1200W	Main Lug	200	Aluminum
1	Indoor	LC4060B1200	SN4060B1200	Main Breaker	200	Aluminum
1	Indoor	LC4060L1225	SN4060L1225	Main Lug	225	Aluminum
1	Indoor	LC4242L1225CU	PN4264L1225C	Main Lug	225	Copper
1	Indoor	LC4260B1200	SN4264B1200	Main Breaker	200	Aluminum
1	Indoor	LC4260B1200P	SN4040B1200P1	Main Breaker	200	Aluminum
1	Outdoor	LW0816L1200TR	SNW0816L1200T	Main Lug	200	Aluminum
1	Outdoor	LW1224B1100	SNW1224B1100	Main Breaker	100	Aluminum
1	Outdoor	LW1224B1200	SNW1224B1200	Main Breaker	200	Aluminum
1	Outdoor	LW1224L1125	SNW1224L1125	Main Lug	125	Aluminum
1	Outdoor	LW1224L1200	SNW1224L1200	Main Lug	200	Aluminum
1	Outdoor	LW1224L1225CU	PNW1224L1225C	Main Lug	225	Copper
1	Outdoor	LW1632B1100	SNW1632B1100	Main Breaker	100	Aluminum
1	Outdoor	LW1632L1125	SNW1632L1125	Main Lug	125	Aluminum
1	Outdoor	LW2040B1150	SNW2040B1150	Main Breaker	150	Aluminum
1	Outdoor	LW2040B1200	SNW2040B1200	Main Breaker	200	Aluminum
1	Outdoor	LW2040L1125	SNW2040L1125	Main Lug	125	Aluminum
1	Outdoor	LW2040L1200	SNW2040L1200	Main Lug	200	Aluminum
1	Outdoor	LW3040B1200	SNW3048B1200	Main Breaker	200	Aluminum
1	Outdoor	LW3040L1200	SNW3048L1200	Main Lug	200	Aluminum
1	Outdoor	LW4040B1200	SNW4040B1200	Main Breaker	200	Aluminum
1	Outdoor	LW4242L1225CU	PNW4264L1225C	Main Lug	225	Copper
1	Indoor	P1212L1125CU	PN1212L1125C	Main Lug	125	Copper
1	Indoor	P1224B1100CU	PN1224B1100C	Main Breaker	100	Copper
1	Indoor	P1224L1125CU	PN1224L1125C	Main Lug	125	Copper
1	Indoor	P1224L1125CUSG	PN1224L1125C	Main Lug	125	Copper
1	Indoor	P1224L1200CU	PN1224L1200C	Main Lug	200	Copper
1	Indoor	P1624B1100CU	PN1632B1100C	Main Breaker	100	Copper
1	Indoor	P1624B1100CUW	PN1632B1100CW	Main Breaker	100	Copper
1	Indoor	P1624L1125CU	PN1632L1125C	Main Lug	125	Copper
1	Indoor	P1624L1125CUSG	PN1632L1125C	Main Lug	125	Copper
1	Indoor	P2020B1100CU	PN2020B1100C	Main Breaker	100	Copper
1	Indoor	P2020L1125CU	PN2020L1125C	Main Lug	125	Copper
1	Indoor	P2020L1125CUW	PN2020L1125CW	Main Lug	125	Copper
1	Indoor	P2024B1100CU	PN2040B1100C	Main Breaker	100	Copper
1	Indoor	P2024L1125CU	PN2040L1125C	Main Lug	125	Copper
1	Indoor	P2030B1150CU	PN2040B1150C	Main Breaker	150	Copper
1	Indoor	P2030L1125CUSG	PN2040L1125C	Main Lug	125	Copper
1	Indoor	P2030L1150CU	PN2040L1150C	Main Lug	150	Copper
1	Indoor	P2030L1150CUSG	PN2040L1150C	Main Lug	150	Copper
1	Indoor	P2040B1100ACU	PN2040B1100C	Main Breaker	100	Copper

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	P2040B1100ACUW	PN2040B1100CW	Main Breaker	100	Copper
1	Indoor	P2040B1150ACU	PN2040B1150C	Main Breaker	150	Copper
1	Indoor	P2040B1150ACUW	PN2040B1150CW	Main Breaker	150	Copper
1	Indoor	P2040B1200ACU	PN2040B1200C	Main Breaker	200	Copper
1	Indoor	P2040B1200ACUW	PN2040B1200CW	Main Breaker	200	Copper
1	Indoor	P2040B1200CU	PN2040B1200C	Main Breaker	200	Copper
1	Indoor	P2040L1125ACU	PN2040L1125C	Main Lug	125	Copper
1	Indoor	P2040L1125ACUW	PN2040L1125CW	Main Lug	125	Copper
1	Indoor	P2040L1150ACU	PN2040L1150C	Main Lug	150	Copper
1	Indoor	P2040L1150ACUW	PN2040L1150CW	Main Lug	150	Copper
1	Indoor	P2040L1200ACU	PN2040L1200C	Main Lug	200	Copper
1	Indoor	P2040L1200ACUW	PN2040L1200CW	Main Lug	200	Copper
1	Indoor	P2040L1200CU	PN2040L1200C	Main Lug	200	Copper
1	Indoor	P2424B1100CU	PN2424B1100C	Main Breaker	100	Copper
1	Indoor	P2430L1125CUSG	PN2448L1125C	Main Lug	125	Copper
1	Indoor	P2440L1125CU	PN2448L1125C	Main Lug	125	Copper
1	Indoor	P2440L1125CUW	PN2448L1125CW	Main Lug	125	Copper
1	Indoor	P2440L1200CU	PN2448L1200C	Main Lug	200	Copper
1	Indoor	P2448B1100ACU	PN2424B1100C	Main Breaker	100	Copper
1	Indoor	P2448B1100ACUW	PN2424B1100CW	Main Breaker	100	Copper
1	Indoor	P2448L1125ACU	PN2448L1125C	Main Lug	125	Copper
1	Indoor	P2448L1125ACUW	PN2448L1125CW	Main Lug	125	Copper
1	Indoor	P2448L1200ACU	PN2448L1200C	Main Lug	200	Copper
1	Indoor	P2448L1200ACUW	PN2448L1200CW	Main Lug	200	Copper
1	Indoor	P3030B1100CU	PN3030B1100C	Main Breaker	100	Copper
1	Indoor	P3030B1125CU	PN3030B1125C	Main Breaker	125	Copper
1	Indoor	P3030B1125CUW	PN3030B1125CW	Main Breaker	125	Copper
1	Indoor	P3030B1150CU	PN3030B1150C	Main Breaker	150	Copper
1	Indoor	P3030L1200CU	PN3030L1200C	Main Lug	200	Copper
1	Indoor	P3040B1200	PN3048B1200	Main Breaker	200	Aluminum
1	Indoor	P3040B1200CU	PN3048B1200C	Main Breaker	200	Copper
1	Indoor	P3040B1200W	PN3048B1200W	Main Breaker	200	Aluminum
1	Indoor	P3040L1125CU	PN3048L1125C	Main Lug	125	Copper
1	Indoor	P3040L1125CUW	PN3048L1125CW	Main Lug	125	Copper
1	Indoor	P3040L1200	PN3048L1200	Main Lug	200	Aluminum
1	Indoor	P3040L1200CU	PN3048L1200C	Main Lug	200	Copper
1	Indoor	P3040L1200CUSG	PN3048L1200C	Main Lug	200	Copper
1	Indoor	P3040L1200CUW	PN3048L1200CW	Main Lug	200	Copper
1	Indoor	P3040L1200SG	PN3048L1200	Main Lug	200	Aluminum
1	Indoor	P3040L1200W	PN3048L1200W	Main Lug	200	Aluminum
1	Indoor	P3042B1125CUSP	PN3030B1125C	Main Breaker	125	Copper
1	Indoor	P3054B1200S140	PN3048B1200S14	Main Breaker	200	Copper

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	P3054L1200CU	PN3048L1200C	Main Lug	200	Copper
1	Indoor	P3060B1100ACU	PN3030B1100C	Main Breaker	100	Copper
1	Indoor	P3060B1100ACUW	PN3030B1100CW	Main Breaker	100	Copper
1	Indoor	P3060B1125ACU	PN3030B1125C	Main Breaker	125	Copper
1	Indoor	P3060B1125ACUW	PN3030B1125CW	Main Breaker	125	Copper
1	Indoor	P3060B1150ACU	PN3030B1150C	Main Breaker	150	Copper
1	Indoor	P3060B1150ACUW	PN3030B1150CW	Main Breaker	150	Copper
1	Indoor	P3060B1200A	PN3048B1200	Main Breaker	200	Aluminum
1	Indoor	P3060B1200ACU	PN3048B1200C	Main Breaker	200	Copper
1	Indoor	P3060B1200ACUW	PN3048B1200CW	Main Breaker	200	Copper
1	Indoor	P3060B1200AW	PN3048B1200W	Main Breaker	200	Aluminum
1	Indoor	P3060L1125ACU	PN3048L1125C	Main Lug	125	Copper
1	Indoor	P3060L1125ACUW	PN3048L1125CW	Main Lug	125	Copper
1	Indoor	P3060L1200A	PN3048L1200	Main Lug	200	Aluminum
1	Indoor	P3060L1200ACU	PN3048L1200C	Main Lug	200	Copper
1	Indoor	P3060L1200ACUW	PN3048L1200CW	Main Lug	200	Copper
1	Indoor	P3060L1200AW	PN3048L1200W	Main Lug	200	Aluminum
1	Indoor	P4040B1200	PN4040B1200	Main Breaker	200	Aluminum
1	Indoor	P4040B1200CU	PN4040B1200C	Main Breaker	200	Copper
1	Indoor	P4040B1200CUSG	PN4040B1200C	Main Breaker	200	Copper
1	Indoor	P4040B1200CUW	PN4040B1200CW	Main Breaker	200	Copper
1	Indoor	P4040B1200W	PN4040B1200W	Main Breaker	200	Aluminum
1	Indoor	P4040L1125CU	PN4040L1125C	Main Lug	125	Copper
1	Indoor	P4040L1125CUW	PN4040L1125CW	Main Lug	125	Copper
1	Indoor	P4040L1200	PN4040L1200	Main Lug	200	Aluminum
1	Indoor	P4040L1200CU	PN4040L1200C	Main Lug	200	Copper
1	Indoor	P4040L1200CUSG	PN4040L1200C	Main Lug	200	Copper
1	Indoor	P4040L1200CUW	PN4040L1200CW	Main Lug	200	Copper
1	Indoor	P4040L1200SG	PN4040L1200	Main Lug	200	Aluminum
1	Indoor	P4060B1200S140	PN4060B1200S14	Main Breaker	200	Copper
1	Indoor	P4080B1200A	PN4060B1200	Main Breaker	200	Aluminum
1	Indoor	P4080B1200ACU	PN4060B1200C	Main Breaker	200	Copper
1	Indoor	P4080B1200ACUW	PN4060B1200CW	Main Breaker	200	Copper
1	Indoor	P4080B1200AW	PN4060B1200W	Main Breaker	200	Aluminum
1	Indoor	P4080L1125ACU	PN4040L1125C	Main Lug	125	Copper
1	Indoor	P4080L1125ACUW	PN4040L1125CW	Main Lug	125	Copper
1	Indoor	P4080L1200A	PN4040L1200	Main Lug	200	Aluminum
1	Indoor	P4080L1200ACU	PN4060L1200C	Main Lug	200	Copper
1	Indoor	P4080L1200ACUW	PN4060L1200CW	Main Lug	200	Copper
1	Indoor	P4080L1200AW	PN4040L1200W	Main Lug	200	Aluminum
1	Indoor	P4260B1225CU	PN4264B1225C	Main Breaker	225	Copper
1	Indoor	P4260B1225CUW	PN4264B1225CW	Main Breaker	225	Copper

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	P4260L1225CU	PN4264L1225C	Main Lug	225	Copper
1	Indoor	P4260L1225CUSG	PN4264L1225C	Main Lug	225	Copper
1	Indoor	P4260L1225CUW	PN4264L1225CW	Main Lug	225	Copper
1	Indoor	P4280B1225ACU	PN4264B1225C	Main Breaker	225	Copper
1	Indoor	P4280B1225ACUW	PN4264B1225CW	Main Breaker	225	Copper
1	Indoor	P4280L1225ACU	PN4264L1225C	Main Lug	225	Copper
1	Indoor	P4280L1225ACUW	PN4264L1225CW	Main Lug	225	Copper
1	Indoor	P5470B1200CU	PN5482B1200C	Main Breaker	200	Copper
1	Indoor	P5470B1200CUW	PN5482B1200CW	Main Breaker	200	Copper
1	Indoor	P5470B1225CU	PN5482B1225C	Main Breaker	225	Copper
1	Indoor	P5470L1225CU	PN5482L1225C	Main Lug	225	Copper
1	Indoor	P5480B1200ACU	PN5482B1200C	Main Breaker	200	Copper
1	Indoor	P5480B1200ACUW	PN5482B1200CW	Main Breaker	200	Copper
1	Indoor	P5480B1225ACU	PN5482B1225C	Main Breaker	225	Copper
1	Indoor	P5480B1225ACUW	PN5482B1225CW	Main Breaker	225	Copper
1	Indoor	P5480L1225ACU	PN5482L1225C	Main Lug	225	Copper
1	Indoor	P5480L1225ACUW	PN5482L1225CW	Main Lug	225	Copper
1	Outdoor	PW0816B1150TC	PNW0816B1150TC	Main Breaker	150	Copper
1	Outdoor	PW0816B1200TC	PNW0816B1200TC	Main Breaker	200	Copper
1	Outdoor	PW0816L1200TC	PNW0816L1200TC	Main Lug	200	Copper
1	Outdoor	PW1212L1125CU	PNW1212L1125C	Main Lug	125	Copper
1	Outdoor	PW1224B1100CU	PNW1224B1100C	Main Breaker	100	Copper
1	Outdoor	PW1224L1125CU	PNW1224L1125C	Main Lug	125	Copper
1	Outdoor	PW1224L1200CU	PNW1224L1200C	Main Lug	200	Copper
1	Outdoor	PW1224L1225CU	PNW1224L1225C	Main Lug	225	Copper
1	Outdoor	PW1624B1100CU	PNW1632B1100C	Main Breaker	100	Copper
1	Outdoor	PW1624L1125CU	PNW1632L1125C	Main Lug	125	Copper
1	Outdoor	PW2020B1100CU	PNW2020B1100C	Main Breaker	100	Copper
1	Outdoor	PW2030B1150CU	PNW2040B1150C	Main Breaker	150	Copper
1	Outdoor	PW2030L1150CU	PNW2040L1150C	Main Lug	150	Copper
1	Outdoor	PW2040B1200CU	PNW2040B1200C	Main Breaker	200	Copper
1	Outdoor	PW2040L1200CU	PNW2040L1200C	Main Lug	200	Copper
1	Outdoor	PW3040B1100CU	PNW3048B1100C	Main Breaker	100	Copper
1	Outdoor	PW3040B1125CU	PNW3048B1125C	Main Breaker	125	Copper
1	Outdoor	PW3040B1150CU	PNW3048B1150C	Main Breaker	150	Copper
1	Outdoor	PW3040B1200CU	PNW3048B1200C	Main Breaker	200	Copper
1	Outdoor	PW3040L1125CU	PNW3048L1125C	Main Lug	125	Copper
1	Outdoor	PW3040L1200CU	PNW3048L1200C	Main Lug	200	Copper
1	Outdoor	PW3054L1200CU	PNW3048L1200C	Main Lug	200	Copper
1	Outdoor	PW4040B1200CU	PNW4040B1200C	Main Breaker	200	Copper
1	Outdoor	PW4040L1200CU	PNW4040L1200C	Main Lug	200	Copper

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Outdoor	PW4260B1225CU	PNW4264B1225C	Main Breaker	225	Copper
1	Outdoor	PW4260L1225CU	PNW4264L1225C	Main Lug	225	Copper
1	Indoor	S1020B1100	SN1224B1100	Main Breaker	100	Aluminum
1	Indoor	S1212L1125	SN1212L1125	Main Lug	125	Aluminum
1	Indoor	S1224B1100	SN1224B1100	Main Breaker	100	Aluminum
1	Indoor	S1224L1125	SN1224L1125	Main Lug	125	Aluminum
1	Indoor	S1224L1200	SN1224L1200	Main Lug	200	Aluminum
1	Indoor	S1624B1100	SN1632B1100	Main Breaker	100	Aluminum
1	Indoor	S1624B1100W	SN1632B1100W	Main Breaker	100	Aluminum
1	Indoor	S1624B1125	SN1632B1125	Main Breaker	125	Aluminum
1	Indoor	S1624L1125	SN1632L1125	Main Lug	125	Aluminum
1	Indoor	S1630B1150	SN1632B1150	Main Breaker	150	Aluminum
1	Indoor	S1632B1200	SN1632B1200	Main Breaker	200	Aluminum
1	Indoor	S2020B1100	SN2020B1100	Main Breaker	100	Aluminum
1	Indoor	S2020B1100P	SN2020B1100P1	Main Breaker	100	Aluminum
1	Indoor	S2020L1125	SN2020L1125	Main Lug	125	Aluminum
1	Indoor	S2020L1125G	SN2020L1125	Main Lug	125	Aluminum
1	Indoor	S2020L1125GW	SN2020L1125W	Main Lug	125	Aluminum
1	Indoor	S2020L1125W	SN2020L1125W	Main Lug	125	Aluminum
1	Indoor	S2024B1100	SN2040B1100	Main Breaker	100	Aluminum
1	Indoor	S2024L1125	SN2040L1125	Main Lug	125	Aluminum
1	Indoor	S2024L1125G	SN2040L1125	Main Lug	125	Aluminum
1	Indoor	S2030B1150	SN2040B1150	Main Breaker	150	Aluminum
1	Indoor	S2030L1125SG	SN2040L1125	Main Lug	125	Aluminum
1	Indoor	S2030L1150	SN2040L1150	Main Lug	150	Aluminum
1	Indoor	S2030L1150W	SN2040L1150W	Main Lug	150	Aluminum
1	Indoor	S2040B1100A	SN2040B1100	Main Breaker	100	Aluminum
1	Indoor	S2040B1100AW	SN2040B1100W	Main Breaker	100	Aluminum
1	Indoor	S2040B1150A	SN2040B1150	Main Breaker	150	Aluminum
1	Indoor	S2040B1150AW	SN2040B1150W	Main Breaker	150	Aluminum
1	Indoor	S2040B1200	SN2040B1200	Main Breaker	200	Aluminum
1	Indoor	S2040B1200A	SN2040B1200	Main Breaker	200	Aluminum
1	Indoor	S2040B1200AW	SN2040B1200W	Main Breaker	200	Aluminum
1	Indoor	S2040C1200	SN2040C1200	Main Convertible	200	Aluminum
1	Indoor	S2040L1125AG	SN2040L1125	Main Lug	125	Aluminum
1	Indoor	S2040L1125AGW	SN2040L1125W	Main Lug	125	Aluminum
1	Indoor	S2040L1150AG	SN2040L1150	Main Lug	150	Aluminum
1	Indoor	S2040L1150AGW	SN2040L1150W	Main Lug	150	Aluminum
1	Indoor	S2040L1200	SN2040L1200	Main Lug	200	Aluminum
1	Indoor	S2040L1200AG	SN2040L1200	Main Lug	200	Aluminum
1	Indoor	S2040L1200AGW	SN2040L1200W	Main Lug	200	Aluminum

1				Main	Amperage	Bus
	Indoor	S2424B1125	SN2424B1125	Main Breaker	125	Aluminum
1	Indoor	S2424B1125W	SN2424B1125W	Main Breaker	125	Aluminum
1	Indoor	S2424C1125	SN2424C1125	Main Convertible	125	Aluminum
1	Indoor	S2424L1125	SN2424L1125	Main Lug	125	Aluminum
1	Indoor	S2424L1125G	SN2424L1125	Main Lug	125	Aluminum
1	Indoor	S2424L1125GW	SN2424L1125W	Main Lug	125	Aluminum
1	Indoor	S2424L1125W	SN2424L1125W	Main Lug	125	Aluminum
1	Indoor	S2430B1150	SN2448B1150	Main Breaker	150	Aluminum
1	Indoor	S2440B1200	SN2448B1200	Main Breaker	200	Aluminum
1	Indoor	S2440L1125	SN2448L1125	Main Lug	125	Aluminum
1	Indoor	S2440L1125G	SN2448L1125	Main Lug	125	Aluminum
1	Indoor	S2440L1200	SN2448L1200	Main Lug	200	Aluminum
1	Indoor	S2440L1200W	SN2448L1200W	Main Lug	200	Aluminum
1	Indoor	S2448B1125A	SN2424B1125	Main Breaker	125	Aluminum
1	Indoor	S2448B1125AW	SN2424B1125W	Main Breaker	125	Aluminum
1	Indoor	S2448B1150A	SN2448B1150	Main Breaker	150	Aluminum
1	Indoor	S2448B1150AW	SN2448B1150W	Main Breaker	150	Aluminum
1	Indoor	S2448B1200A	SN2448B1200	Main Breaker	200	Aluminum
1	Indoor	S2448B1200AW	SN2448B1200W	Main Breaker	200	Aluminum
1	Indoor	S2448L1125AG	SN2448L1125	Main Lug	125	Aluminum
1	Indoor	S2448L1125AGW	SN2448L1125W	Main Lug	125	Aluminum
1	Indoor	S2448L1200AG	SN2448L1200	Main Lug	200	Aluminum
1	Indoor	S2448L1200AGW	SN2448L1200W	Main Lug	200	Aluminum
1	Indoor	S3030B1100	SN3030B1100	Main Breaker	100	Aluminum
1	Indoor	S3030B1100W	SN3030B1100W	Main Breaker	100	Aluminum
1	Indoor	S3030B1125	SN3030B1125	Main Breaker	125	Aluminum
1	Indoor	S3030B1125W	SN3030B1125W	Main Breaker	125	Aluminum
1	Indoor	S3030B1150	SN3030B1150	Main Breaker	150	Aluminum
1	Indoor	S3030B1150SG	SN3030B1150	Main Breaker	150	Aluminum
1	Indoor	S3030B1150W	SN3030B1150W	Main Breaker	150	Aluminum
1	Indoor	S3030L1200	SN3030L1200	Main Lug	200	Aluminum
1	Indoor	S3030L1200W	SN3030L1200W	Main Lug	200	Aluminum
1	Indoor	S3040B1125	SN3048B1125	Main Breaker	125	Aluminum
1	Indoor	S3040B1150	SN3048B1150	Main Breaker	150	Aluminum
1	Indoor	S3040B1200	SN3048B1200	Main Breaker	200	Aluminum
1	Indoor	S3040B1200P	SN3048B1200P1	Main Breaker	200	Aluminum
1	Indoor	S3040B1200W	SN3048B1200W	Main Breaker	200	Aluminum
1	Indoor	S3040C1200	SN3048C1200	Main Convertible	200	Aluminum
1	Indoor	S3040L1125	SN3048L1125	Main Lug	125	Aluminum
1	Indoor	S3040L1125G	SN3048L1125	Main Lug	125	Aluminum
1	Indoor	S3040L1125GW	SN3048L1125W	Main Lug	125	Aluminum
1	Indoor	S3040L1125W	SN3048L1125W	Main Lug	125	Aluminum

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	S3040L1200	SN3048L1200	Main Lug	200	Aluminum
1	Indoor	S3040L1200L50	SN3048L1200L50	Main Lug	200	Aluminum
1	Indoor	S3040L1200L50W	SN3048L1200L5W	Main Lug	200	Aluminum
1	Indoor	S3040L1200P	SN3048B1200P1	Main Lug	200	Aluminum
1	Indoor	S3040L1200W	SN3048L1200W	Main Lug	200	Aluminum
1	Indoor	S3054B1200P	SN3048B1200P1	Main Breaker	200	Aluminum
1	Indoor	S3054B1200S060	SN3048B1200S06	Main Breaker	200	Aluminum
1	Indoor	S3054L1200	SN3048L1200	Main Lug	200	Aluminum
1	Indoor	S3060B1100A	SN3048B1100	Main Breaker	100	Aluminum
1	Indoor	S3060B1100AW	SN3048B1100W	Main Breaker	100	Aluminum
1	Indoor	S3060B1125A	SN3048B1125	Main Breaker	125	Aluminum
1	Indoor	S3060B1125AW	SN3048B1125W	Main Breaker	125	Aluminum
1	Indoor	S3060B1150A	SN3048B1150	Main Breaker	150	Aluminum
1	Indoor	S3060B1150AW	SN3048B1150W	Main Breaker	150	Aluminum
1	Indoor	S3060B1200A	SN3048B1200	Main Breaker	200	Aluminum
1	Indoor	S3060B1200AW	SN3048B1200W	Main Breaker	200	Aluminum
1	Indoor	S3060L1125AG	SN3048L1125	Main Lug	125	Aluminum
1	Indoor	S3060L1125AGW	SN3048L1125W	Main Lug	125	Aluminum
1	Indoor	S3060L1200AG	SN3048L1200	Main Lug	200	Aluminum
1	Indoor	S3060L1200AGW	SN3048L1200W	Main Lug	200	Aluminum
1	Indoor	S4040B1200	SN4040B1200	Main Breaker	200	Aluminum
1	Indoor	S4040B1200P	SN4040B1200P1	Main Breaker	200	Aluminum
1	Indoor	S4040B1200SG	SN4040B1200	Main Breaker	200	Aluminum
1	Indoor	S4040B1200W	SN4040B1200W	Main Breaker	200	Aluminum
1	Indoor	S4040C1200	SN4040C1200	Main Convertible	200	Aluminum
1	Indoor	S4040L1125	SN4040L1125	Main Lug	125	Aluminum
1	Indoor	S4040L1200	SN4040L1200	Main Lug	200	Aluminum
1	Indoor	S4040L1200W	SN4040L1200W	Main Lug	200	Aluminum
1	Indoor	S4060B1200S060	SN4060B1200S06	Main Breaker	200	Aluminum
1	Indoor	S4080B1200A	SN4060B1200	Main Breaker	200	Aluminum
1	Indoor	S4080B1200AW	SN4060B1200W	Main Breaker	200	Aluminum
1	Indoor	S4080L1125AG	SN4040L1125	Main Lug	125	Aluminum
1	Indoor	S4080L1125AGW	SN4040L1125W	Main Lug	125	Aluminum
1	Indoor	S4080L1200AG	SN4040L1200	Main Lug	200	Aluminum
1	Indoor	S4080L1200AGW	SN4040L1200W	Main Lug	200	Aluminum
1	Indoor	S4260B1200	SN4264B1200	Main Breaker	200	Aluminum
1	Indoor	S4260B1225	SN4264B1225	Main Breaker	225	Aluminum
1	Indoor	S4260L1225	SN4264L1225	Main Lug	225	Aluminum
1	Indoor	S4280B1225A	SN4264B1225	Main Breaker	225	Aluminum
1	Indoor	S4280B1225AW	SN4264B1225W	Main Breaker	225	Aluminum
1	Indoor	S4280L1225AG	SN4264L1225	Main Lug	225	Aluminum
1	Indoor	S4280L1225AGW	SN4264L1225W	Main Lug	225	Aluminum

Phase	Enclosure	Legacy Catalog Number	New Catalog Number	Main	Amperage	Bus
1	Indoor	S5470B1200	SN5482B1200	Main Breaker	200	Aluminum
1	Indoor	S5470B1225	SN5482B1225	Main Breaker	225	Aluminum
1	Indoor	S5470L1225	SN5482L1225	Main Lug	225	Aluminum
1	Indoor	S5480B1200A	SN5482B1200	Main Breaker	200	Aluminum
1	Indoor	S5480B1200AW	SN5482B1200W	Main Breaker	200	Aluminum
1	Indoor	S5480B1225A	SN5482B1225	Main Breaker	225	Aluminum
1	Indoor	S5480B1225AW	SN5482B1225W	Main Breaker	225	Aluminum
1	Indoor	S5480L1225AG	SN5482L1225	Main Lug	225	Aluminum
1	Indoor	S5480L1225AGW	SN5482L1225W	Main Lug	225	Aluminum
1	Outdoor	SW0816B1200T	SNW0816B1200T	Main Breaker	200	Aluminum
1	Outdoor	SW0816L1200T	SNW0816L1200T	Main Lug	200	Aluminum
1	Outdoor	SW1212L1125	SNW1212L1125	Main Lug	125	Aluminum
1	Outdoor	SW1224B1100	SNW1224B1100	Main Breaker	100	Aluminum
1	Outdoor	SW1224B1125	SNW1224B1125	Main Breaker	125	Aluminum
1	Outdoor	SW1224L1125	SNW1224L1125	Main Lug	125	Aluminum
1	Outdoor	SW1224L1200	SNW1224L1200	Main Lug	200	Aluminum
1	Outdoor	SW1224L1225	SNW1224L1225	Main Lug	225	Aluminum
1	Outdoor	SW1624B1100	SNW1632B1100	Main Breaker	100	Aluminum
1	Outdoor	SW1624L1125	SNW1632L1125	Main Lug	125	Aluminum
1	Outdoor	SW2020B1100	SNW2020B1100	Main Breaker	100	Aluminum
1	Outdoor	SW2024B1125	SNW2040B1125	Main Breaker	125	Aluminum
1	Outdoor	SW2030L1150	SNW2040L1150	Main Lug	150	Aluminum
1	Outdoor	SW2040B1200	SNW2040B1200	Main Breaker	200	Aluminum
1	Outdoor	SW2040C1200	SNW2040C1200	Main Convertible	200	Aluminum
1	Outdoor	SW2040L1200	SNW2040L1200	Main Lug	200	Aluminum
1	Outdoor	SW2424B1125	SNW2424B1125	Main Breaker	125	Aluminum
1	Outdoor	SW2424C1125	SNW2424C1125	Main Convertible	125	Aluminum
1	Outdoor	SW2424L1125	SNW2424L1125	Main Lug	125	Aluminum
1	Outdoor	SW3040B1125	SNW3048B1125	Main Breaker	125	Aluminum
1	Outdoor	SW3040B1150	SNW3048B1150	Main Breaker	150	Aluminum
1	Outdoor	SW3040B1200	SNW3048B1200	Main Breaker	200	Aluminum
1	Outdoor	SW3040C1200	SNW3048C1200	Main Convertible	200	Aluminum
1	Outdoor	SW3040L1125	SNW3048L1125	Main Lug	125	Aluminum
1	Outdoor	SW3040L1200	SNW3048L1200	Main Lug	200	Aluminum
1	Outdoor	SW3054L1200	SNW3048L1200	Main Lug	200	Aluminum
1	Outdoor	SW4040B1150	SNW4040B1150	Main Breaker	150	Aluminum
1	Outdoor	SW4040B1200	SNW4040B1200	Main Breaker	200	Aluminum
1	Outdoor	SW4040C1200	SNW4040C1200	Main Convertible	200	Aluminum
1	Outdoor	SW4040L1200	SNW4040L1200	Main Lug	200	Aluminum
1	Outdoor	SW4260B1225	SNW4264B1225	Main Breaker	225	Aluminum
1	Outdoor	SW4260L1225	SNW4264L1225	Main Lug	225	Aluminum

Notes

Published by Siemens 2020

Siemens Industry, Inc. 5400 Triangle Parkway Norcross, GA 30092

Siemens Technical Support: 1-800-333-7421 info.us@siemens.com

Printed in USA-CP Order No. RPSA-LOADC-0320 All Rights Reserved © 2020, Siemens Industry, Inc. usa.siemens.com/loadcenters

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.