

PASS & SEYMOUR®


Specification Grade PlugTail[®] Receptacles 15 & 20A, 125V

PlugTail[®] — The fastest, most consistent and reliable wiring devices – ever.

PT5262, PT5362

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle. The connector simply snaps into the back of the device — no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

Features & Benefits



3rd Party Compliance



cULus Listed, File Number E140596, Standard UL498. US LISTED Federal Specification WC596.





PASS & SEYMOUR® Specification Grade PlugTail® Receptacles

15 & 20Å, 125V

Technical Specifications

Performance	
Electrical	
Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rate current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current
Mechanical	
PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only
Product Identification	Ratings are a permanent part of the device
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact

PlugTail[®] Receptacle Materials

Face	Nylon		
Body	PVC		
Contacts	.036 688 Brass		
Mounting Strap	.042" Zinc-Plated Steel		
Internal Ground System	.036 260 Brass		
Assembly Drive Screw	Zinc-Plated Steel		
Auto-Ground Clip	Steel		
Mounting Screws	Tri-Drive Steel		

PlugTail[®] Connector Materials

Housing	Polycarbonate
Contacts	.030 Brass

Warranty

1 Year



Dimensions for 15 & 20 Amp







Ordering Information

	NEMA			
Catalog Number	Α.	V.	Color	Config. No
Duplex Receptacles				
PT5262I	15	125	lvory	5-15R
PT5262W	15	125	White	5-15R
PT5262	15	125	Brown	5-15R
PT5262GRY	15	125	Gray	5-15R
PT5262BL	15	125	Blue	5-15R
PT5262RED	15	125	Red	5-15R
PT5262LA	15	125	Light Almond	5-15R
PT5262BK	15	125	Black	5-15R
PT5362I	20	125	lvory	5-20R
PT5362W	20	125	White	5-20R
PT5362	20	125	Brown	5-20R
PT5362GRY	20	125	Gray	5-20R
PT5362BL	20	125	Blue	5-20R
PT5362RED	20	125	Red	5-20R
PT5362LA	20	125	Light Almond	5-20R
PT5362BK	20	125	Black	5-20R

PlugTail[®] Connectors — Right Angle

Catalog Number	Wire Type	Wire Length
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"







PASS & SEYMOUR®

Specification Grade PlugTail® Receptacles 15 & 20A, 125V

Also available...

- Hospital Grade Devices
- SPD & Isolated Ground Devices

trademarks of their respective holders.

- Ground Continuity Monitoring (GCM)
- Straight Blade
 Plugs & Connectors
- Turnlok[®] Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor[®] Wire Mesh Grips
- USB Charging Devices



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us 570 Applewood Crescent

570 Applewood Crescent Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca



The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or