



Pass & Seymour


Extra Heavy-Duty Receptacles PlugTail™ Devices Tamper-Resistant HG 15 & 20A, 125V

PTTR62H, PTTR63H

PlugTail™. The fastest, most consistent and reliable wiring devices – ever.

Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each extra heavy-duty receptacle. The connector simply snaps into the back of the device — no fussing with wires, stripping, or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now device installation is a snap!

A sturdy mechanical shutter system helps prevent children from sticking objects into the receptacle. The toughest and safest tamper-resistant hospital grade receptacle available.



FEATURES & BENEFITS

Auto-ground clip assures positive ground.


Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Dual mechanical shutter system to help prevent insertion of foreign objects.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.



PTTR63H-W

Large brass contacts snugly terminate on device blade terminals. Audible snapping latch assures connection, allows release.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

No exposed terminals before, during, or after installation increases safety at all phases of product life.

FIELD USES/VERTICAL MARKETS

■ Industrial

■ Health Care

■ Education

■ Institutional

Extra Heavy-Duty Receptacles PlugTail™ Devices Tamper-Resistant HG 15 & 20A, 125V

ORDERING INFORMATION

Catalog Number	Rating A. V.	Color	NEMA Config. No.
Duplex Receptacles			
PTTR62H-I	15 125	Ivory	5-15R
PTTR62H-W	15 125	White	5-15R
PTTR62H	15 125	Brown	5-15R
PTTR62H-GRY	15 125	Gray	5-15R
PTTR62H-BK	15 125	Black	5-15R
PTTR62H-BL	15 125	Blue	5-15R
PTTR62H-RED	15 125	Red	5-15R
PTTR62H-LA	15 125	Light Almond	5-15R
PTTR63H-I	20 125	Ivory	5-20R
PTTR63H-W	20 125	White	5-20R
PTTR63H	20 125	Brown	5-20R
PTTR63H-GRY	20 125	Gray	5-20R
PTTR63H-BK	20 125	Black	5-20R
PTTR63H-BL	20 125	Blue	5-20R
PTTR63H-RED	20 125	Red	5-20R
PTTR63H-LA	20 125	Light Almond	5-20R

Catalog Number	Wire Type	Wire Length
PlugTail Connectors — Right Angle		
PTRA6STR	Stranded	6"
PTRA6SOL	Solid	6"



NEMA
5-15R



NEMA
5-20R

For more information on these and other P&S products refer to our Product Guide or visit our web site.

Extra Heavy-Duty Receptacles PlugTail™ Devices Tamper-Resistant HG 15 & 20A, 125V



Pass & Seymour

TECHNICAL SPECIFICATIONS

3rd Party Compliance

cULus Listed, File Number E140596, Standard UL498.
Federal Specification WC596, Hospital Grade.

Performance

Electrical


Dielectric Voltage	Withstands 2000V minimum
Maximum Working Voltage	125V
Current Interrupting	Certified for current interrupting at full-rated current (receptacle only)
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current

Mechanical

PlugTail Connector Identification	#12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only.
Product Identification	Ratings are a permanent part of the device

Environmental

Flammability	UL94 V2
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact



Dimensions for
15 & 20 Amp



PlugTail Receptacle Materials


Face	Nylon	Integral Ground System	.036 260 Brass
Back Body	Nylon	Assembly Drive Screw	Zinc-Plated Steel
Line Contacts	.036 688 Brass	Auto-Ground Clip	Brass
Mounting Strap	.050 260 Brass	Mounting Screws	Tri-Drive Steel
Tamper Shutter	Thermoplastic		

PlugTail Connector Materials

Housing	Polycarbonate	Contacts	.036 688 Brass
---------	---------------	----------	----------------


Warranty

1 Year




PTRA6STR

COMPLEMENTARY DEVICES & ACCESSORIES




PLUGTAIL™ DEVICES

- Extra Heavy-Duty Spec Grade
- Extra Heavy-Duty Hospital Grade
- Extra Heavy-Duty Tamper-Resistant




STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Hard Use
- Construction Grade
- Construction Grade Leaded
- Commercial Grade




DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



SWITCHES

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



GFCIs

- Specification Grade



WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Screwless Polycarbonate
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

ALSO AVAILABLE...

- | | | | |
|--------------------------------------|-------------------------------------|-------------------------------|----------------------------|
| ■ Hospital Grade Devices | ■ Straight Blade Plugs & Connectors | ■ Weatherproof Boxes & Covers | ■ Flexcor® Wire Mesh Grips |
| ■ TVSS & Isolated Ground Devices | ■ Turnlok® Locking Devices | ■ IEC 309 Industrial Products | ■ Bulk Solutions |
| ■ Ground Continuity Monitoring (GCM) | | | |

legrand®
Pass & Seymour

P.O. Box 4822
Syracuse, NY 13221-4822
Phone: 1.800.776.4035
www.legrand.us/passandseymour

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
Phone: 905.738.9195

