# Stonco by (s) ignify

**Wall Mount** 

Wall Pack DualSelect

60W and 100W



**Stonco LED Wall Pack DualSelect** family features energy saving LED technology ideal for wall mounted applications. The Wall pack DualSelect is available in two sizes to accommodate multiple mounting heights.

Project:	
Location:	
Cat.No:	
Туре:	
Lamps:	Qty:
Notes:	

Example: WP60-SCT-G2-10-BZ

#### Ordering guide

Luminaire WP	Wattage	Generation SCT-G2	Voltage 10	Finish BZ
WP Wall Pack	60 28W/40W/60W 100 70W/80W/90W/100W	80CRI Integrated Daylight	<b>10</b> 120–347V	BZ Bronze

# **Specifications**

#### Housing

Die-cast aluminum housing and lens frame with heat and impact resistant borosilicate glass lens.

# **IP Rating**

LED light engine is weather proof sealed in a luminaire rated IP65.

#### Electrical

Driver efficiency (>84% at full load). Available in 120–347V.

#### **LED Board and Array**

1 or 2 Chip on Board (Mid-power) LEDs. Selectable Color temperature 3000K, 4000K, 5000K. Minimum CRI of 70.

# Mounting

Mounts to standard 3-½" to 4" round and octagonal or 4 inch square electrical junction boxes.  $\frac{1}{2}$  NPT threaded conduit access.

# **Energy Saving Benefits**

System efficacy 123lm/W @ 3000K - 128lm/W @ 5000K

#### **Daylight Sensor**

	Photocell	Luminaire
Set 1	Disable	On
Set 2 (Default)	Ambient light <10lux, Ambient light >30lux	On Off
Set 3	Ambient light <25lux, Ambient light >50lux	On Off
Set 4	Ambient light <50lux, Ambient light >80lux	On Off

#### Listings

UL/cUL listed to the UL 1598 standard, suitable for Wet Locations. Suitable for use in ambient from -40° to 40°C (-40° to 104°F).

Product is DesignLights Consortium® qualified.

#### Finish

Each luminaire receives a powdercoat finish. Standard color is bronze (BZ).

#### **Limited Warranty**

Luminaires are all covered by a 5-year limited warranty. See <a href="mailto:signify.com/warranties">signify.com/warranties</a> for details.






# WP Wall pack DualSelect LED

# 60W and 100W

#### **Dimensions**





# Weight

Product	Weight		
WP60W	9.2lbs (4.2kg)		
WP100W	10.14lbs (4.6kg)		

# **LED Wattage and Lumen Values**

Ordering Codes	Total LEDs	System Current (mA)	Color Temp.(K)	Average System Wattage <sup>1</sup>	Lumen Output <sup>1,2</sup>	Efficacy (LPW)	Weight (kg)
WP60-SCT-G2-10-BZ	280	230 @ 120V 330 @ 120V 500 @ 120V	3000/4000/5000 3000/4000/5000 3000/4000/5000	28 40 60	3860/4060/3920 5280/5720/5360 7380/8160/7680	138/145/140 132/143/134 123/136/128	3.7
WP100-SCT-G2-10-BZ	560	583 @ 120V 667 @ 120V 750 @ 120V 835 @ 120V	3000/4000/5000 3000/4000/5000 3000/4000/5000 3000/4000/5000	70 80 90 100	9240/10080/9800 10240/11360/10960 11250/12330/11970 12300/13600/12800	132/144/140 128/142/137 125/137/133 123/136/128	3.9

Wattage and lumen output may vary by due to LED manufacturer forward volt specification and ambient temperature. Wattage shown is average for 120V input. Measured wattage may vary due to variation in input voltage..

NOTE: Contact outdoorlighting.applications@philips.com for details or additional information.

#### **Predicted Lumen Depreciation Data**

Predicted performance derived from LED manufacturer's data and engineering design estimates, based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions. L70 is the predicted time when LED performance depreciates to 70% of initial lumen output.

Calculated per IESNA TM21-11. Published L70 hours limited to 6 times actual LED test hours.

Ordering Codes	Ambient Temperature °C	LED Current mA	Driver output current mA	L <sub>70</sub> perTM21 <sup>2,3</sup>	Lumen Maintenance @ 60,000 hrs	
WP60-SCT-G2-10-BZ	25 °C	43	1300	>54,000 hrs	89.9%	
WP100-SCT-G2-10-BZ	25 °C	39	2000	>54,000 hrs	88.7%	

<sup>1.</sup> Predicted performance derived from LED manufacturer's data and engineering design estimates,

 $The information\ presented\ in\ this\ document\ is\ not\ intended\ as\ any\ commercial\ offer\ and\ does\ not\ form\ part\ of\ any\ quotation\ or\ contract.$ 



© 2020 Signify Holding. All rights reserved. This document contains information relating to the product portfolio of Signify which information may be subject to change. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereor is disclaimed. All trademarks are owned by Signify Holding or their respective owners. Signify North America Corporation 200 Franklin Square Drive, Somerset, NJ 08873 Telephone 855-486-2216 Signify Canada Ltd. 281 Hillmount Road, Markham, ON, Canada L6C 2S3 Falenhone 800-668-9008

Lumen values based on photometric tests performed in compliance with IESNA LM-79.

based on IESNA LM-80 methodology. Actual experience may vary due to field application conditions. L70 is the predicted time when LED performance depreciates to 70% of initial lumen output.

<sup>3.</sup> Calculated per IESNA TM 21-11. Published L70 hours limited to 6 times actual LED test hours.