



## T&B° Fittings



# Star Teck®








#### STRAIGHT REPRESENTATION


#### MATERIALS:

- ALUMINIUM
- NITRILE
- SANTOPRENE
- SILICONE





**CERTIFICATIONS:** 



CLASS I, CLASS II GROUP EFG, CLASS III TYPE 4/4X Ex e IIC IP68 Class I, Zone 1, AEx e II IP68

#### 90° REPRESENTATION



SUITABLE FOR CLASS I, II, III DIV 2 PER NEC, TYPE 4X

CAT NO.	HUB SIZE	TORQUE (in-lbs)	RANGE OVER JACKET (in)		RANGE OVER ARMOR (in)		THROAT DIA. MIN (in)		OVERALL	"^"	"B"	"0"	"D"
			MIN.	MAX.	MIN.	MAX.	with armor stop	without armor stop	(in)	A"	В.	C	"D"
STED050	1/2-14 NPT	450	0.600	0.885	0.520	0.795	0.505	0.617	5.375	1 15/16	2 1/2	3 13/16	13/16
STED075	3/4-14 NPT	600	0.860	1.205	0.780	1.125	0.645	0.819	6.630	2 1/2	3	4	1 1/16

#### GENERAL NOTES

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- 2. DIMENSIONS IN BRACKETS [] ARE IN METRIC UNITS.

REVISIONS

SEE ERN ( ) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: www.tnb.com

DESCRIPTION:

RM401886 / (2016718)

## STED

### STARTECK EXTREME DIRECTOR FITTING

ORIGINAL PROJECT NO / (ERN NO ) SHEET NO:

HEET NO: REV. NO:

WSD-001536

DRAWING NO:

Thomas & Betts

A Member of the ABB Group