


PHILIPS

LED Transformers

Datasheet



LED Transformers

LED Transformer 60W 24V 120V PP

Product description

Philips full-electronic constant voltage LED Transformers are designed to operate 24VDC LED solutions used in general applications such as refrigerated display lighting, retail display lighting and linear accent lighting. They are specifically designed to ensure the highest performance with maximum robustness combined with a long lifetime.

Benefits

- UL Class 2 output, ensuring safe assembly and maintenance
- Easy to install with simple parallel wiring
- High reliability

Features

- Stable output voltage
- Wide ambient temperature range
- Protection against overpower and overvoltage
- Output short-circuit shutdown feature with automatic restart
- Compliant with California Title 24 technical requirements

Applications

Retail display lighting, linear accent lighting and refrigerated display lighting

- Shelf lighting
- Cove lighting
- Facade accent lighting
- Coolers and freezers

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	120	Vac	Performance
Rated input voltage range	108 ... 132	Vac	Operational safety
Rated input frequency	50 ... 60	Hz	Performance
Rated input frequency	45 ... 66	Hz	Operational safety
Rated input current	0.58	A	120Vac, @ rated output power
Rated input power	70	W	120Vac, @ rated output power
Power factor	0.98		120Vac, @ rated output power.
Total harmonic distortion	13	%	120Vac, @ rated output power.
Efficiency (typ)	86	%	120Vac, @ rated output power.

Electrical output data


Specification item	Value	Unit	Condition
Regulation method	Constant Voltage		Rated output voltage = 24VDC
Output voltage range	22.8 ... 25.2	Vdc	@ output current range 1.5 ... 2.5A
Output current range	0.1 ... 2.5	A	
Output voltage ripple	< 2	V _{pp}	
Rated output power	60	W	
Line regulation	< 1	%	
Load regulation	< 3	%	
Turn-on delay	< 0.5	s	With Integrate engine 24VDC module at rated output power
Output voltage rise time	≤ 50	ms	
Hold-up time	≥ 10	ms	

Logistical data

Specification item	Value
Product name	LED Transformer 60W 24V 120V PP
Order code	695125 00
Logistic code 12NC	9290 021 06080
Pieces per box	20

Wiring & Connections

Specification item	Value	Unit	Condition
Input cable cross-section	2 x 18	AWG	Length: 5ft, cUL listed with NEMA 1-15P polarized 120V plug
Voltage/current rating	125/10	V/A	
Input wire strip length	6 ... 7	mm	
Output cable cross-section	2 x 18	AWG	Length: 7in, cUL listed
Junction box	8	Fold	
Maximum output cable length	8	ft	FCC47CFR15 Class A: between driver and LED module




Warning: When using this product with extension cords, please adhere to all local and national codes.

Insulation

Insulation	Mains	LED
Mains		SELV (double)
LED	SELV (double)	

Dimensions and weight

Specification item	Value	Unit	Condition
Length (A1)	250.0	mm	
Width (B1)	40.0	mm	
Height (C1)	30.0	mm	
Fixing hole distance (A2)	240.0	mm	Fixing hole diameter (D): 4.2 mm
Fixing hole distance (B2)	29.0	mm	
Weight	390/13.8	gram/oz	
Junction box Length (G)	60.0	mm	
Junction box Width (E)	30.0	mm	
Junction box Height (K)	13.0	mm	
Cable hole diameter (J)	4.0	mm	
Cable hole distance (H)	10.0	mm	
Output cable Length (F)	7	in	
Input cable Length (L)	5	ft	



Operational temperatures and humidity

Specification item	Value	Unit	Condition
Driver ambient temperature	-20 ... +45	°C	At rated output power. Higher ambient temperature allowed as long as Tcase-max is not exceeded.
Tcase-min	-20	°C	
Tcase-max	+75	°C	Max. steady-state Tcase
Tcase-life	+75	°C	For rated driver lifetime
Maximum housing temperature	110	°C	In case of failure
Relative humidity	10 ... 90	%	Non-condensing
Ingress Protection *	IP20		
Sound rating	Class A		

*: The LED Power Driver is indoor use only. It is not allowed to be exposed to the elements like snow, water and ice. Exposure will lead to driver failure. It is the luminaire manufacturer's / installer's responsibility to prevent exposure.

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20 ... +80	°C	
Relative humidity	5 ... 95	%	Non-condensing