1

POWER PRODUCT Loadcentres



Contents

Odlitolito	
Application and Description	1-2
Product Offering and Specification Guide	1-3
Product Features and Customer Benefits	1-4
Catalogue Numbering System	1-5
EQL, SNC, & SEQ Single phase Loadcentres	
EQL Loadcentres with main lug only	1-6
SNC Loadcentres with main lug only	1-6
SEQ Service Entrance Loadcentres	1-6
EQL Loadcentres Type 3R	1-7
SEQ Service Entrance Loadcentres Type 3R	1-7
SEQ Dual Listed/cULus Loadcentres	1-8
EQ3 Single phase & EQ4 Three phase Loadcentres	1-9
SPA panel, Mini panels and Enclosed Breaker	1-10
EQG Generator Panels	
EQG 3 Pole	1-11
EQG 2 Pole	1-11
Plug in Branch Breakers Type Q	
Full Module (1" per pole)	1-12
Half Module (1/2" per pole): Twin and Quad Type	1-12
Replacement Main Breakers	1-13
Arc Fault Interrupters	1-14
Ground Fault Interrupters	1-14
Bolt-On Branch Breakers Type BQ	
Full Module (1" per pole)	1-15
Blue Line Breakers	1-15
Accessories and Replacement Parts	1-16 – 1-18
Surge Protection	
Circuit Breaker and Surge Protective Device (SPD)	1-19
Power Service Entrance Surge Protection	1-20
Telephone Service Entrance Surge Protection	1-21
Coaxial Service Entrance Surge Protection	1-21
Knockout Data for Loadcentres	1-22 - 1-23
Line Diagrams/Dimension Drawings for Breakers	1-24
Lug Data	1-24
Notes	1-25

Applications and Descriptions

Description

No. A	pplications	Products
1	Miscellaneous Applications	
	Standard Main Lugs Only Panel	EQL & SNC Loadcentre-Indoor & Outdoor Type
2	Single Family	SEQ Loadcentre – Indoor & Outdoor Type
3	Duplex Units, Small Apartment Building, Small Professional and Commercial Building (Two to Six Units Maximum)	a) SEQ Service Entrance Equipment – Indoor & Outdoor Type b) EQL Main Lugs Loadcentre – Indoor & Outdoor Type c) SNC Main Lugs Loadcentre - Indoor type
4	Office Building/Condo/Apartment Building (3Ø Application)	a) Switchboards b) Busways c) Modular Metering d) EQ4 Loadcentres Main Lug only or Main Breaker
5	Small Industrial/Commercial Building (3Ø Application)	a) Switchboards b) Busways c) 3Ø Modular Metering

d) EQ4 Loadcentres Main Lug Only or Main Circuit Breaker

A loadcentre is a metal enclosed distribution panel containing circuit breakers which distribute, protect and control lighting and power circuits in residential and light commercial applications, including single-family homes, townhouses, apartment buildings, and small office buildings.

All Siemens loadcentres can be classified into two types: main lug or main circuit breaker. Each Siemens loadcentre consists of three basic components: the enclosure, the interior, and the trim. The enclosure is used to contain the circuit breakers which mount on the interior. The trim seals the enclosure, offering protection to personnel from the environment.

A complete line of breakers and accessories which give Siemens loadcentres flexibility. For example, Ground Fault Interrupters protect personnel, an important consideration with the stress placed on personnel protection by the CEC. Handle ties, handle blocking devices, padlocking devices and filler plates are also available. Neutral lug kits in a variety of wire range sizes.



Included into all Loadcentres and Q Breakers

Description

Loadcentres

Product Offering and Specification Guide

Application

Main lug loadcentre

- 1 Phase 3 W 120/240V, 60 to 200A, 2/4 - 40/80 circuits
- 3 Phase 4W 120/208V, 100 to 225A, 12 - 42 circuits
- Outdoor Type 3R, 1 Phase 3 W, 120/240V, 100 to 200A, 8/16 -40/80 circuits

Main breaker loadcentre

- 1 Phase 3 W 120/240V, 60 to 200A, 12/24 - 60/120 circuits
- 3 Phase 4W 120/208V, 100 to 200A, 24 - 42 circuits
- Outdoor Type 3R, 1 Phase 3 W 120/240V, 100 to 200A, 16/32 - 40/80 circuits
- Dual certified loadcentre 1 Phase 3 W 120/240V, 100 to 200A, 38 circuits

Generator panel

- Generator panel 3 Pole 1 Phase 3 W 120/240V, 30 to 100A, 6/12-34/68 circuits
- Generator panel 2 Pole 1 Phase 3 W 120/240V, 30 to 100A, 8/16 - 36/72 circuits

SPA panel

 Type 3R, 1Phase 3 W 120/240V, 125A, 4/8 circuits

Mini panel/ Enclosed breaker,

- Indoor, 1Phase 3 W 120/240V, 60 & 125A, 2 circuits
- Outdoor Type 3R, 1 Phase 3 W 120/240V, 60 & 125A, 3 & 2/4 - 4/8 circuits

Circuit breaker

Plug- in

Interrupting rating of 10kA

- Full module
 - 1 Pole 15-70 Amp
 - 2 Pole 15-200 Amp
 - 3 Pole 15-100 Amp
- Half module

Twin: two single-pole, 15-15 to 40-15 Amp

40-15 Amp

Quad: two single-pole and one 2-pole inner breaker, 15-15 to 15-40 Amp

Bolt- on

Interrupting rating of 10kA & 22kA

- Full module
 - 1 Pole 15-70 Amp
 - 2 Pole 15-125 Amp
- 3 Pole 15-100 Amp

Ground fault circuit interrupter

1 and 2 Pole, 15-60A, 5 and

30mA sensitivity Arc fault circuit interrupter Interrupting rating of 10kA & 22kA

 1 Pole, 15 and 20 Amp Surge arrester breakers

- Two single pole breakers and one surge arrester, 15 and 20 Amp Surge protection device (SPD)
- Power service entrance surge protection
- Telephone service entrance surge protection
- Coaxial service entrance surge protection

Specification Guide -Loadcentres

Loadcentre enclosures and trims are formed of cold rolled, code gauge steel. All devices are finished with ANSI 61 grey paint (electro deposition painting process).

The combination flush/surface trim is flat and plumb in appearance. The Siemens Type 3R loadcentre features industry exclusive gasketed door for improved weatherproof protection. The enclosures and interiors provide 41/4" (108 mm) side wiring gutters for branch circuits. Main bus bars are formed of cold rolled, one piece tin plated (acid bath tin, zincate process) aluminum. Copper bus is also available. Main lugs, neutral assemblies, and ground bars are suitable for copper or aluminum conductors and comply with the requirements of CSA. The extended capacity fully distributed neutrals give a neutral termination at every breaker position, and is mounted, along with bus bars, on a base part made of engineered resin. CSA listed for 60/75YC wiring applications; ratings are as follows:

Individual circuit breakers are thermal magnetic, quick-make quick-break, trip free, plug-in construction. All two and three pole breakers are common trip. All circuit breakers are CSA listed under file #14374.

loadcentre main terminals 60/75YC cu/al

wire; branch breaker terminals-60/75YC


cu/al wire. All loadcentres are CSA listed

under file #13069.

*Series rating labels on all loadcentres.



Product Features and Customer Benefits



pan: Makes breaker installation

and removal quick and easy

Concentric knockouts: Makes wiring easy




Gasketed hinge door with outdoor loadcentre: Provides easy installation and improved weatherproof protection

Features and Benefits

Siemens provides the broadest product portfolio related to single and multifamily applications. Flexibility, innovation and quality are the hallmarks of Siemens products for single and multi-family applications providing the customer with unmatched value. One example is our quick-make quick-break circuit breakers which give homeowners peace of mind and fast acting circuit protection. Our whole house surge protection solutions, arc fault and ground fault circuit interrupters provide additional protection against the risks of electrocution, fire hazard and property damage. With the comprehensive selection of options and accessories, Siemens loadcentres and breakers are the smart choice for the conscientious customer.

Catalogue Numbering System

Catalogue Numbering System[®]













① The Catalogue numbering system applies only to EQL, EQL Type 3R, SEQ, SEQ.Type 3R, EQ4 and EQG loadcentres.

EQL & SEQ Single Phase Main Lug & Main Breaker Loadcentres

EQL Loadcentres with main lugs only 1 phase 3 wire 240 V AC max.

Selection and Ordering Data





EQL24125D

1001 800			
100110			
3331 123			
100			
3001 500			
1000			
	888	1	
2000			

330		
10000	[20000000000]	
	[00000000]	
	5555	
	4-1	
2003		
	E 100 (100 (1))	
3000		
55003		
3000		
1000		
1000		
9233	100000000000000000000000000000000000000	
100		
1933		
3333		
0.000		
2000		
100000		

SEQ40200

Number	Cotologue Number	Skid	Main	Dimens	ions - Inch	nes (mm)	Lug	Mounting	Door Kit	Factory
of Circuits	Catalogue Number	Qty.	Amps	Н	w	D	Data	Trim	Catalogue Number	Mod.
2/4	EQL260S	330	60	7 (178)	5 (127)	2 ^{3/4} (70)	3	surface	N/A	N/A
4/8	EQL4100	90	100	12 ^{5/8} (322)	6 ^{5/8} (168)	3 ^{1/2} (90)	1	comb.	N/A	N/A
8/16	EQL8100D*	72	100	14 ^{7/8} (378)	12 (305)	3 ^{3/4} (95)	4-2/0	comb.	DK8-A	N/A
12/24	EQL12125D3	45	125	16 ^{7/8} (429)	12 (305)	3 ^{3/4} (95)	4-2/0	comb.	DK12-A	1
16/32	EQL16125D ³	45	125	18 ^{7/8} (479)	12 (305)	3 ^{3/4} (95)	4-2/0	comb.	DK16-A	1)
24/48	EQL24125D ³	36	125	24 ^{1/8} (613)	13 ^{1/32} (331)	3 ^{3/4} (95)	4-2/0	comb.	DK24-A	1)
32/64	EQL32200D ³	27	200	33 (838)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	DKL32-2A	1
40/80	EQL40200D ³	27	200	33 (838)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	DKL40-2A	1
Note: EQ	L8100D through EQL4	0200D ③	are stocke	d comple	te with do	ors ¹	Neutral b	ar only on o	ne side of panel.	
12/24	SNC1224L1125 ³	28	125	18	14 ^{1/4}	37/8	2/0	comb.	RSCT1224L1125	N/A
16/32	SNC1632L1125®	28	125	21	14 ^{1/4}	37/8	2/0	comb.	RSCT1632L1125	N/A
24/48	SNC2448L1125 ³	28	125	24	14 ^{1/4}	37/8	2/0	comb.	RSCT2448L1125	N/A
30/48	SNC3048L1200 ³	21	200	30	14 ^{1/4}	3 ^{7/8}	300 kcmil	comb.	RSCT3048L1200	N/A
40/60	SNC4060L1200 ³	21	200	36	14 ^{1/4}	37/8	300 kcmil	comb.	RSCT4060L1200	N/A
Service E	ntrance Loadcentres \	with Fac	tory installe	ed main br	eaker 1 ph	nase 3 wire	240 V AC r	nax.		
12/24	SEQ12060SM	54	60	17 ^{5/8} (448)	13 ^{1/8} (333)	3 ^{3/4} (95)	6-2/0	comb.	DK1216SM-1	1)
16/32	SEQ16060SM ²	36	60	19 ^{5/8} (498)	13 ^{1/8} (333)	3 ^{3/4} (95)	6-2/0	comb.	DK1216SM-1	1
24/48	SEQ24060SM ^②	36	60	24 ^{1/8} (613)	13 ^{1/8} (333)	3 ^{3/4} (95)	6-2/0	comb.	DK24SM-1	1
12/24 16/32	SEQ12100SM SEQ16100SM	54 36	100	17 ^{1/2} (444)	13 ^{1/8} (333)	3 ^{3/4} (95)	4-2/0	comb.	DK1216SM-1	1
24/48 24/48 24/48	SEQ24100SM ^② SEQ24100SMK [■] SEQ24125SM ^②	36	100 125	24 ^{1/8} (613)	13 ^{1/8} (333)	3 ^{3/4} (95)	4-2/0	comb.	DK24SM-1	1)
24/48	SEQ24150 ² SEQ24200	27	150 200	27 (686)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	DKS24-2A	1
32/64	SEQ32100SM SEQ32125SM	27	100 125	27 ^{1/8} (689)	13 ^{1/8} (333)	3 ^{3/4} (95)	4-2/0	comb.	DK32SM-1	1
32/64	SEQ32150 SEQ32200	27	150 200	33 (838)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	DKS32-2A	1
40/80	SEQ40100 SEQ40125	27	100 125	36 (914)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	DKS40-1A	1
40/80	SEQ40150 SEQ40200 [©]	27	150 200	36 (914)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	DKS40-2A	1
60/120	SEQ60200	18	200	46 (1168)	14 ^{1/4} (362)	4 (102)	6-250 MCM	comb.	N/A	N/A
■ Standa	rd SEQ24100SMK with	h additi	onal knock	outs to be	ottom plat	te				

Note: Comb= Combination Flush/Surface mounted Certified for use with any combination of full or half module plug-in circuit breakers. Certiled for mounting vertical, horizontal or inverted and for use with CU/AL conductors including compact stranded. All neutral bar connectors are No. 14 - No.4.

Typical circuit rating (ie. 24/48) indicates the circuit capacity of the loadcentre is 24 full module (1") breaker of 48 half-module (1/2") breakers.

① Factory modification, see next page.

[®] For copper bus add suffix C to existing part number. 4 weeks delivery required.

 $[\]ensuremath{\texttt{③}}$ EQL and SNC available in White paint colour. Add "W" to end of part number.

EQL, SNC, & SEQ Single Phase Main Lug & Main Breaker Loadcentres

Selection and Ordering Data





Factory IV	odifications [©]											
Туре	Description	Catalogue Number	Example	Delivery								
EQL	White door and trim	add suffix W	EQL24125D W									
SNC	White door and trim	add suffix W										
SEQ Grey door installed White door and trim		add suffix D add suffix DW	SEQ24125SM D SEQ24125SM DW	2 weeks								
Door Kit	White Door kit	add suffix W	DK24SM-1 W									
Note: All	door kits are available in Gre	y and White colours.										
EQL	Copper Bus	add suffix CR	EQL24125DCR	4 weeks								



	40/80	EQL40200DCK	21	4
EQL24125DCR	* Neutral I	har only on one side	e of nar	اما

40/80

Weatherpr	therproof Loadcentre Main Lug Only, 1 phase 3 wire 120/240V AC max.										
Number	Catalogue Number	Skid Qty.	Main	Dimens	sions - Inc	ches (mm)	Lug Data	Mounting Trim	Factory Mod.	Hubs (sold seperately)	
Circuits			Amps	н	w	D				Conduit size (')	Catalogue Number
12/24	EQL12125DCR	35	125	19 ^{7/8} (505)	13 ^{3/4} (349)	5 (127)	6-2/0	surface only	N/A	3/4 1	ECHS075 ECHS100
24/48	EQL24125DCR	28	125	24 ^{7/8} (632)	13 ^{3/4} (349)	5 (127)	6-2/0	surface only	N/A	1 1/4 1 1/2	ECHS125 ECHS150
40/80	EQL40200DCR	21	200	335/8	15	5 (127)	6-250	surface	N/A	2 1/2	ECHS200 ECHS250

* Neutral bar only on one side of panel.

SEQ40200CR

	Number	Catalogue	Skid	Main	Dimensions - Inches (mm)			Lug	Mounting	Factory	(sold seperately)	
Circuits	Number	Qty.	Amps	Н	W	D	Data	Trim	Mod.	Conduit size (')	Catalogue Number	
	16/32	SEQ16100SMCR	35	100	21 ^{5/8} (549)	13 ^{9/16} (345)	5 (127)	6-2/0	surface only	N/A		
	24/48	SEQ24100SMCR	28	100	24 ^{5/8} (625)	13 ^{9/16} (345)	5 (127)	6-2/0	surface only	N/A	3/4 1 1 1/4	ECHS075 ECHS100 ECHS125
	24/48	SEQ24200CR	21	200	27 ^{1/2} (699)	15 (381)	5 (127)	6-250 MCM	surface only	N/A	1 1/2	ECHS150 ECHS200

5 (127)

6-250

MCM

surface

only

SEQ Type 3R Weatherproof Loadcentre with Factory installed main breaker 1 phase 3 wire 240V AC max.

361/2

(927)

200



Note: Both SEQ and EQL weatherproof panels are stocked complete with gasketed hinged door for improved weatherproof protection. All SEQ and EQL Type 3R panels come standard with copper bus.

15

(381)

SEQ24100SMCR

2 1/2

N/A

ECHS250

EQL, SNC, & SEQ Single Phase Main Lug & Main Breaker Loadcentres (continued)

Selection

Selection and Ordering Data



Dual Listed/c	Dual Listed/cULus Loadcentres 120/240V 1 phase 3 Wire											
Number of	Catalogue Number	Skid Qty.	Main Amps	Dimens	sions - Incl	hes (mm)	Lug Data	Mounting Trim	Door Kit			
Circuits				Н	w	D			Catalogue Number			
20	SEQ38100U SEQ38125U	27 27	100 125	36	14 ^{1/4} (362)	4	6-250MCM	comb.	DKS38-1A			
38	SEQ38150U SEQ38200U	27 27	150 200	(362)		(102)			DKS38-2A			

Branch breakers: Only 1" full module breakers that are both UL & CSA certified are allowed to be installed in this loadcentre; 1/2" twin and quad branch breakers must not be used as per NEC 384-14(a) and NEC-384-15. Consult Siemens Sales Rep. for details.

Application benefit: Allows modular home builders who have businesses in both US & Canada to carry only one line of inventory.

SEQ38200U

Selection

Loadcentres

EQ424BQ100

SFK225

TFK100

TFK225

EQ3 Single Phase & EQ4 Three Phase Loadcentres

Selection and Ordering Data

rdering Dat	ta									
EQ3 Single Ph	ase Loadcentres									
With Main Lug	gs only 1 phase 3 Wire 120	/240 V AC r	nax. 10KA							
Number of		Main	Dimensi	ions - In	ches (mm)		Mounting	Door	Factory	
Circuits	Catalogue Number	Amps	Н	W	D	Lug Data	Trim	Catalogue Number	Mod.	
24	EQ324225	225	34 (864)	14 ^{3/8}	1	6-300 MCM	comb.	DKEQ2430	(1)	
40	EQ340225	225	40 (1016)	(365)) (111)	o soo wiew	comb.	DKEQ42		
EQ3 Service E	ntrance Loadcentre									
With factory Ir	nstalled Main Breaker 1 ph	ase 3 Wire	120/240 V	AC max	k. 10KA					
24	EQ324BQ125	125	34 (864)	14 ^{3/8}	43/8	#6 2/0	b	DKEQ24BQ		
32	EQ332BQ125	125	40 (1016)	(365)	(111)	#6 - 2/0	comb.	DKEQ42	1	
EQThree Phas	se Loadcentres ^①									
With main lug	s only 3 phase 4 wire 240\	' AC max. '	10 KA							
12	EQ412100	100	28 (711)			14-2/0		DKEQ1218		
18	EQ418100	100	28 (711)			14 2/0	comb.	DKEQ1218	①	
24	EQ424225	225	34 (864)	14 ^{3/8} (365)	4 ^{3/8} (111)			DKEQ2430		
30	EQ430225	225	34 (864)			6-300 MCM		DKEQ2430		
42	EQ442225	225	40 (1016)					DKEQ42		
Service Entrar	nce Loadcentres									
With factory in	nstalled main breaker 3 ph	ase 4 wire	240 V AC	max. 10	KA.					
24	EQ424BQ100	100(BQ)	34 (864)			4-2/0		DKEQ24BQ		
42	EQ442QR100	100(QR)	46 (1168)							
42	EQ442QR125	125(QR)	46 (1168)	14 ^{3/8} (365)	4 ^{3/8} (111)	6-300 MCM	comb.	DKEQ42QR	1	
42	EQ442QR150	150(QR)	46 (1168)							
42	EQ442QR200	200(QR)	46 (1168)							
Factory Modifi										
Туре	Description	Catal	ogue Nun	nber	Ex	cample		Delivery		
EQ4	Copper Bus	ac	ld suffix	C	EQ	430225 C		4 Weeks		
Lug Kits For E	Q Loadcentres									
Catalogue Nu ber	um- Loadcen	tre Amps F	Rating			1	Description			
SFK100		100					ub-feed Kit /0 (Per Phase	e)		
SFK225		225			Sub-feed Kit 1/0-250 MCM (Per Phase)					
TFK100		100					ough-feed Ki '0 (Per Phase			

Note: Certified for use with either plug-in (Type Q) or bolt-on (Type BQ) branch breakers. Number of circuits can be doubled by use of plug-in (Type QT) twin breakers. Certified for mounting vertical, horizontal or inverted and for use with CU/AL conductor including compact stranded.

All neutral bar connectors are No. 14 - No. 4.

225

©AllThree Phase EQ loadcentres are stocked complete with doors. Interior only is not available.Must be ordered as a complete unit. **Note:** For copper bus add suffix C to existing part number. 4 weeks delivery required

Through-feed Kit

6-300 MCM (Per Phase)

SPA panel and Mini Panel/Enclosed Breaker

Selection and Ordering Data







SPA pane	I package, 3R enclosure	3R enclosure 120/240V 1 Phase 3 Wire										
Number	of Doolsons	Main	GFCI	Enclosure	Dimensions -	Inches (mm)	Hubs (sold seperately)					
Circuits		Amps.	Included	Н	w	D	Conduit Size (")	Catalogue Number				
	W0408ML1125-20	125	QF220A	12 ^{1/4} (312)	6 (153)	4 ^{1/4} (108)	Cover	ECHS000				
	W0408ML1125-30		QF230A				3/4	ECHS075 ECHS100				
4/8	W0408ML1125-40		QF240A				1 ^{1/4} 1 ^{1/2}	ECHS125				
	W0408ML1125-50		QF250A				2	ECHS150 ECHS200				
	W0408ML1125-60		QF260A				21/2	ECHS250				

2-POLE GFCI

Each package also includes a 4-point ground bar and French instructions.



Circuit Breaker Enclosures for Service Entrance and Commercial Use

EEMAC 1 Enclosure (Indoor) 1 phase 3 wire 240V AC Max.

Breaker	Catalogue	Main	Number	Dimensions - Inches (mm)		Lug Doto	
Range	Number	Amps.	of Poles	Н	w	D	Lug Data
15-60A	EQS260* ^①	60	1,2	7 ^{3/4} (197)	5 (127)	23/4	14-4 (70)
15-125A	EQS2125* ^①	125	1,2	13 (330)	6 ^{5/8} (168)	33/8	14-2/0 (86)


EQS260

*Does not accept quad type breaker.



WEQ60-4

EEMAC 3R We	eatherproof Enclosure, 1 phase	3 wire 240V	AC Max.
Full Module	Catalogue Number	Main	Dir
Circuits	Catalogue Nullibei	Amps.	- 11





W0816ML1125CU

Note: Package does not include a 4-point ground bar, please order: GBK4

Key Features:

Outdoor EEMAC 3R enclosure

- Accepts plug-in Q type breakers
- One piece bus bar construction
- Combination trim flush/surface

- ① The panels will not accommodate a 2 pole ground fault breaker (GFCI) or breaker with shunt trip.
- ² Hubs sold seperately
- 3 Not to be used as service entrance.

Hubs

Catalogue Number	Conduit size (')	Catalogue Number	Conduit size (')
ECHA075	3/4	ECHS075	3/4
ECHA100	1	ECHS100	1
ECHA125	1 1/4	ECHS125	1 1/4
ECHR075	3/4	ECHS150	1 1/2
ECHR100	1	ECHS200	2
ECHR125	1 1/4	ECHS250	2.5
ECHR150	1 1/2		

Generator panel Selection

Selection and Ordering Data

Generator Panel, 3 Pole 1 phase 3 wire 240V AC Max. Suitable for use with a generator having a bonded neutral conductor.

Number of	Catalogue	Skid		Dimens	ions - Incl	nes (mm)		Mounting
Circuits	Number	Qty.	Main Amps	Н	W	D	Lug Data	Trim
6/12	EQG630D EQG660D EQG680D EQG6100D	63	30 60 80 100	16 ^{7/8} (429)	12 (305)	3 ^{3/4} (95)	14-6 6-2/0 6-2/0 6-2/0	Comb.
10/20	EQG1030D EQG1060D EQG1080D EQG10100D	45	30 60 80 100	18 ^{7/8} (479)	12 (305)	3 ^{3/4} (95)	14-6 6-2/0 6-2/0 6-2/0	Comb.
18/36	EQG1830D EQG1860D EQG1880D EQG18100D	36	30 60 80 100	24 ^{1/8} (613)	13 ^{1/32} (331)	3 ^{3/4} (95)	14-6 6-2/0 6-2/0 6-2/0	Comb.
26/52	EQG2630D EQG2660D EQG2680D EQG26100D	27	30 60 80 100	33 (838)	14 ^{1/4} (362)	4 (102)	14-6 6-2/0 6-2/0 6-2/0	Comb.
34/68	EQG3430D EQG3460D EQG3480D EQG34100D	27	30 60 80 100	33 (838)	14 ^{1/4} (362)	4 (102)	14-6 6-2/0 6-2/0 8-2/0	Comb.



EQG630D



EQG860NSND

	2 Pole 1 phase 3 wi with a generator hav			conductor				
8/16	EQG830NSND EQG860NSND EQG880NSND EQG8100NSND	63	30 60 80 100	16 ^{7/8} (429)	12 (305)	3 ^{3/4} (95)	14-8 6-2/0 6-2/0 6-2/0	Comb.
12/24	EQG1230NSND EQG1260NSND EQG1280NSND EQG12100NSND	45	30 60 80 100	18 ^{7/8} (479)	12 (305)	3 ^{3/4} (95)	14-8 6-2/0 6-2/0 6-2/0	Comb.
20/40	EQG2030NSND EQG2060NSND EQG2080NSND EQG20100NSND	36	30 60 80 100	24 ^{1/8} (613)	13 ^{1/32} (331)	3 ^{3/4} (95)	14-8 6-2/0 6-2/0 6-2/0	Comb.
28/56	EQG2830NSND EQG2860NSND EQG2880NSND EQG28100NSND	27	30 60 80 100	33 (838)	14 ^{1/4} (362)	4 (102)	14-8 6-2/0 6-2/0 6-2/0	Comb.
36/72	EQG3630NSND EQG3660NSND EQG3680NSND EQG36100NSND	27	30 60 80 100	33 (838)	14 ^{1/4} (362)	4 (102)	14-8 6-2/0 6-2/0 6-2/0	Comb.

Note: The EQG panels are stocked complete with doors

Key Features:

- Ensures reliable and continuous operation, allows customers to permanently connect critical loads to back up generators in cases of main power failures
- Factory ready for use in both switched and non-switched neutral applications
- Additional number of generator circuits for more flexibility

Circuit Breakers

Type Q Plug-In Breakers

Selection and Ordering Data



Standard Package

48

24



Q115



Q215



Q315



Q1515NC



Q21515CTNC

© Typical catalogue number (ie. Q1515NC) represents two single-pole 15A circuit breakers - total width 1".

/	0	Q170			
Two Pole Comm	non Trip				
1	5	Q215			
2	.0	Q220			
25		Q225			
	30	Q230	24		
	85	Q235	27		
	10	Q240			
	0	Q250			
-	60	Ω260			
	0	Q270			
	30	Q280			
	00	Q290	5		
	00	Q2100			
	10 25	Q2110 Q2125			
	50	QN2150R@3	1		
20	00	QN2200R ^{@®}			
Three Pole Com	mon Trip				
1	5	Q315			
2	.0	Q320			
	25	Q325			
	80	Q330	3		
	.0	Q340			
	0	Q350			
	0	Q360			
/	0	Q370			
	80	Q380			
	0	Q390	2		
	00	Q3100			
Half Module (1/2	2" per pole) 10,00	00 A.I.C.			
Poles	Amps	Catalogue Number ^①	Standard Package		
	15-15	Q1515NC			
	15-20	Q1520NC			
	15-30	Q1530NC			
	15-40	Q1540NC			
QT .	20-15	Q2015NC			
Dual	20-20	Q2020NC	48		
(Twin)	30-15	Q3015NC			
	30-20	Q2030NC			
	30-30	Q3030NC			
	40-15	Q4015NC			
0 1 7					
Quad Type (1/2"	per pole) 10,000	A.I.C. Common Trip - centre poles	only.		
Poles	Ampere Rating	Catalogue Number ²	Standard Package		

Q21515CTNC

Q21520CTNC

Q21525CTNC

Q21530CTNC

Q21540CTNC

Catalogue Number

Q115³

Q120³ Q125

Q130

Q140

Q150

Q160

Q170

15-15 15-20

15-25

15-30

15-40

Full Module (1" per pole) 10,000 A.I.C

Ampere Rating

15 20

25 30

40

50

60

70

Single Pole

QT

Quad

Typical catalogue number (ie. Q21520CTNC) represents two single-pole, outer poles (two 15A 1-pole circuit breakers) and one 2-pole inner breaker with common trip (one 20A 2-pole circuit breaker) - total width 2".

③ Typical CSA Listed for frequent switching applications (SWD). 120V AC Fluorescent Lighting.

Requires 4 panel circuits, 2 adjacent and 2 opposite.
 Two twist outs should be only removed.


Will not fit in EQ3 or EQ4 loadcenters

Circuit Breakers


Surge Arrester and Replacement Main Breakers

Selection and Ordering Data





Selection and Ordering Data





1-Pole Combination Type AFCI



Arc-Fault and Ground Fault Circuit Interrupters

Combination



1-Pole Twin AFCI



1-Pole Dual Function AFCI/GFCI



1-Pole GFCI



2-Pole GFCI



1-Pole GFCI



2-Pole GFCI

		Interrupting Rating						
Poles	Ampere Rating	10Ka	65Ka					
		Catalogue Number						
	Combination Arc Fault Circuit Interupters (AFCI), Full Module (1" per pole) Detects all three possible types of arc faults: line-to-ground, line-to-neutral, and series.							
1	15 20	QA115AFCCSA QA120AFCCSA						
2	15 20	Q215AFCCSA Q220AFCCSA	Q215AFCH Q220AFCH	N/A N/A				

Dual Function AFCI/GFCI, Full Module (1" per pole)

The Dual Function Circuit Breaker combines Combination Type AFCI and GFCI, protecting against both Arc Faults and (5mA) Ground Faults. Includes Self Test as an added safety feature.

1	15	Q115DF	Q115DFH	Q115DFHH
'	20	Q120DF	Q120DFH	Q120DFHH

Ground Fault Circuit Interrupters (QFA), Full Module (1" per pole) Class A (5mA) Sensitivity Provides Class A (5mA) ground fault protection. Intended for personnel protection. Includes Self Test as an added safety feature.

1	15 20 30	QF115A QF120A QF130A	QF115AH QF120AH QF130AH	QF115AHH QF120AHH QF130AHH
2	15 20 30 40 50 60	QF215A QF220A QF230A QF240A QF250A QF260A	QF215AH QF220AH QF230AH QF240AH QF250AH QF260AH	N/A

Ground Fault Equipment Protection (QE), Full Module (1" per pole) 30mA Sensitivity Provides protection of equipment from damaging line-to-ground faults currents.

1	15 20	QE115 QE120	N/A N/A	N/A N/A
2	30 15 20 30 40 50	QE130 QE215 QE220 QE230 QE240 QE250 QE260	QE130H QE215H QE220H QE230H QE240H QE250H QE260H	N/A N/A N/A N/A N/A N/A



1-Pole Plug on **Neutral Arc Fault**



1-Pole Plug on **Neutral Ground Fault**

Breaker	Poles	Ampere	Interrupting Rating			
Туре	Poles	Rating	10KA	22KA	65Ka	
Plug on Neutral	1	15	Q1515AFCNCSA	N/A	N/A	
Twin Arc Fault	1	20	Q2020AFCNCSA	N/A	N/A	
Pig Tail Twin	1	15	Q1515AFCCSA	N/A	N/A	
Arc Fault	1	20	Q2020AFCCSA	N/A	N/A	
	1	15	QA115AFCNCSA	N/A	N/A	
Plug on	1	20	QA120AFCNCSA	N/A	N/A	
Neutral AFCI	2	15	Q215AFCNCSA	N/A	N/A	
	2	20	Q220AFCNCSA	N/A	N/A	
	1	15	QF115ANCSA	N/A	N/A	
Plug on Neutral GFCI	1	20	QF120ANCSA	N/A	N/A	
	1	30	QF130ANCSA	N/A	N/A	
Plug on Neutral	1	15	Q115DFNCSA	N/A	N/A	
AFCI/GFCI	1	20	Q120DFNCSA	N/A	N/A	

Type BQ Bolt-on[®] and Blue line Circuit Breakers

Selection

Selection and Ordering Data





BQ1B015



BQ2B015



BQ3B015

Ampere Rating	10,000 A.I.C. Catalogue Number	22,000 A.I.C. Catalogue Number	Std. Pkg
Single Pole			
15 20 25 30 40 50 60 70	BQ1B015 BQ1B020 BQ1B025 BQ1B030 BQ1B040 BQ1B050 BQ1B060 BQ1B070	BQ1B015H BQ1B020H BQ1B025H BQ1B030H BQ1B040H BQ1B050H BQ1B060H BQ1B070H	12
Two Pole Comm	non Trip		·
15 20 25 30 40 50 60 70 80 90 100 125	BQ2B015 BQ2B020 BQ2B025 BQ2B030 BQ2B040 BQ2B050 BQ2B060 BQ2B070 BQ2B080 BQ2B090 BQ2B100 BQ2B125	BQ2B015H BQ2B020H BQ2B025H BQ2B030H BQ2B040H BQ2B050H BQ2B060H BQ2B060H BQ2B070H BQ2B080H BQ2B090H	6
Three Pole Com	nmon Trip		
15 20 30 40 50 60 70 90 100	BQ3B015 BQ3B020 BQ3B030 BQ3B040 BQ3B050 BQ3B060 BQ3B070 BQ3B090 BQ3B100	BQ3B015H BQ3B020H BQ3B030H BQ3B040H BQ3B050H BQ3B060H BQ3B070H BQ3B090H BQ3B100H	4

BQ Screws are sold separately $^{\scriptsize\textcircled{\scriptsize{1}}}$



BL1-015

pe Blue line circuit breakers		
Ampere Rating	Catalogue Number	Standard Package
15	BL1-015	
20	BL1-020	
30	BL1-030	20
40	BL1-040	
50	BL1-050	
15	BL2-015	
20	BL2-020	10
30	BL2-030	10
40	BL2-040	
Description	Catalogue Number	Standard Package
Tie Handle	BLTH1	
6 - 1 Pole Fillers	BLF6	20


[©] Order line side screw kits separately: 8217-6 (6 pcs.) 8217-12 (12 pcs.) 8217-100 (100 pcs.) 8217-200 (200 pcs.)

Accessories and Replacement Parts

Selection

Selection and Ordering Data





These lug kits simply plug on to the bus of any SEQ or EQL Loadcentre as sub-feed or through-feed lugs to take advantage of CEC Rule 14-100 (c).

Accessories and Replacement Parts

Selection INSTA WIRE

SEQ Loadcentres



Door Kit



Door & Trim

# of	Catalogue	Doo	or Kit	Door 8	& Trim
Circuits	Number	Grey	White	Grey	White
12/24	SEQ12060SM	DK1216SM-1	DK1216SM-1W	DK12SM	DK12SMW
16/32	SEQ16060SM	DK12165W-1	DK12165W-1W	DK16SM	DK16SMW
24/48	SEQ24060SM	DK24SM-1	DK24SM-1W	DK24SM	DK24SMW
12/24	SEQ12100SM	DK1216SM-1	DK1216SM-1W	DK12SM	DK12SMW
16/32	SEQ16100SM	DK12105W-1	DK 12 16 5 WI-1 W	DK16SM	DK16SMW
24/28	SEQ24100SM SEQ24125SMK SEQ24125SM	DK24SM-1	DK24SM-1W	DK24SM	DK24SMW
24/48	SEQ24150 SEQ24200	N/A	N/A	DKS24-2A	DKS24-2AW
32/64	SEQ32100SM SEQ32125SM	DK32SM-1	DK32SM-1W	DK32SM	DK32SMW
32/64	SEQ32150 SEQ32200	N/A	N/A	DKS32-2A	DKS32-2AW
40/80	SEQ40100 SEQ40125	N/A	N/A	DKS40-1A	DKS40-1AW
40/80	SEQ40150 SEQ40200	N/A	N/A	DKS40-2A	DKS40-2AW
60/120	SEQ60200	N/A	N/A	DKS60-2A	DKS60-2AW

SEQ Loadcentres





Branch Breaker Cover

# of	Catalogue	Main Brea	aker Cover	Branch Bre	eaker Cover
Circuits	Number	Grey	White	Grey	White
12/24	SEQ12060SM			SEQ12060SM-T	SEQ12060SM-TW
16/32	SEQ16060SM			SEQ16060SM-T	SEQ16060SM-TW
24/48	SEQ24060SM			SEQ24060SM-T	SEQ24060SM-TW
12/24	SEQ12100SM	DKMCSM	DKMCSMW	SEQ12100SM-T	SEQ12100SM-TW
16/32	SEQ16100SM	DKIVICSIVI	DKING2INIAA	SEQ16100SM-T	SEQ16100SM-TW
	SEQ24100SM			SEQ24100SM-T	SEQ24100SM-TW
24/28	SEQ24125SMK			SEQ24125SM-T	SEQ24125SM-TW
	SEQ24125SM			SEQ24125SM-T	SEQ24125SM-TW
24/48	SEQ24150 SEQ24200	N/A®	N/A [©]	SEQ24-TA	SEQ24-TAW
20/04	SEQ32100SM	DKMCCM		SEQ32100SM-T	SEQ32100SM-TW
32/64	SEQ32125SM	DKMCSM	DKMCSMW	SEQ32125SM-T	SEQ32125SM-TW
32/64	SEQ32150 SEQ32200			SEQ32-T	SEQ32-TW
40/80	SEQ40100 SEQ40125	N/A ^①	N/A ^①	SEQ40100-T	SEQ40100-TW
40/80	SEQ40150 SEQ40200			SEQ40-T	SEQ40-TW
60/120	SEQ60200			SEQ60-T	SEQ60-TW

① Branch Breaker Cover part covers the main breaker area and branch circuits.

Selection *INSTA WHIRE*

EQL Loadcentres



		Door Kit	
# of Circuits	Catalogue Number	Grey	White
2/6	EQL260S		
4/8	EQL4100	N/A	N/A
8/16	EQL8100D	DK8-A	DK8-AW
12/24	EQL12125D	DK12-A	DK12-AW
16/32	EQL16125D	DK16-A	DK16-AW
24/48	EQL24125D	DK24-A	DK24-AW
32/64	EQL32200D	DKL32-2A	DKL32-2AW
40/80	EQL40200D	DKL40-2A	DKL40-2AW

SNC Loadcentres



	SNC	SNC D	oor Kit
# of Circuits	Catalogue Number	Grey	White
12/24	US2:SNC1224L1125	US2:RSCT1224L1125	US2:RSCT1224L1125W
16/32	US2:SNC1632L1125	US2:RSCT1632L1125	US2:RSCT1632L1125W
24/48	US2:SNC2448L1125	US2:RSCT2448L1125	US2:RSCT2448L1125W
30/48	US2:SNC3048L1200	US2:RSCT3048L1200	US2:RSCT3048L1200W
40/60	US2:SNC4060L1200	US2:RSCT4060L1200	US2:RSCT4060L1200W
12/24	US2:SNC1224L1125W	US2:RSCT1224L1125	US2:RSCT1224L1125W
16/32	US2:SNC1632L1125W	US2:RSCT1632L1125	US2:RSCT1632L1125W
24/48	US2:SNC2448L1125W	US2:RSCT2448L1125	US2:RSCT2448L1125W
30/48	US2:SNC3048L1200W	US2:RSCT3048L1200	US2:RSCT3048L1200W
40/60	US2:SNC4060L1200W	US2:RSCT4060L1200	US2:RSCT4060L1200W

EQ3 & EQ4 Loadcentres



	Catalogue Number		Doo	r Kit
# of Circuits	EQ3	EQ4	Grey	White
12	N/A	EQ412100	DKEQ1218	N/A
18	N/A	EQ418100	DREGIZIO	IN/A
24	EQ324225	EQ424225	DKEQ2430	N/A
30	N/A	EQ430225	DREUZ430	IN/A
40	EQ340225	N/A		
42	N/A	EQ442225	DKEQ42	N/A

EQ3 & EQ4 Service Entrance Rated



	Catalogue Number		Doo	r Kit
# of Circuits	EQ3	EQ4	Grey	White
24	EQ324BQ125	EQ424BQ100	DKEQ24BQ	N/A
32	EQ332BQ125	N/A	DKEQ42	N/A
		EQ442QR100	DKEQ42QR	N/A
42	N/A	EQ442QR125 EQ442QR125C EQ442QR150 EQ442QR200	DKEQ42QR	N/A

Selection

Loadcentres Surge Protection

Circuit Breaker and Surge Protective Device (SPD)

Features

- 2 inch wide plug-on design
 - Includes (2) 1 Pole circuits breakers
 - No loss of loadcentre spaces
- Easy to install and perfect for retrofit
- LEDs provide protection status

Benefits

By installing a Siemens Circuit Breaker and Surge Protective Device (SPD) in the loadcentre of the residence, surge protection is provided for all branch circuits[®].

Two green LED indicator lights are provided to show that surge protection is provided for all circuits connected to the loadcentre. These breakers should be used for circuit protection of frequently used household or facility circuits because the lights and devices connected to these circuits provide an effective indication that surge protection is being provided.

The circuit breaker and SPD utilize Siemens-built 150V AC, 40mm, metal oxide varistors (MOVs). The maximum impulse rating for the SPD module is 40kA. The standard interrupting rating for the circuit breakers is 10k AIC. All Type QP circuit breakers and SPD are plug-on style, with load terminals provided. The devices are rated for 120/240V AC and are calibrated for 40 degrees C maximum ambient applications.

Breaker Type	Ampere Rating	Catalogue Number	Surge Type
QP	(2) 15	QSA1515SPD	SPD
1- Pole	(2) 15	Q3A 13 133FD	350
120/240V AC	(2) 20	QSA2020SPD	SPD
10K AIC	(2) 20	USA20203FD	350

Catalogue Number	QSA1515SPD QSA2020SPD
Amperage	15 or 20 Amp
Number of Poles	(2) 1-Pole Circuit Breakers
Initial Clamping Level	240 Volts
Transient Energy Rating	360 Joules line-to-neutral 720 Joules line-to-line
Transient Suppression	500 volts peak, line-to-neutral
Voltage Rating	1000 volts peak, line-to-line
Peak Current Rating (impulse)	40,000 amperes
Discharge Voltage Characteristic	@ 1,500A, 600 volts @ 5,000A, 800 volts (both line-to-neutral)
Discharge Current Withstand Rating	10,000 amperes line-to-neutral
Circuit Breaker Interrupting Rating	10,000A, 120/240V AC
Listings/Certifications	UL, CSA Meets UL 1449 4th Edition



① For warranty information please refer to the surge website www.usa.siemens.com/surge

Loadcentres Surge Protection

Power Service Entrance Surge Protection

FirstSurge™

Total Home Protection

Siemens believes today's residential surge protectors come up short when protecting today's modern home filled with smart appliances and electronics.

This is why we developed our FirstSurge™ commercial class total home surge protectors. These electrical system surge protectors are sized for where you live. They will let you know when there is something wrong or when they are worn out.

Based upon thunderstorm frequency, geographic location, and home size, we developed a surge exposure map correlating with FirstSurgeTM current capacities known to provide years of protective service for each shaded area.

Sized For Where You Live

Model	Surge Capacity
FirstSurge™ Power	(FS060) 60,000 A
FirstSurge™ Plus	(FS100) 100,000 A
FirstSurge™ Pro	(FS140) 140,000 A



Know You're Protected:

3 Stage Commerical Grade Notification

When there is a problem, Siemens FirstSurge™ takes the guesswork out of knowing when it is time to be replaced. What will you see and hear when this occurs?

Audible Alarm: Beeps Green LED(s): Extinguish Red Service Light: Flashes

Ground Reference Monitoring (GRM)

FirstSurge™ is GRM-equipped notifying you a rare safety hazard exists due to a compromised electrical system neutral to ground bond. What will you see and hear when this occurs?

Audible Alarm: Beeps Green LED(s): Remains Lit Red Service Light: Flashes



*See warranty for details

Selection



Features & Benefits

- UL 1449 4th Ed Listed, CSA 22.2 No.269.2-13, Type 2 Surge Protective Device (SPD)
- Rated for 120/240 split phase panels up to 400A
- Surge Current Capacities:
 - 60.000 A
 - 100,000 A
 - 140.000 A
- 3 Stage Commercial Grade Notification
- Ground Reference Monitoring (GRM)
- Installs onto any brand loadcenter
- Type 4 rated outdoor enclosure
- 10 year product and connected equipment warranty*

Technical Specifications		
Surge Spike Capacity	FirstSurge™ Power (FS060) 60,000 A FirstSurge™ Plus (FS100) 100,000 FirstSurge™ Pro (FS140) 140,000	Α
Line Voltage	120/240 Split Phase, 50/60 Hz	
UL 1449 4th Ed VPR	L-N: 600 V L-G: 600 V N-G: 600 V L-L: 900 V	
Rated Voltage (MCOV)	150V – L-N, L-G, and N-G; 300V – L-L	
Response Time	<1 nanosecond	
Enclosure	NEMA 4X Indoor and Outdoor Rated	
Selection Information		
FirstSurge™ Power	FS060	
FirstSurge™ Plus	FS100	
FirstSurge™ Pro	FS140	
FirstSurge™ Flush Mount Kit	XMFMKIT	

Selection

Loadcentres Surge Protection

Telephone Service Entrance Surge Protection

Siemens FSPHONE is a 2 pair, hardwired surge protector for telephone, DSL or modem connected electronics in residential and light commercial applications. The FSPHONE protects against electrical power surges that can enter through the main telephone connection and is equipped with a failshort device to permanently ground the telephone line in the event of a power cross.

The FSPHONE is designed for indoor applications or can be mounted inside another weatherproof enclosure for outdoor mounting applications.

The FSPHONE4X consists of the FSPHONE plus a weatherproof enclosure to facilitate indoor or outdoor applications. The enclosure is molded of temperature and humidity resistant thermoplastic to resist cracking and discoloration. The cover can be secured with a tie wrap or similar locking device.

For total home protection please use FirstSurge™ to protect your incoming AC Power lines and FSPHONE to protect your incoming telephone line.

Features & Benefits

- UL listed
- Hardwired Modem/Fax/DSL protection
- Easy to install
- Exceptionally fast response time
- Low insertion loss
- Available with or without enclosure
- 5-Year product warranty*





Technical Specific	ations		
Catastrophic Surge Circuit		Yes	
Spike Capacity		200 Amps	
Let Through Voltag	e	<270 V	
Overcurrent Protec	tion	Yes	
Response Time		<1 nanosecond	
Enclosure		Yes	
Agency Approvals & Warranty			
UL/cUL Listings		497C	
Meets Telcordia (formally Bellcore) GR-974-CORE Requirements for Telecommunications Line Protectors		Yes	
Product Warranty		FS140	
Catalogue Numbe	r		
FSPHONE	2 pair protection module		
FSPHONE4X	2 pair protection module & 1 Weatherproof Enclosure		

UL Model No. - SATH2


Coaxial Service Entrance Surge Protection

Siemens FSCATV shields coaxial connected electronics in residential and light commercial applications against electrical transient damage, including lightning, from entering through the main cable connection.

FSCATV includes a section of coaxial cable with female to female splice for line side application. The Siemens warranty covers product defects for 5 years. To have complete protection for your equipment, home, or business, it is important to protect AC power lines and all data lines the equipment is connected through.

Features & Benefits

- UL Listed
- Rated for CATV, DSS, TV, VCR, and Cable Modem
- Easy to install
- Standard Female to Female F connector
- Low insertion loss
- Automatic recovery
- 5 Year product warranty*




Technical Spe	cifications			
Frequency Range		DC thru 1.5 GHz		
Catastrophic St	urge Circuit	Yes		
Spike Capacity		5000 Amps, 8/20 μSec		
Impedance		75 Ohms		
Overcurrent Pr	otection	Yes		
Return Loss		30dB @ 1 GHz		
Insertion Loss		<0.1dB		
Agency Appro	vals & Warranty			
UL/cUL Listings		497C		
Meets IEEE C6	2.41.1 Requirements	Yes		
Product Warrar	nty	FS140		
Catalogue Nu	mber			
FSCATV	F-Type Inline Coax Protector			
	T1 1 0 11 (FFF			


UL Model No. - SurgeassureTM SAVFFF

*See warranty for details

Knockout Data Selection


K.O. Qty							
			Α	В	С	D	
		Box	6	6	6	4	
EQL8		Тор	1	6	4	2	
		Bot.	1	6	4	2	
EQG 6		Box	6	6	6	4	
EQL 12		Тор	1	6	4	2	
EQG 8N	Bot.	1	6	4	2		
EQG 10		Box	6	8	8	4	
EQL 16		Тор	1	6	4	2	
EQG 12N	ISND	Bot.	1	6	4	2	
K.O. Trade Dia.							
Α	3/4" - 1" - 1 1/4" - 1 1/2"						
В	1/2" - 3/4"						
С	1/2"						
D	1/4"						






Top and Bottom

K.O. Qty.							
			Α	В	С	D	Е
EQG	18	Box	4	2	-	18	16
EQL	24	Тор	1	-	1	6	4
EQG	20NSND	Bot.	1	-	1	6	4
EQG	EQG 24		4	2	2	2	36
EQL	EQL 32		1	1	1	4	13
EQG 28NSND		Bot.	1	1	1	4	13
EQL 34		Box	4	2	2	2	36
EQL 40		Тор	1	1	1	4	13
EQG 36NSND		Bot.	1	1	1	4	13
	K.O. Trade Dia.						
Α	1 1/4" - 1 1/2" - 2" - 2 1/2"						
В	3/4" - 1" - 1 1/4"						
О	1/2" - 3/4" - 1"						
D	1/2" - 3/4"						
Е	1/2"						






Top and Bottom for EQL 24 EQG 18 EQG 20NSND



A



Top and Bottom for EQL 32 & 40 cir.

Knockout Data Selection

Service Entrance Loadcentres with Plug-in Breakers

			K.O. 0	lty.			
			Α	В	С	D	Е
SEQ 1	2 SM	Box	4	2	0	10	8
SEQ 1	6 SM	Тор	3	0	0	0	2
		Bot.	1	0	1	6	4
SEQ 2	4 SM	Box	4	2	-	18	16
SEQ 3	2 SM	Тор	3	-	-	-	2
		Bot.	1	-	1	6	4
		Box	4	2	2	2	22
SEQ 2	4	Тор	1	1	1	4	13
		Bot.	1	1	1	4	13
		Box	4	2	2	2	36
SEQ 32		Тор	1	1	1	4	13
		Bot.	1	1	1	4	13
		Box	4	2	2	2	36
SEQ 40		Тор	1	1	1	4	13
		Bot.	1	1	1	4	13
		Box	4	2	2	2	68
SEQ60	200	Тор	1	1	1	4	13
		Bot.	1	1	1	4	13
		K.	O. Trad	e Dia.			
Α	1 1	/4" - 1	1/2" - 2	2" - 2 1	/2"		
В	3/4" - 1" - 1 1/4"						
С	1/2" - 3/4" - 1"						
D	1/2" - 3/4"						
Е	1/2"						


A	A








Bottom for SEQ 12-16-24-32 SM





(A)




SEQ 24-32, 40,60



Service Entrace Loadcentres (Type 3R) Bottom Only








EQ Loadcentres with Plug-in or Bolt-on Breakers

K.O. Qty.							
A B C D E							
	Box	6	-	-	4	-	
Q 1PH Top		1	1	1	4	13	
EQ 3PH Bot.		1	1	1	4	13	
K.O. Trade Dia.							
1 1/4" - 1 1/2" - 2 1/2"							
3/4" - 1" - 1 1/4"							
1/2" - 3/4" - 1"							
1/2" - 3/4"							
1/2"							
	1 3/ 1/	H Top H Bot. 1 1/4" - 1 - 3/4" - 1" - 1/2" - 3/4" 1/2" - 3/4"	Box 6 Top 1 Bot. 1 K.O. Trad 1 1/4" - 1 1/2" - 2 3/4" - 1" - 1 1/4" 1/2" - 3/4" - 1" 1/2" - 3/4"	A B Box 6 -	A B C Box 6 Top 1 1 1 1	A B C D Box 6 4 Top 1 1 1 4 H Bot. 1 1 1 4 H EXAMPLE Box 1 1 1 1 4 H Bot. 1 1 1 1 4 H EXAMPLE Box 1 1 1/4" - 1 1/2" - 2 1/2" S/4" - 1" - 1 1/4" 1/2" - 3/4" - 1" 1/2" - 3/4" Top 1 Top 2 Top 3 Top	








A



Top and Bottom







Lug Data

Circuit Breaker Type	Circuit Breaker Ampere Rating	Cables Per Connector	Connector Wire Range		
	LOAD SIDE				
Q	15–30	1	#14–#8 AWG Cu #12–#8 AWG AI		
	40–50	1	#8-#6 AWG Cu #8-#4 AWG AI		
	60–70	1	#6-#2/0 AWG Cu #6-#2/0 AWG AI		
	80-125	1	#8-#2/0 AWG Cu #8-#2/0 AWG AI		
QNR	150–200	1	#1-300kcmil Cu-Al		
ОТ	15–30	1	#14–#8 AWG Cu #12–#8 AWG AI		
	40	1	#8 AWG CU-AI		
QF, QE	15–30	1	#14-#10 AWG Cu #12-#8 AWG AI		
	40–60	1	#8-#6 AWG Cu #8-#4 AWG AI		
QAF, QAFH	15–20	1	#14-#12 AWG Cu #12-#10 AWG AI		

Line Diagrams/Dimension Drawings for Circuit Breakers/Lug Data

