



**SKU:** SPAR-250

**UPC:** 0783669857283

**Features & Benefits:**

**Description:** RocketSplice Insulated Aluminum Splicer/Reducer, Dual Rated, Conductor Range 250-6, UL, CSA

## Specs

### Additional Class Attributes

Connection	Mechanical
Contains DE-OX®	No
Number of Conductors	2
Number of Poles	1
Number of Ports Tap	1
Wire Orientation	Parallel

### Dimensions

Drive Size Main	5/16
Drive Type Main	Internal Hex
Height (IN)	1.431
Height BX (IN)	3.75
Length (IN)	5.81
Weight (LB)	0.733
Weight BX (LB)	2.5949
Width (IN)	2.53
Width BX (IN)	6.5

### Material and Finish

Conductor Material	Aluminum
Connector Finish	Tin
Insulation Material	Plastisol
Material	Aluminum
Wire Binding Hardware Finish	Tin
Wire Binding Hardware Material	Aluminum

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### Bolt and Screw Sizes

Number of Wire Binding Screws per Port	1
Wire Binding Screw Size	5/8
Wire Binding Torque	275

## General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 3
Direct Burial	No
Dual Rated	Yes
NEMA Code	S-588-1
UPC Code	78366985728

## Testing Standards

CSA File Number	LR-29601
CSA Standard	C22.2 No. 65-03
Prop65 Compliance	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65warnings.ca.gov">www.P65warnings.ca.gov</a>
UL / CULUS Specification	UL 486A/B Listed
UL File Number	E6207

## Environment and Temperature

Temperature Rating	90°C
--------------------	------

## Color

Color	Clear
-------	-------

## Conductor Ranges

Conductor Range AL Solid (Secondary, tap, load)	NA
Conductor Range AL Stranded (Primary, run, main, line)	250 kcmil - 6 Str
Conductor Range AL Stranded (Secondary, tap, load)	250 kcmil - 6 Str
Conductor Range CU Solid (Primary, run, main, line)	NA
Conductor Range CU Solid (Secondary, tap, load)	NA
Conductor Range CU Stranded (Primary, run, main, line)	250 kcmil - 6 Str
Conductor Range CU Stranded (Secondary, tap, load)	250 kcmil - 6 Str
Conductor Range AL Solid (Primary, run, main, line)	NA

## Voltage

Voltage Rating	600 V
----------------	-------