


REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	5/26/08	CHNG'D LEVER TO KNOB	16169	PL	RP



VIEW A

NOTES:

READ AND FOLLOW ALL INSTRUCTIONS PROVIDED BY THE OPERATOR'S MANUAL AND WARNING LABELS BEFORE USING THIS TOOL.

DIMENSIONS IN [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE FOR REFERENCE ONLY.

SPECIFICATIONS

WEIGHT: 4.0 LBS. [1.8 KG].

JAWS:  
PATENTED HIGH STRENGTH STEEL, AND REPLACEABLE. YIELDING MINIMUM CONDUCTOR DISTORTION.

HANDLES:  
FIBERGLASS WITH COMFORT GRIP DESIGN AND ERGONOMIC HANDLE ENDS PROVIDES A POSITIVE ANTI-SLIP GRIP.

FIBERGLASS HANDLE MATERIAL MEETS OR EXCEEDS ASTM F711.

TYPE OF MECHANISM:  
HAND DRIVEN RATCHET WITH RAPID ADVANCE

\* TOOL WILL CUT THE FOLLOWING ACSR CABLE: 18 STRDS AL / 1 STRD ST AND 24 STRDS AL / 7 STRDS ST. OTHER CONFIGURATIONS ARE NOT RECOMMENDED AS TOOL DAMAGE MAY OCCUR.

CUTTING CAPACITY	
!WARNING DO NOT CUT ENERGIZED LINE	
ACSR - 556 KCMIL *	
COPPER - 600 KCMIL	
ALUMINUM - 750 KCMIL	
MAX. INSU. DIA - 1.40 IN. [35.56]	

TO ORDER BURNDY® PRODUCTS CALL		RATCHET CABLE CUTTER - HAND TOOL	
UNITED STATES:		ITEM NO: 25015086	
1-800-346-4175 (LONDONDERRY, NH)		CAT NO: RCC556	
CANADA:		SCALE: N/A	
1-800-361-6975 (QUEBEC)		DRAWN BY: D DOBRINSKI 1/23/98	
1-800-387-6487 (ALL OTHER PROVINCES)		CHECKER: D DOBRINSKI 3/18/98	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DSN APPVL: G HESKEY 3/4/98	
		MFG APPVL: B HARGROOVE 3/4/98	
		QC APPVL: S GRAY 3/4/98	
		MKT APPVL: ---	
		DRAWING NO	
		SE211273-01	
		REV	
		B	
		PROJECT #: ---	
		SIZE	
		D	
		DOCUMENT TYPE: Sales	
		SHEET 1 OF 1	
		REL LEVEL: AutoCAD	

