



NOTES:

1. APPROXIMATE AMP RATING: INDOOR = 700, OUTDOOR = 840. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 "UL" SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY®PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID, FLEXIBLE

ITEM NO: 000819

CAT NO: B2G12D75G70SV

SCALE: 1/1

DRAWN BY: P LAPONIUS 7/23/03
CHECKER: D BOISVERT 7/28/03
DSN APPVL: J MICHAUD 7/21/03
MFG APPVL: ---
QC APPVL: J BRODEUR 7/21/03
MKT APPVL: D HAMILTON 7/21/03
PROD FAM: ---
PROJECT #: ---
DOCUMENT TYPE: Sales
REL LEVEL: AutoCAD

BURNDY
PRODUCTS

DRAWING NO	REV
10031575	B

SHEET 1 OF 1