





REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	11/22/2019	NOTES UPDATED AND PARALLEL AND PERPENDICULAR CONFIGURATION SHOWN	52560	PB	RG



PARALLEL CONFIGURATION



PERPENDICULAR CONFIGURATION



**NOTES:**

- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.
- MATERIAL:  
CLAMP BODY : CAST COPPER ALLOY  
HARDWARE : SCREW AND WASHERS - STAINLESS STEEL  
NUT - BRONZE
- UL467 LISTED TO GROUNDING AND BONDING EQUIPMENT STANDARD.
- ACCOMMODATES WIRE 250 TO 500 kcmil.  
ACCOMMODATES STEEL 1/2" TO 1" THICK.
- INSTALLATION TORQUE:  
SCREW : 180 IN-LB  
NUT : 480 IN-LB
- WIRES CAN BE INSTALLED IN EITHER A PARALLEL OR PERPENDICULAR ARRANGEMENT, AS SHOWN IN INSTALLED VIEW.
- PRODUCT IS SUITABLE FOR DIRECT BURIAL APPLICATIONS.
- ADD SUFFIX "TN" FOR TIN PLATED FINISH ON CLAMP BODY AND CAP.

TO ORDER BURNDY® PRODUCTS CALL		GROUND CLAMP TO STEEL	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50097512	CAT. NO: GCS34HEX
CANADA: 1-800-387-6487		DRAWN BY: B.PARTHIBAN 01/22/2019	CHECKER: C.BECERRIL 06/28/2019
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DSN APRVL: R.R.RULAND 07/01/2019	MFG APRVL: --
		QA APRVL: E.RIVERA 06/26/2019	MKT APRVL: --
		PROD FAM: C&I - GROUNDING	DRAWING NO
		PROJECT #: --	SIZE
		DOCUMENT TYPE: SALES	50097517
		REL LEVEL: Released	B
		SHEET 1 OF 1	B