


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE	DIMENSIONS in. [mm]				
		L ± .03 [0,8]	W ± .01 [0,3]	C ± .015 [0,4]	M ± .03 [0,8]	H ± .01 [0,3]
PN22-2R	#2	.69 [17,5]	.20 [5,1]	.18 [4,6]	.59 [15,0]	.10 [2,5]
PN22-4R	#4	.69 [17,5]	.20 [5,1]	.18 [4,6]	.59 [15,0]	.13 [3,3]
PN22-6R	#6	.69 [17,5]	.20 [5,1]	.18 [4,6]	.59 [15,0]	.15 [3,8]
PN22-8R	#8	.78 [19,8]	.26 [6,6]	.26 [6,6]	.65 [16,5]	.17 [4,3]
PN22-10R	#10	.78 [19,8]	.31 [7,9]	.24 [6,1]	.62 [15,8]	.21 [5,3]

INSTALLATION TOOLS
CT-520
CT-1525 (A POCKET)
CT-2500 (CT-2525CH: A PKT)



#### NOTES:

##### 1. RECOMMENDED FOR:

- A. #26-22 AWG SOLID OR STRANDED COPPER WIRE
- B. 221°F [105°C] MAX. OPERATING TEMPERATURE
- C. 300 V. MAX. VOLTAGE RATING


##### 2. MATERIAL:

- A. STAMPING: .02" [0,5] THK COPPER, TIN PLATED
- B. HOUSING: NYLON, YELLOW
- C. SLEEVE: BRASS, TIN PLATED

##### 3. SEE [www.panduit.com](http://www.panduit.com) FOR PACKAGE QUANTITIES

##### 4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT

##### 5. WIRE STRIP LENGTH: 3/16" <sup>+1/32</sup><sub>-0</sub> [4,8mm <sup>+0,8</sup><sub>-0</sub>]

TITLE					
RING TERMINAL, NYLON INSULATED #26-22 AWG					
CUSTOMER DRAWING					
ITEM REVISION NAME			<b>PANDUIT</b>		
N41233BA/08					
DATASET FILE NAME			MATERIAL :		
N41233BA_DC/08					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]			SEE NOTES		
.x ± .1 [ 2.54 ]                      .xxx ± .005 [ .13 ]					
.xx ± .01 [ .25 ]                      ANGLES ± 5 °					
			THIRD ANGLE PROJECTION		
DRAWN BY			DRAWING NUMBER:		
DAW			A41233		
DATE		CHK	SCALE	SIZE	
-		RLS	N.T.S.	A	
SHT 1 OF 1					

08	04-27-15	JHNU	TMR	RGB	ADDED A POCKET WITH CT-1525, CT-2500	A41233
07	04-24-13	JBN	RTFI	RTFI	UPDATED DRAWING BORDER & TITLE BLOCK	A41233
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN