




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PANDUIT PART NUMBER | STUD SIZE | DIMENSIONS in. | | | | |
|------------------------|--------------|----------------|---------------|---------------|----------------|---------------|
| | | A $\pm .03$ | W $\pm .01$ | C min | M $\pm .03$ | H $\pm .01$ |
| PN18-6FF | #6 | .81 (20.57) | .28 (7.11) | .20 (5.08) | .65 (16.51) | .15 (3.81) |
| PN18-8FF | #8 | .88 (22.35) | .31 (7.87) | .23 (5.84) | .66 (16.76) | .17 (4.32) |
| PN18-10FF | #10 | .86 (21.84) | .35 (8.89) | .23 (5.84) | .66 (16.76) | .20 (5.08) |

NOTES :


1. UL LISTED AND CSA CERTIFIED FOR:
 - A. 600V. MAX. BLDG WIRE
(1000 V. MAX IN SIGNS, FIXTURES & LUMINARIES)
 - B. #22-16 AWG SOLID OR STRANDED
COPPER WIRE WITH THE CT-550, CT-500, CT1550, CT-1551
AND CT-400 (UL ONLY) INSTALLATION TOOLS.
 - C. #22-18 AWG SOLID OR STRANDED
COPPER WIRE WITH THE CT-100
AND CT-250 INSTALLATION TOOLS.
 - D. 221°F (105°C) MAX TEMP. RATING
 2. MATERIAL:
 - A. STAMPING - .032" (.81) THK COPPER, TIN PLATED
 - B. HOUSING - NYLON, RED
 - C. SLEEVE - BRASS, TIN PLATED
 3. STRIP LENGTH - $7/32^{+1/32}_{-0}$
 4. SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
 5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- 



LISTED
587H
E52164



CERTIFIED
LR31212

| | | | | | | | | | |
|-----|-------|------|---|------|-----|---|--------------|---------------|-----------------------|
| 08 | 8/11 | SHOR | MODIFIED NOTE #4, REMOVED NOTE #6 | | |  PANDUIT CORP. TINLEY PARK, ILLINOIS | | | |
| 07 | 10/04 | JHNU | ADDED NOTE 6. | | | | | | |
| 06 | 1/01 | KMD | CAD FILE SPEC. WAS N41239AA_PCD_05 | JAC | CCH | | | | |
| 05 | 12/96 | JAMB | ADDED DIM., "MIN WIRE INSUL. DIA." UPDATED NOTES | | | #22-18 BARREL NYLON INSULATED FLANGED FORK, .136" (3.45) MAX. WIRE INSUL. DIA. | | | |
| 04 | 10/94 | TH | REVISED TOOL/WIRE NOTES, DIMENSIONS | LA | KS | | | | |
| REV | DATE | BY | DESCRIPTION | CUST | PM | DRAWN BY DAW | CHK'D RLS | SCALE NONE | DRAWING NO. A41239 |