


1. USED FOR:
 - A. 600V MAX. VOLTAGE RATING
 - B. 105°C (221°F) MAX. TEMP. RATING
 - C. SOLID & STRANDED COPPER WIRE
2. SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
3. MATERIAL:
 - A. STAMPING: COPPER, TIN PLATED
 - B. HOUSING: NYLON, BLUE
 - C. SLEEVE: BRASS, TIN PLATED
4. WIRE STRIP LENGTH: $5,6^{+8}_{-0}$ ($7/32^{+1/32}_{-0}$)
5. INSTALLATION TOOLS: CT-1550, CT-2550 WITH
CT-2550CH CRIMP HEAD
6. DIMENSIONS IN BRACKETS ARE IN INCHES OR AWG



05	12/20/11	FS		Obsolete installation tools removed, UL information clarified, general dimensional updates.			
REV	DATE	BY	CHK	DESCRIPTION	ECN #	PM	CUST

1,5-2,5 mm² METRIC NYLON INSULATED,
FUNNELED ENTRY FORK TERMINAL

DRAWN BY	CHK'D	SCALE	DRAWING NO.
BDK	LM	NONE	A41518