


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]					TOOLS
	ENGLISH	METRIC	L ± .03 [0,51]	W ± .01 [0,25]	C ± .02 [0,38]	M ± .03 [0,51]	H ± .01 [0,25]	
PMNF2-3F	--	M3	.78 [19,81]	.23 [5,89]	.20 [5,05]	.64 [16,26]	.13 [3,30]	CT-100A *CT-160 *CT-260 *CT-400 *CT-460 CT-600-A (CT-500CH) CT-600-A (CT-550CH) CT-1550 CT-1551 CT-2500 (CT-2550CH)
PNF14-6F	#6	M3,5	.80 [20,32]	.28 [7,11]	.22 [5,59]	.66 [16,76]	.15 [3,81]	
PNF14-8F	#8	M4	.85 [21,59]	.31 [7,87]	.25 [6,35]	.69 [17,52]	.17 [4,32]	
PNF14-10F	#10	--	.87 [22,10]	.34 [8,64]	.26 [6,60]	.71 [18,03]	.20 [5,08]	
PMNF2-5F	--	M5	.86 [21,85]	.34 [8,58]	.25 [6,35]	.70 [17,78]	.21 [5,33]	
PNF14-14F	1/4"	M6	1.05 [26,67]	.44 [11,18]	.35 [8,89]	.80 [20,32]	.27 [6,86]	

*PANDUIT APPROVED TOOL

NOTES:

- cULus LISTED FOR:
 - 16-14 AWG [1,5-2,5 mm²] STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE
 - 600V. MAX. BLDG WIRE
(1000 V. MAX. IN SIGNS, FIXTURES & LUMINAIRES)
- SEE www.panduit.com FOR PACKAGE QUANTITIES
- MATERIAL:
 - STAMPING: .032" [0,8] THK COPPER, TIN PLATED
 - HOUSING: NYLON, BLUE
 - SLEEVE: BRASS, TIN PLATED
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT
- WIRE STRIP LENGTH: 5/16 ^{+1/32}₀ [7,9 ^{+0,8}₀]



TITLE
**#16-14 BARREL FORK, NYLON INSULATED FUNNELED
WIRE ENTRY, .162 [4,11] MAX WIRE INSUL DIA.**

CUSTOMER DRAWING

ITEM REVISION NAME

N41261AA/09


DATASET FILE NAME

N41261AA_DC/09A

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±
.XX ±

.XXX ±
ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

SEE NOTES

DRAWING NUMBER:

A41261

DRAWN BY

DATE

CHK

SCALE

SIZE

DAW

CJH

NONE

SHT 1 OF 1

A