

# 5MP HDCVI Vari-focal Bullet Camera

HDCVI

Starlight IR Camera with 16:9 Aspect Ratio



- 1/2.7-in. 5 MP Progressive-scan CMOS Sensor
- 5 MP (2880 x 1620) at 25 fps Maximum Resolution
- 2.7 mm to 13.5 mm Motorized Vari-focal Lens
- 16:9 Aspect Ratio for no Image Stretching
- Starlight Technology for Low-light Applications
- True Wide Dynamic Range (120 dB) and 3D Noise Reduction
- Built-in Microphone
- HDCVI, AHD, TVI, or CVBS Output, Switchable
- Maximum IR Length 80 m (262.47 ft), Smart IR
- IP67 Ingress Protection
- Five-year Warranty\*



### Smart IR

With IR illumination, detailed images can be captured in low light or total darkness. The camera's Smart IR technology adjusts the intensity of the camera's infrared LEDs to compensate for the distance of an object. Smart IR technology prevents IR LEDs from whitening out images as they come closer to the camera. The camera's integrated infrared illumination provides high-performance in extreme low-light environments.

### Multiple-format Support

The camera supports multiple video formats including, HDCVI, CVBS, AHD, and TVI. The camera can switch between these four formats via the OSD menu or the switch located on the video output cable, making the camera compatible with not only HDCVI DVRs but also most existing HD/SD DVRs.

### True Wide Dynamic Range

The camera achieves vivid images, even in the most intense contrast lighting conditions, using industry-leading wide dynamic range (WDR) technology. For applications with both bright and low lighting conditions that change quickly, True WDR (120 dB) optimizes both the bright and dark areas of a scene at the same time to provide usable video.

### Protection

The camera is subjected to rigorous dust and water immersion tests and certified to the IP67 Ingress Protection rating making it suitable for demanding outdoor applications. The camera allows for input voltage tolerance, suitable for the most unstable conditions for outdoor applications, and its 4KV lightning rating provides effective protection for both the camera and its structure against lightning.

#### System Overview

Experience the superior clarity of Dahua's 5 MP HDCVI cameras for vast coverage and superior image details. The 5 MP HDCVI series leverages existing coax infrastructures to deliver forensic-level images seamlessly and over long distances. The HDCVI camera offers multiple output formats that are easily switchable and a 16:9 aspect ratio. With a 16:9 format, images maintain a true, undistorted view without stretching, a feature not found on many 5MP HD over coax cameras. The camera is suitable for most applications, offering IR illumination for difficult lighting conditions, input voltage tolerance for inconsistent power supplies, and IP67 certification for operation in harsh outdoor environmental conditions.

### Functions

### Three Signals over One Coaxial Cable

HDCVI technology simultaneously transmits video, audio, and data over a single coaxial cable. Dual-way data transmission allows the HDCVI camera to communicate with an HDCVI DVR to send control signals or to trigger alarms.

### Starlight Technology

For challenging low-light applications, Dahua's Starlight Ultra-low Light Technology offers best-in-class light sensitivity, capturing details in low-light applications. The camera uses a set of optical features to balance light throughout the scene, resulting in clear images in dark environments.

### Long Distance Transmission

HDCVI technology guarantees real-time transmission over long distances without loss of video quality. HDCVI cameras provide the same resolution as most IP network camera systems using existing RG-59, RG-6, or CAT 6 UTP cabling.

### Simplicity

HDCVI technology seamlessly integrates traditional analog surveillance systems with upgraded, high-quality HD video, making it the best choice to protect security investments. The plug and play approach enables full HD video surveillance without the hassles of configuring a network.

# Pro Series | A52BFAZ

# Technical Specification

Image Sensor	1/2.7-in. CMOS Sensor
Effective Pixels	2880 (H) x 1620 (V), 5 MP
Aspect Ratio <sup>1</sup>	16:9
Scanning System	Progressive
Electronic Shutter Speed	1/4 s to 1/100,000 s
Minimum Illumination	Color: 0.001 lux at F1.6, 30 IRE 0 lux with IR on
S/N Ratio	More than 65 dB
IR Distance	Up to 80.0 m (262.47 ft)
IR On/Off Control	Auto, Manual
IR LEDs	Four (4)
Lens	
	Motorized Vari-focal
Lens	
Lens Lens Type	Motorized Vari-focal
Lens Lens Type Mount Type	Motorized Vari-focal ø14
Lens Lens Type Mount Type Focal Length	Motorized Vari-focal ø14 2.7 mm to 13.5 mm
Lens Lens Type Mount Type Focal Length Maximum Aperture	Motorized Vari-focal ø14 2.7 mm to 13.5 mm F1.6 Horizontal: 31.4° to 113.0° Vertical: 17.6° to 58.0°
Lens Lens Type Mount Type Focal Length Maximum Aperture Angle of View	Motorized Vari-focal ø14 2.7 mm to 13.5 mm F1.6 Horizontal: 31.4° to 113.0° Vertical: 17.6° to 58.0° Diagonal: 36° to 138.0°

### Installation Angle

Pan: 0° to 360° Tilt: 0° to 90° Rotation: 0° to 360°

### DORI Distances<sup>2</sup>

	Detect	Observe	Recognize	<b>Identify</b>
	(8 ppf)	(19 ppf)	(38 ppf)	(76 ppf)
Tele	64.0 m	25.60 m	12.80 m	6.40 m
	(210.0 ft)	(84.0 ft)	(42.0 ft)	(21.0 ft)
Wide	210.0 m	84.0 m	42.0 m	21.0 m
	(689.0 ft)	(275.59 ft)	(137.80 ft)	(68.90)

#### Video

Range

Resolution	Output	5 MP (2880 x 1620), 4 MP (2560 x 1440), 1080p (1920 x 1080), 720p (1280 x 720), 960H (960 x 480), D1 (704 x 480), CIF (352 x 240)
	HDCVI	5 MP at 25 fps, 4 MP at 30 fps, 1080p at 30 fps
Maximum	AHD	4 MP at 30 fps
Frame Rate	TVI	4 MP at 30 fps
	CVBS	960H
Video Output		One (1) BNC Output, HDCVI, AHD, TVI, CVBS switchable

	RG-59/U Coax	720p: 800 m (2624.67 ft) 1080p: 500 m (1640.42 ft) 5 MP: 500 m (1640.42 ft)	
Video Transmission <sup>3</sup>	RG-6/U Coax	720p: 1200 m (3937.01 ft) 1080p: 800 m (2624.67 ft) 5 MP: 700 m (2296.59 ft)	
	CAT 6 UTP (balun required)	720p: 450 m (1476.38 ft) 1080p: 300 m (984.25 ft) 5 MP: 300 m (984.25 ft)	
Day/Night		Auto (ICR)	
OSD Menu		Multi-language	
BLC Mode		BLC, HLC, HLC-Pro, True WDR	
WDR		120 dB	
Gain Control		Auto, Manual	
Noise Reduction		3D NR	
White Balance		Auto, Manual	
Advanced Features		Smart IR Mirror	
Privacy Masking		Off, On (8 Areas, rectangular)	
Certifications			
CE		EN55032:2015, EN 61000-3-2:2014, EN 61000-3-3:2013, EN55024:2010+A1:2015, EN 55035:2017, EN50130-4:2011+A1:2014,	
Safety		UL60950-1 EN 62368-1:2014+A11:2017 CAN/CSA C22.2 No.60950-1	
Electromagnetic Compatibility (EMC)		CFR 47 FCC Part 15 subpart B ANSI C63.4-2014	
Interface			
Audio		One (1) Built-in Microphone	
Electrical			
Power Supply		24 VAC ±25% or 12 VDC ±10%	
Power Consumption		Maximum 12.5 W (12 VDC, IR on)	
Environmental			
Operating Conditions		-30° C to +60° C (-22° F to +140° F) Less than 95% RH, non condensing	
Storage Conditions		-30° C to +60° C (-22° F to +140° F) Less than 95% RH, non condensing	
Ingress Protection		IP67	
Construction			
Casing		Metal	
Dimensions		244.10 mm x 90.40 mm x 90.40 mm (9.61 in. x 3.56 in. x 3.56 in.)	
Net Weight		0.79 kg (1.70 lb)	
Gross Weight		1.07 kg (2.40 lb)	

 To view the 16:9 video output on a Dahua HDCVI DVR you must update the DVR to the latest firmware. Obtain the latest firmware on the Dahua Wiki at <u>https://dahuawiki.com/Recorders</u>.

 The DORI distance is a measure of the general proximity for a specific classification to help pinpoint the right camera for your needs. The DORI distance is calculated based on sensor specifications and lab test results according to EN 62676-4, the standard that defines the criteria for the Detect, Observe, Recognize and Identify classifications.

 Transmission distance results verified by real-scene testing in Dahua's test laboratory. Actual transmission distances may vary due to external influences, cable quality, and wiring structures.

## Pro Series | A52BFAZ

## **Ordering Information**

Туре	Part Number	Description
5 MP HDCVI Camera	A52BFAZ	5 MP Starlight HDCVI IR Vari-focal Lens Bullet Camera, 16:9 Aspect Ratio
	PFA122	Waterproof Junction Box
	PFA130-E	Waterproof Junction Box
Accessories,	PFA151	Corner Mount
optional	PFA152-E	Pole Mount
	DH-PFM321D-US	12 VDC, 1 A Power Adapter
	DH-PFM800-4K	4K Passive HDCVI Balun

### Accessories

### Optional:



PFA122 Waterproof Junction Box



PFA152-E

PFA152-E Pole Mount



PFA130-E Waterproof Junction Box



DH-PFM321D-US 12 VDC, 1 A Power Adapter




PFA151

Corner Mount

DH-PFM800-4K Passive HDCVI Balun

### Mounting Diagram



### Dimensions (mm/in.)

