

SAFETY DATA SHEET

1. Identification

T & B CONTAX IK Product identifier

Other means of identification

SDS-00058 SDS number * See Section 16 **Product code** Corrosion Inhibitor Recommended use None known. **Recommended restrictions**

Manufacturer/Importer/Supplier/Distributor information

Company name ABB Installation Products Inc.

Address 860 Ridge Lake Blvd. Memphis, TN 38120

US

901-252-5000 ext.8324 Telephone

E-mail Not available.

Emergency phone number CHEMTREC - 24 HOURS: +1 703-741-5970

2. Hazard(s) identification

Physical hazards Not classified. **Health hazards** Not classified. **OSHA** defined hazards Not classified.

Label elements

Hazard symbol None. None. Signal word

Hazard statement The mixture does not meet the criteria for classification.

Precautionary statement

Observe good industrial hygiene practices. Prevention

Wash hands after handling. Response

Store away from incompatible materials. Storage

Disposal Dispose of waste and residues in accordance with local authority requirements.

Hazard(s) not otherwise

classified (HNOC)

None known.

Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	CAS number	%
Fiberglass	65997-17-3	10 - 30
Other components below reportable levels		70 - 90

All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

4. First-aid measures

Inhalation No specific treatment is necessary since this material is not likely to be hazardous by inhalation. Skin contact Wash off immediately with plenty of water. Get medical attention if irritation develops and persists. Eye contact

Flush eyes immediately with large amounts of water. Get medical attention if irritation develops

and persists.

Ingestion Rinse mouth. Do not induce vomiting. Never give anything by mouth to a victim who is

unconscious or is having convulsions. Get medical attention if symptoms occur.

T & B CONTAX IK SDS US Issue date: 05-November-2018

Most important symptoms/effects, acute and delayed

Symptoms may include redness, edema, drying, defatting and cracking of the skin. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Indication of immediate medical attention and special treatment needed

Treat symptomatically.

General information

Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media

Use extinguishing agent suitable for type of surrounding fire.

Unsuitable extinguishing

No restrictions known.

media

Specific hazards arising from the chemical

During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters

Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

and precautions for firefighter
Fire fighting

Move containers from fire area if you can do so without risk.

equipment/instructions
Specific methods

Use standard firefighting procedures and consider the hazards of other involved materials.

General fire hazards Product is nonflammable and does not support combustion.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Keep unnecessary personnel away. In case of spills, beware of slippery floors and surfaces. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Large Spills: Stop the flow of material, if this is without risk. Dike the spilled material, where this is possible. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water.

Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination.

Environmental precautions

Never return spills to original containers for re-use. For waste disposal, see section 13 of the SDS. Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling

Avoid contact with skin and eyes. Do not swallow. Handle and open container with care. When using do not eat or drink. Be aware of potential for surfaces to become slippery. Observe good industrial hygiene practices.

applicable, use process enclosures, local exhaust ventilation, or other engineering controls to

maintain airborne levels below recommended exposure limits. If exposure limits have not been

Conditions for safe storage, including any incompatibilities

Store in original tightly closed container.

8. Exposure controls/personal protection

Occupational exposure limits

controls

US. NIOSH: Pocket Guide to Chemical Hazards Value **Form** Components **Type** TWA Fiber. Fiberglass (CAS 3 fibers/cm3 65997-17-3) 3 fibers/cm3 Fibrous dust. 5 mg/m3 Fiber, total 5 mg/m3 fibers, total dust No biological exposure limits noted for the ingredient(s). **Biological limit values Exposure guidelines** Occupational Exposure Limits are not relevant to the current physical form of the product. Good general ventilation should be used. Ventilation rates should be matched to conditions. If Appropriate engineering

T & B CONTAX IK SDS US

established, maintain airborne levels to an acceptable level.

932596 Version: C Revision date: 12-July-2021 Issue date: 05-November-2018 2 / 7

Individual protection measures, such as personal protective equipment

Wear safety glasses with side shields (or goggles). Eye/face protection

Skin protection

Hand protection Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove

supplier.

Skin protection

Wear suitable protective clothing. Other

No personal respiratory protective equipment normally required. Respiratory protection Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective

equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Solid.

Form Paste. Thick grease

Tan. Color

Not available. Odor Not available. **Odor threshold** Hq Not available. Not available. Melting point/freezing point Initial boiling point and boiling Not available.

range

Flash point Not applicable. Not available. **Evaporation rate** Flammability (solid, gas) Not flammable.

Upper/lower flammability or explosive limits

Flammability limit - lower

Not available.

(%)

Flammability limit - upper

Explosive limit - lower (%)

Not available.

Not available.

(%)

Explosive limit - upper (%) Not available. Vapor pressure Not available. Not available. Vapor density Not available. Relative density

Solubility(ies)

Not available. Solubility (water) Not available. Partition coefficient

(n-octanol/water)

Not available. **Auto-ignition temperature** Not available. **Decomposition temperature** Not available. **Viscosity**

Other information

Not explosive. **Explosive properties** Not flammable **Flammability** Oxidizing properties Not oxidizing.

10. Stability and reactivity

Reactivity The product is stable and non-reactive under normal conditions of use, storage and transport.

Chemical stability Material is stable under normal conditions.

SDS US T & B CONTAX IK Issue date: 05-November-2018 Revision date: 12-July-2021

Possibility of hazardous

reactions

No dangerous reaction known under conditions of normal use.

Conditions to avoid Heat.

Incompatible materials Hazardous decomposition None known.

products

oxides of carbon

11. Toxicological information

Information on likely routes of exposure

Inhalation Not likely, due to the form of the product.

Skin contact May cause skin irritation. May cause eye irritation. Eye contact

Ingestion Ingestion may cause nausea, headache and dizziness.

Symptoms related to the physical, chemical and toxicological characteristics Symptoms may include redness, edema, drying, defatting and cracking of the skin. Symptoms

may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Not expected to be acutely toxic. **Acute toxicity**

Skin corrosion/irritation May cause skin irritation. Serious eye damage/eye May cause eye irritation.

irritation

Respiratory or skin sensitization

Respiratory sensitization Not a respiratory sensitizer.

Skin sensitization Not expected to be a skin sensitizer.

Germ cell mutagenicity No data available to indicate product or any components present at greater than 0.1% are

mutagenic or genotoxic.

This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA. Carcinogenicity

IARC Monographs. Overall Evaluation of Carcinogenicity

Fiberglass (CAS 65997-17-3) 3 Not classifiable as to carcinogenicity to humans.

NTP Report on Carcinogens

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not regulated.

Reproductive toxicity This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity -

single exposure

Not classified.

Specific target organ toxicity -

repeated exposure

Not classified.

Not an aspiration hazard. **Aspiration hazard**

12. Ecological information

Ecotoxicity

The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Persistence and degradability

No data is available on the degradability of this product.

Bioaccumulative potential

No data available. No data available.

Other adverse effects

Mobility in soil

No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions

Collect and reclaim or dispose in sealed containers at licensed waste disposal site.

Local disposal regulations

Dispose in accordance with all applicable regulations.

Hazardous waste code

The waste code should be assigned in discussion between the user, the producer and the waste

disposal company.

T & B CONTAX IK SDS US Issue date: 05-November-2018

932596 Version: C Revision date: 12-July-2021 Waste from residues / unused

products

Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see:

Disposal instructions).

Contaminated packaging

Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

Not regulated as dangerous goods.

IATA

Not regulated as dangerous goods.

IMDG

Not regulated as dangerous goods.

Transport in bulk according to Not established. Annex II of MARPOL 73/78 and the IBC Code

15. Regulatory information

US federal regulations

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

SARA 311/312 Hazardous No

chemical

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act

Contains component(s) regulated under the Safe Drinking Water Act.

(SDWA)

US state regulations

US. Massachusetts RTK - Substance List

Not regulated.

US. New Jersey Worker and Community Right-to-Know Act

Fiberglass (CAS 65997-17-3)

US. Pennsylvania Worker and Community Right-to-Know Law

Not listed.

US. Rhode Island RTK

Fiberglass (CAS 65997-17-3)

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 2016 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov.

T & B CONTAX IK SDS US Revision date: 12-July-2021 Issue date: 05-November-2018

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Fiberglass (CAS 65997-17-3)

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

^{*}A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 05-November-2018 **Revision date** 12-July-2021

Version С Health: 1 **HMIS®** ratings

Flammability: 0 Physical hazard: 0

NFPA ratings



Disclaimer

ABB Installation Products Inc. cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available.

ACJ266	
ACJ336	
ACJ40	

Product Codes

ACJ266	AL9	ALS44	ICS75-1	PKL56-1
ACJ336	AL9P	ALS44P	ICS76-1	PKL58-1
ACJ40	ALS1	ALS4P	ICS77-1	PKL66-1
AL10	ALS10	ALS5	ICS78-1	PKL66-12
AL11	ALS10P	ALS6	KL20-1	PKL68-1
AL12	ALS11	ALS60	KL22-1	PRS25N
AL12P	ALS11P	ALS60P	KL24	PRS30N
AL16	ALS12	ALS6P	KL25-1	PRS35N
AL16P	ALS12P	ALS7	KL31-1	PRS40N
AL18	ALS13	ALS8	KL36-1	QCD41
AL18P	ALS14	ALS8P	KL365-1	QCN50
AL20	ALS14P	ALS9	KL45-1	QCO02
AL20P	ALS15	ASP1000	KL46-1	QCO21
AL24	ALS16	ASP350	KL47-1	RCJ266M
AL24P	ALS17	ASP400	KL476-1	RCJ477M
AL28	ALS17P	ASP500	KL54-1	RS2525
AL28P	ALS18	ASP600	KL55-1	RS253

T & B CONTAX IK SDS US Issue date: 05-November-2018

932596 Version: C Revision date: 12-July-2021

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

AL32	ALS18P	ASP750	KL56-1	RS403
AL32P	ALS19	ICS61-1	KL57-1	RS4040
AL4	ALS2	ICS62-1	KL58-1	RS4525
AL44	ALS20	ICS63-1	KL64-1	RS4545
AL44P	ALS20P	ICS64-1	KL65-1	RS8080
AL4P	ALS23	ICS65-1	KL66-1	TR65
AL5	ALS23P	ICS66-1	KL67-1	TR613
AL6	ALS24	ICS67-1	KL68-1	
AL60	ALS24P	ICS68-1	KL69-1	
AL60P	ALS28	ICS69-1	KL698-1	
AL6P	ALS3	ICS70-1	PKL31-1	
AL7	ALS32	ICS71-1	PKL36-1	
AL7P	ALS32P	ICS72-1	PKL36-1025	
AL8	ALS3P	ICS73-1	PKL365-1	
AL8P	ALS4	ICS74-1	PKL46-1	

SDS US T & B CONTAX IK Issue date: 05-November-2018