



Reversing contactor assembly AC-3, 15 kW/400 V, 3-pole Size S2, Screw terminal 110 V AC 50 Hz/120 V AC 60 Hz Electrical and mechanical interlock !!! Phased-out product !!! Successor is SIRIUS 3RA2

size of contactor
product function
 protection class IP on the front
reference code according to IEC 81346-2
Substance Prohibitance (Date)
 ambient temperature during operation
 operational current at AC-3 at 400 V rated value
 operating power at AC-3 at 400 V rated value
type of voltage of the control supply voltage
control supply voltage 1 at AC

- at 50 Hz rated value
- at 60 Hz rated value

control supply voltage frequency

- 1 rated value
- 2 rated value

 number of NC contacts for auxiliary contacts per direction of rotation
 number of NO contacts for auxiliary contacts per direction of rotation
fastening method

height
width
depth
 type of electrical connection for main current circuit

S2
 Reversing contactor
 IP20
 Q
 05/01/2012
 -25 ... +60 °C
 32 A
 15 kW
 AC

 120 V
 120 V

 60 Hz
 60 Hz
 0
 0
 screw and snap-on mounting onto 35 mm DIN rail according to DIN EN 50022
 133 mm
 120 mm
 115 mm
 screw-type terminals

Further information

- Information- and Downloadcenter (Catalogs, Brochures,...)
<https://www.siemens.com/ic10>
- Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA1334-8XB30-1AK6>
- Cax online generator
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA1334-8XB30-1AK6>
- Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/3RA1334-8XB30-1AK6>
- Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA1334-8XB30-1AK6&lang=en
- Characteristic: Tripping characteristics, I_t, Let-through current
<https://support.industry.siemens.com/cs/ww/en/ps/3RA1334-8XB30-1AK6/char>
- Further characteristics (e.g. electrical endurance, switching frequency)
<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA1334-8XB30-1AK6&objecttype=14&gridview=view1>



