



## NVENT CADDY ROD LOCK COUPLER, 3/8" ROD

### CATALOG NUMBER

---

**CRLC37EG**



### FEATURES

---

Joins two sections of threaded rod by an easy "push-to-install" mechanism

Can be easily installed at the end of a threaded rod, or to any existing male thread

Plastic protection cap prevents dirt or structural coatings from obstructing the "push-to-install" mechanism

Prefabricated assemblies easily lift and lock into place, helping to save time and money

Works with slightly damaged threads and minor burrs on the threaded rod

### PRODUCT ATTRIBUTES

---

Material: Steel

Finish: Electrogalvanized

Static Load Safety Factor: 3.5:1

Rod Size: 3/8"

Height: 2.400"

Wrench Size 1: 1/2"

Wrench Size 2: 15/16"

Static Load: 1,000 lb


## ADDITIONAL PRODUCT DETAILS

---

Wrench Size 1 represents hex size used to tighten to threaded rod from structure. Wrench Size 2 represents nVent CADDY Rod Lock hex nut size.

## DIAGRAMS

---



## WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**nVent.com** CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2022 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.