



LED Highbay

38HB/LED/830/ND FB 6/1

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Available in both plug-and-play (UL Type A) and MainsFit (UL Type B) options, Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

E26 [Single Contact Medium Screw]
Yes
25000 h
50000X
38-85W
830 [CCT of 3000K]
200 °
3500 lm
White (WH)
3000 K
92.00 lm/W
<6
80
70 %
50 to 60 Hz
38 W

320 mA 85 W

Starting Time (Nom)	0.5 s	
Warm Up Time to 60% Light (Nom)	0.5 s	
UL Type	Type B - bypass the ballast	
Power Factor (Nom)	0.92	
Voltage (Nom)	120 V	
Temperature		
T-Case Maximum (Nom)	90 °C	
Controls and dimming		
Dimmable	No	
Mechanical and housing		
Bulb Finish	Frosted	
Bulb Shape	T-shape	
Approval and application		
Energy Consumption kWh/1000 h	- kWh	
Product data		
Order product name	38HB/LED/830/ND FB 6/1	
EAN/UPC - Product	046677541927	
Order code	929001989704	


Lamp Current (Nom)

Wattage Equivalent

LED Highbay


Numerator - Quantity Per Pack	1	Net Weight (Piece)
Numerator - Packs per outer box	6	
Material Nr. (12NC)	929001989704	

Dimensional drawing




38HB/LED/830/ND FB 6/1

Photometric data



LEDTrueForce E26 120-240V 38HB



LEDTrueForce E26 120-240V 38HB 830 37W


Product	D	с
38HB/LED/830/ND FB 6/1	138 mm	238 mm

0.247 kg

LEDTrueForce E26 120-240V 38HB 830 37W

LED Highbay

Lifetime



LEDTrueForce E26 120-240V

LEDTrueForce E26 120-240V



© 2022 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2022, January 11 - data subject to change