


SCH

PORTABLE MULTIPURPOSE HEATER



EFFICIENT, SAFE AND VERSATILE

Any construction worker will tell you that the SCH is the fast-acting heating unit most often found on construction sites, hence its nickname: “the construction heater.” Housed in a 20-gauge steel casing, it features a rugged protective grille and nichrome element for instant heat at start-up. Despite its small size, this heating powerhouse boasts 4800 W. The SCH can be placed on the ground or against a wall, using a support bracket, available as an option. This heater is right at home on construction sites and in workshops and garages. Choose the SCH when you need rapid, reliable heat.

SAFE AND RUGGED

20-GAUGE STEEL

4800 W HOUSED IN A SMALL UNIT

OPEN COIL GENERATES INSTANT HEAT

PERMANENTLY ENCLOSED LUBRICATED MOTOR (SCH4800T)

VERSATILE: PERMANENT OR TEMPORARY INSTALLATION WITH OPTIONAL SUPPORT BRACKET

COLOURS

- **standard:** red (SCH48T models), canary yellow (SCH4800T)

FINISH

- epoxy-polyester powdercoat

MANUFACTURING

- 20-gauge steel cabinet
- sturdy handle for portability that also serves as cord rack and which adapts to the mounting bracket
- 6 ft. (2 m) 12 Awg. molded cable with 3-prong grounded, 30 A 250 V plug (except for SCH48TWBPL)
- 6 ft. (2 m) 12 Awg. molded cable for hard-wired connection (SCH48TWBPL)
- thermal protection with automatic reset

MOTOR

- 250 CFM fan (SCH48T models)
- permanently enclosed lubricated motor and 300 CFM fan (SCH4800T)

ELEMENT

- nichrome element ensuring increased comfort
- cone-shaped to concentrate the air around the element

CONTROL

- built-in thermostat with control knob protector

INSTALLATION

- connects to a standard 30 A 250 V grounded receptacle (except for SCH48TWBPL)
- hard-wired into a wall junction box (SCH48TWBPL)
- mounting bracket that can rotate at 360° while preventing the unit from tipping

WARRANTY

- three years (SCH4800T)
- two years (SCH48T models)

IDEAL FOR:

construction site

ACCESSORY

PRODUCT	DESCRIPTION
SCH-WBB	mounting bracket (models with plug)



TECHNICAL SPECIFICATIONS

PRODUCT	POWER	VOLTAGE	CONNECTION	MOUNTING BRACKET	COLOUR	WEIGHT	
CODE	WATTS	VOLTS				KG	LB
SCH48T	4800/3600	240/208	30 A 250 V PLUG	NO	RED	5.9	13
SCH4800T	4800/3600	240/208	30 A 250 V PLUG	NO	CANARY YELLOW	5.9	13
SCH48TWB	4800/3600	240/208	30 A 250 V PLUG	YES	RED	5.9	13
SCH48TWBPL	4800/3600	240/208	HARD-WIRED	YES	RED	5.9	13

THROW DISTANCE AND HEAT RISE

MODEL	UNITS	THROW DISTANCE		HEAT RISE	
		M	FT	°C	°F
SCH48T	4.8	5.9	19'4"	81	145
SCH4800T	4.8	6.4	21'	70	125

TECHNICAL DRAWINGS

