



Pass and Seymour
20A, 125V Heavy Duty Spec Grade Plug Load Timer Receptacle
Part No. PLT26351W



New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of P&S Plug Load Controllable solutions will take a load off your mind and a load off your customers' electric bills.

Features & Benefits

Receptacle compliant with 2014 NEC, CA Title 24, and ASHRAE 90.1.

Power button on face serves as a manual override to scheduled programs.

Corrosion-resistant, plated steel strap locked into face and back body to resist pulling away from face/body assembly.

Clear LCD display shows program status, ON/OFF status, current time, and day of the week.

Center panel flips open for easy, three button programming.

.032 inch thick, brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Products meets requirements of UL498B: Receptacles with integral switching means.

Two individual programs can be set to automatically control plug loads.

Bottom half of device features a single receptacle that is automatically controlled by the time clock.

Feed-thru capability allows for downstream control of multiple receptacles.

Permanently molded power symbol on face identifies controlled receptacle in accordance with ASHRAE 90.1, NEC, and Title 24.

Auto-ground eliminates the necessity to terminate grounding conductor in device.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007039962	Country Of Origin	China
Application Sector	Commercial	Standard	RoHS, CSA Listed, CuUS, UL Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Dielectric Strength Withstands 2000V minimum Phase Single

Connection Screw terminals Number of Wires 3

Temperature Rating Maximum continuous +60°C, minimum
-40° without impact Number of Poles Double Pole

Wire Size #14 - #10 AWG Copper Conductor Only Voltage 125 V

Environmental Conditions UL94 V2
