



Catalog Number
Notes
Type

Contractor Select™

RB56 RB56S SWW5

RetroBasics™ 5 5/8" Switchable White LED Trim Kit

RetroBasics 5 5/8" LED trim kits provide the most economical solution for efficiently lighting a space using LED technology with virtually zero maintenance. This LED downlight is designed to work in both 5" and 6" housings and can be used to provide general illumination in any room. Use as an option to replace legacy incandescent technology in an already installed housing or pair with the quick connect LED housings for a low-cost LED downlight solution. The LED trim maintains at least 70% light output for 50,000 hours.

FEATURES:

- 5 switchable white color temperatures to choose from via switch; 2700K, 3000K, 3500K, 4000K, 5000K CCT; 90 CRI. Switch is factory preset at 3000K CCT
- Dimmable flicker-free dimming from 100% to 10%
- Non-conductive thermal plastic trim ideal for dead front applications
- Low profile construction optimized for wider fixture spacings
- Baffle and smooth trim options available offering a choice of traditional or more modern aesthetic
- Trim features quick connect plug for easy electrical connection in seconds
- Torsion springs are pre-installed and designed to fit into most 5" or 6" compatible recessed housings

APPLICATIONS:

- Retrofit into existing recessed housings or use with quick connect housings for new construction or remodel applications
- Wet rated and air-loc: perfect for showers, bathrooms, and outdoor soffits
- For use with housings installed in IC rated applications (direct contact with insulation)



RB56



RB56S



CONTRACTOR PACK (CP6) ORDERING EXAMPLES:

Example 1: Ordered in Qty of 1

Ordered Line: Qty: 1 RB56 SWW5 CP6 MW M2
 *Will receive 1 box with 6 units not individually packaged

Example 2: Ordered in Qty of 2

Ordered Line: Qty: 2 RB56 SWW5 CP6 MW M2
 *Will receive 1 master carton that includes 2 separate boxes with 6 units in each box not individually packaged

Catalog Number	UPC	Description	Replaces Up To	Lumens	Input Watts	CCT	CRI	Voltage	Finish	Dimming Protocol	Pallet qty.
RB56 SWW5 MW M6	00196182808999	5 5/8" Switchable White LED Baffle Trim Kit	75W Incandescent	860	10.2W	2700K-5000K	90	120V	White	100% to 10%	240
RB56 SWW5 CP6 MW M2	00196182809477	5 5/8" Switchable White LED Baffle Trim Kit	75W Incandescent	860	10.2W	2700K-5000K	90	120V	White	100% to 10%	60
RB56S SWW5 MW M6	00196182750144	5 5/8" Switchable White LED Smooth Trim Kit	75W Incandescent	860	10.2W	2700K-5000K	90	120V	White	100% to 10%	360
RB56S SWW5 CP6 MW M2	00196182750229	5 5/8" Switchable White LED Smooth Trim Kit	75W Incandescent	860	10.2W	2700K-5000K	90	120V	White	100% to 10%	36



Pairs perfectly with Juno housings for a complete downlight solution: Order housings as separate catalog number.

QC6 Series - New Construction Quick Connect LED Housing



QC6R Series - Remodel Quick Connect LED Housing



PERFORMANCE DATA

RB56 /RB56S	
Input Voltage	120V
Input Power Typical	10.2W (+/-5%)
Power Factor	.9
Frequency	60 Hz
EMI/RFI	FCC Title 47, Part 15 Class B (consumer)
Minimum Starting Temp	-20°C (-4°F) minimum

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25° C

**LIGHTING PERFORMANCE DATA
DONNÉES SUR LE RENDEMENT
DE L'ÉCLAIRAGE**

Light Appearance (CCT)
Aspect de la lumière (CCT)

2700K soft white | blanc doux

787 lumens | 77 lumens per watt

3000K warm white | blanc chaud

825 lumens | 81 lumens per watt

3500K neutral white | blanc neutre

862 lumens | 85 lumens per watt

4000K cool white | blanc froid

859 lumens | 84 lumens per watt

5000K daylight | blanc neutre

799 lumens | 78 lumens per watt

Watts **10.2**

Color Accuracy (CRI) **90**
Précision des couleurs (CRI)



Specifications

DOWNLIGHT LED TRIM KIT:

Molded thermal plastic housing with non-conductive trim frame offered in baffle or smooth design in matte white finish • Pressed-in diffusing lens optimized for concealing the LEDs from direct view in the on and off state • All-in-one design where LED light engine mounts directly to the trim for ease of installation into existing 5" or 6" recessed housings with medium base sockets or quick connect LED housings • Provided with torsion springs.

LED LIGHT ENGINE:

LEDs are mounted directly to housing providing superior thermal management to ensure long life • Switchable white LED color temperature technology offers 2700K, 3000K, 3500K, 4000K, 5000K all in one trim • Switch factory set at 3000K • 90 CRI minimum • Accommodates 120 volts AC at 60Hz • Dimmable with most standard incandescent, magnetic low voltage and electronic low voltage dimmers • For a list of compatible dimmers, see [JUNORBSERIES-DIM](#).

OPTICAL SYSTEM:

Regressed, diffused lens at end of mixing chamber to provide even light distribution for general illumination • Optimized for wide fixture spacings • Up to 860 nominal lumens is equivalent to 75W BR30 lamp.

ELECTRICAL CONNECTIONS:

Trim features quick connect plug installed as standard for installation into Juno quick connect housings with mating connector • Trim ships with a medium base socket adapter whip for installation into 5" or 6" incandescent housings with medium base sockets.

LIFE:

Rated for 50,000 hours at 70% lumen maintenance.

LABELS:

CSA certified to US and Canadian safety standards • ENERGY STAR® certified product • Suitable for wet location • Air-Loc certified in accordance with ASTM E283-2004 • NOM Certified • Can be used to comply with California Title 24 Part 6 High Efficacy LED light Source Requirements • T20 Certified.

TESTING:

All reports are based on published industry procedures; field performance may differ from laboratory performance.

WARRANTY:

5-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at: www.acuitybrands.com/support/warranty/terms-and-conditions

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

Dimensions

