

# RE25 – RE30

## ELECTRONIC RELAY – LOW VOLTAGE

### CONTROL


- pulsed signal (PWM) or all or nothing (on/off) at 24 Vac, 3-32 Vdc signal
- with a transformer (RE253T)
- compatible with the STE241, T822K1034, T87K1015, D010 and ET180 thermostats
- two additional relays without transformers can be added to the same control circuit as a relay with a transformer
- installing more than four relays without transformers to the same thermostat is not recommended

### INSTALLATION

- the relay must be installed in an external junction box

### WARRANTY

- three years



PRODUCT	DESCRIPTION
RE253C	ELECTRONIC LOW VOLTAGE RELAY [25 A @ 120 V, 208 V, 240 V, 277 V OR 347 V]
RE253T	ELECTRONIC LOW VOLTAGE RELAY [25 A @ 208 V, 240 V, 277 V OR 347 V] (W/TRANSFORMER)
RE306C	ELECTRONIC LOW VOLTAGE RELAY [30 A @ 120 V-600 V]

Dimensions: RE253: 4.10 in. x 4.10 in. x 2.10 in. (104.1 mm x 104.1 mm x 53.3 mm) / RE306C: 4.76 in. x 4.70 in. x 3 in. (120.9 mm x 119.4 mm x 76.2 mm)



# RE15

## ELECTRONIC RELAY – LOW VOLTAGE – SMALLER-SIZED

### CONTROL


- pulsed signal (PWM) or all or nothing (on/off) at 24 Vac, 3-32 Vdc signal
- with a transformer (RE153T)
- compatible with the STE241, T822K1034, T87K1015, D010 and ET180 thermostats
- two additional relays without transformers can be added to the same control circuit as a relay with a transformer
- installing more than four relays without transformers to the same thermostat is not recommended

### INSTALLATION

- the relays must be installed inside the junction box of the heating unit

### WARRANTY

- three years



PRODUCT	DESCRIPTION
RE153	ELECTRONIC LOW VOLTAGE RELAY [15 A @ 120 V-347 V]
RE156	ELECTRONIC LOW VOLTAGE RELAY [6 A @ 120 V-600 V]
RE153T	ELECTRONIC LOW VOLTAGE RELAY [15 A @ 208 V-347 V] (W/TRANSFORMER)

Dimensions: RE153 and RE156: 3.31 in. x 2.17 in. x 0.89 in. (84.1 mm x 55.1 mm x 22.6 mm) / RE153T: 3.31 in. x 2.17 in. x 1.5 in. (84.1 mm x 55.1 mm x 38.1 mm)

