

ELECTRONIC CONVECTOR

MIR SERIES

THE MOST DISCREET ON THE MARKET!

The new MIRAGE™ electronic convector is the result of a combination of a unique look that is modern and discreet, paired with unquestionable efficiency.

Available with an ultra precise integrated electronic thermostat or no thermostat and in several voltages, the MIRAGE™ is suitable for rooms in both the home and business. The MIRAGE™ blends in with any decor with its simple facade and elegant design.

MIRAGE™



HARMONIZES DISCREETLY WITH ANY DECOR

NEW STYLISH WHITE SATIN FINISH

STURDY ONE-PIECE FRONT PANEL

TOTALLY QUIET

BUILT-IN ELECTRONIC THERMOSTAT (OPTIONAL)

WITH A BACKLIGHT THAT CAN SERVE AS A NIGHTLIGHT (120 V TO 240 V MODELS)

IDEAL FOR:

KITCHEN, LIVING ROOM, BEDROOM, BASEMENT,
COMMERCIAL BUILDING, OFFICE

COLOURS

- standard: white, soft white
- luxurious finish: stainless steel

FINISH

epoxy-polyester powdercoat or stainless steel

MANUFACTURING

- 20-gauge steel cabinet and front
- the cabinet height improves the chimney effect
- bottom air intake and top air discharge

ELEMENTS

two stainless steel tubular sheathed elements insulated with nylon sleeves reducing expansion and contraction noises

CONTROL

- electronic thermostat required: built-in electronic thermostat with LCD screen (optional) or electronic wall thermostat (not included)
- automatic lowering of temperature at night (Automatic mode)
- lock option at a maximum temperature setpoint (Security mode)

INSTALLATION

- surface mounted only
- wall mounted at least 4 in. from the floor
- concealed mounting bracket (included)
- back entry plate with cable clamps (included)



ALSO AVAILABLE: SEMI-PERMANENT
INSTALLATION MODEL

QUICK PLUG-IN INTO RESIDENTIAL 120 V OUTLET




TECHNICAL SPECIFICATIONS

BUILT-IN THERMOSTAT		WITHOUT THERMOSTAT		POWER	VOLTAGE	HEIGHT		LENGTH		WEIGHT	
CODE		CODE		WATTS	VOLTS	MM	IN.	MM	IN.	KG	LB
MIR0501		MIR0501WC		500	120	457	18	444	17 1/2	5.3	11.75
MIR0508		MIR0508WC		500	208	457	18	444	17 1/2	5.3	11.75
MIR0502		MIR0502WC		500/375	240/208	457	18	444	17 1/2	5.3	11.75
---		MIR0507WC		500	277	457	18	444	17 1/2	5.3	11.75
---		MIR0503WC		500	347	457	18	444	17 1/2	5.3	11.75
MIR1001		MIR1001WC		1000	120	457	18	597	23 1/2	6.7	14.75
MIR1008		MIR1008WC		1000	208	457	18	597	23 1/2	6.7	14.75
MIR1002		MIR1002WC		1000/750	240/208	457	18	597	23 1/2	6.7	14.75
---		MIR1007WC		1000	277	457	18	597	23 1/2	6.7	14.75
---		MIR1003WC		1000	347	457	18	597	23 1/2	6.7	14.75
---		MIR1005WC		1000	480	457	18	597	23 1/2	6.7	14.75
---		MIR1006WC		1000	600	457	18	597	23 1/2	6.7	14.75
MIR1501		MIR1501WC		1500	120	457	18	749	29 1/2	8	17.75
MIR1508		MIR1508WC		1500	208	457	18	749	29 1/2	8	17.75
MIR1502		MIR1502WC		1500/1125	240/208	457	18	749	29 1/2	8	17.75
---		MIR1507WC		1500	277	457	18	749	29 1/2	8	17.75
---		MIR1503WC		1500	347	457	18	749	29 1/2	8	17.75
---		MIR1505WC		1500	480	457	18	749	29 1/2	8	17.75
---		MIR1506WC		1500	600	457	18	749	29 1/2	8	17.75
MIR2008		MIR2008WC		2000	208	457	18	902	35 1/2	9.4	20.75
MIR2002		MIR2002WC		2000/1500	240/208	457	18	902	35 1/2	9.4	20.75
---		MIR2007WC		2000	277	457	18	902	35 1/2	9.4	20.75
---		MIR2003WC		2000	347	457	18	902	35 1/2	9.4	20.75
---		MIR2005WC		2000	480	457	18	902	35 1/2	9.4	20.75
---		MIR2006WC		2000	600	457	18	902	35 1/2	9.4	20.75

Add W for white, SW for soft white or SS for stainless steel. Mechanical wall thermostats are not compatible with the without thermostat model (WC) – electronic thermostat is required.
 --- not available

MODEL WITH 120 V PLUG (RESIDENTIAL OUTLET)										
BUILT-IN THERMOSTAT	POWER	VOLTAGE	HEIGHT		LENGTH		WEIGHT			
CODE	WATTS	VOLTS	MM	IN.	MM	IN.	KG	LB		
MIR1501PW	1500	120	457	18	749	29 1/2	8	17.75		


TECHNICAL DRAWINGS



ACCESSORIES

PRODUCT	DESCRIPTION
MIRRE153*	built-in electronic low voltage relay [15 A @ 120 V-347 V]
MIRRE156*	built-in electronic low voltage relay [6 A @ 600 V]
MIRRE153T*	built-in electronic low voltage relay c/w transformer 24 V [15 A @ 208 V-347 V]

Electronic relays can receive a PWM (pulsed width modulation) or digital (on/off) signal.
 * Factory installed



BUILT-IN ELECTRONIC THERMOSTAT AVAILABLE FOR THE 120 V TO 240 V MODELS